ESD0571P6

1-Line Uni-directional TVS Diode

Features


- Small package: 1.6x1.0x0.5mm
- Protects one data or power line
- Operating Voltage: 5V
- High peak pulse current capability
- Ultra low clamping voltage
- 2-pin leadless package
- Complies with following standards:
  – IEC 61000-4-2 (ESD) immunity test
    Air discharge: ±30kV
    Contact discharge: ±30kV
  – IEC 61000-4-5 (Lightning) 120A(8/20μs)
- RoHS Compliant



DFN1610-2L

Mechanical Characteristics


- Package: DFN1610-2L
- Case Material: “Green” Molding Compound.
- Terminal Connections: See Diagram Below
- Marking Information: See Below



Circuit diagram

Applications

- Mobile Phones and Accessories
- Battery Protection
- USB VBus
- Power Line Protection
- Hand Held Portable Applications



91= Device Marking Code
Bar denotes Cathode

Marking (Top View)

Ordering Information

Part Number	Packaging	Reel Size
ESD0571P6	3000/Tape & Reel	7 inch


Absolute Maximum Ratings (T_A=25°C unless otherwise specified)

Parameter	Symbol	Value	Unit
Peak Pulse Power (8/20μs)	Ppk	1800	W
Peak Pulse Current (8/20μs)	Ipp	120	A
ESD per IEC 61000−4−2 (Air) ESD per IEC 61000−4−2 (Contact)	V_{ESD}	±30 ±30	kV
Operating Temperature Range	T_J	−55 to +125	°C
Storage Temperature Range	Tstg	−55 to +150	°C


Electrical Characteristics (T_A=25°C unless otherwise specified)

Parameter	Symbol	Min	Typ	Max	Unit	Test Condition
Reverse Working Voltage	V_{RWM}			5.0	V	
Breakdown Voltage	V_{BR}	6.0			V	I_T = 1mA
Reverse Leakage Current	I_R			1	μA	V_{RWM} = 5V
Clamping Voltage	V_C			9.5	V	I_{PP} = 20A (8 x 20μs pulse)
Clamping Voltage	V_C			15	V	I_{PP} = 120A (8 x 20μs pulse)
Junction Capacitance	C_J		450		pF	VR = 0V, f = 1MHz


Typical Performance Characteristics (T_A=25℃ unless otherwise Specified)




Junction Capacitance vs. Reverse Voltage




Peak Pulse Power vs. Pulse Time




Clamping Voltage vs. Peak Pulse Current (tp = 8/20μs)



Power Derating Curve



8 X 20μs Pulse Waveform




Note：Data is taken with a 10x attenuator

ESD Clamping Voltage


8 kV Contact per IEC61000−4−2

DFN1610-2L Package Outline Drawing



SYM	DIMENSIONS					
	MILLIMETERS			INCHES		
	MIN	NOM	MAX	MIN	NOM	MAX
A	0.45	0.50	0.55	0.018	0.020	0.022
A1	0.00	0.02	0.05	0.000	0.001	0.002
b	0.75	0.80	0.85	0.030	0.032	0.034
c	0.10	0.15	0.20	0.004	0.006	0.008
D	1.55	1.60	1.65	0.062	0.064	0.066
e	1.10 BSC			0.044 BSC		
E	0.95	1.00	1.05	0.038	0.040	0.042
L	0.35	0.40	0.45	0.014	0.016	0.018
h	0.15	0.20	0.25	0.006	0.008	0.010

Suggested Land Pattern



SYM	DIMENSIONS	
	MILLIMETERS	INCHES
X	1.00	0.040
Y1	0.62	0.025
Y2	0.60	0.024
Y3	1.22	0.049
Z	1.85	0.074