


SYMBOL DEFINITION			MISSING NUMBERS
THE NUMBER INSIDE THE SYMBOL CORRESPONDS TO THE NUMBER ON THE INSPECTION REPORT FOR THIS DRAWING/PART NUMBER	TOTAL NO. OF SYMBOLS ON DRAWING	47	
	LAST NO. USED	80	


DRG STATUS DATE	STS	REV	N/P	CHG	ZONE	REVISION HISTORY	AUTH	DR	VP	VP
14SEP99	R	01	-	-	-	ALL ACTIVES PARTS - REDRAWN TO PD	990209	JTV	MM	JC
23OCT03	R	02	-	-	-	ALL ACTIVE PARTS - REVISED TOLERANCES (4 PLCS)	247927	EDV	EDV	DMB
05NOV07	R	03	-	-	-	12129858 OBSOLETE REPLACED BY 12129811	402831	MM	MM	GB
29NOV07	R	04	-	-	-	12129858 - REINSTATED	403052	MDH	FRS	GB
29SEP9	R	05	-	-	-	ALL ACTIVE PARTS - 29.5 +0.3/-0.35 WAS 29.5±0.3, 9.5 +0.1/-0.13 WAS 5.5±0.1, 2X 20.25 +0.57/-0.15 WAS 2X 20.25±0.15, 2X 20.25 +0.15/-0.19 WAS 2X 20.25±0.15, 2X 20.35 +0.15/-0.34 WAS 2X 20.35±0.15, 10.65 +0.15/-0.21 WAS 10.65±0.15	408956	FRE	FKV	JPZ






STRAIN RELIEF SHOWN
IN ASSEMBLED POSITION







CENTERLINE MEASUREMENTS
TO BE TAKEN FROM DATUM
-A- AT 3 MM PROGRESSIONS
ALLOWABLE TOLERANCE ±0.1









NOTES

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:

   DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.

2. REFERENCE MATING COMPONENTS OR EQUIVALENT:

   FEMALE CONNECTOR 12129225
   TERMINAL 12084912
   CPA 12110299

3. THIS PART ACCEPTS THE FOLLOWING COMPONENTS OR EQUIVALENT:

   RETAINER 12129183
   SEAL (12110403)
   CAVITY PLUG(S) 12129557
   AND WHEN FULLY ASSEMBLED MATES TO HEADER CONNECTOR ASSEMBLY 12092320

4. MAX. INSULATION CRIMP DIMENSION IS 2.55 DIAMETER.

5. CRIMP WING DIMENSIONS AFTER CRIMPING MAY NOT EXCEED 2.55 MM DIAMETER MAX. CABLE O.D. 2.42 MM. REFER TO ESA-605 FOR CRIMP DIMENSION

6. (3.2)X(0.3) RAISED DELPHI CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY. OPTIONAL CONSTRUCTION TO BE "PED" OR NO LOGO.

7. THIS PRODUCT IS NOT CATEGORIZED AS AN APPEARANCE ITEM. MINOR IMPERFECTIONS INCLUDING, BUT NOT LIMITED TO, FLOW MARKS, COLOR BLEMISHES, GATE VESTIGE, AND SOFT FLASH THAT DO NOT AFFECT THE FIT, FORM, OR FUNCTION OF THE PART ARE PERMISSIBLE PER DPNP-4.7-CS-01.

PART NO	REV	N/P	STATUS	MATERIAL SPECIFICATION AND COLOR	BLOCKED CAVITIES	NUMBERS OF CAVITIES AVAILABLE	VACUUM PORT CAVITIES	VOLUME	REPLACED BY
12146313	C5	-	-	TPE COMPOUND BLACK	1,3,16,17	20	18	11.890	-
12129858	C9	-	-	TPE COMPOUND GRAY	NONE	24	18,24	11.780	-
12129255	B	-	OBSOLETE	MZ372001 TEEE 820 GRA	3,16,17	21	18	-	-

DRAWING NUMBER
12129857
SIZE A1x3 | SCALE 2:1 | PAGE 2 OF 2 | SHEET 1 OF 1 | REV R | CHG 05 | N/P -

(1) PROCESS SENSITIVE DIMENSION
DIMENSIONS ENCLOSED IN ( ) INDICATE REFERENCE DIMENSION, FOR 4D TOLERANCE (SEE MATH AND STATUS TABS)

ACCUMULATIVE ANGLE (DEG) FROM	TO	OVER	TO	OVER	TO	OVER	TO	OVER	TO
0	30	30	90	90	180	180	270	270	360
TOLERANCE UNLESS OTHERWISE SPECIFIED									
±0.15	±0.4	±0.6	±0.8	±1.0	±1.2	±1.4	±1.6	±1.8	±2.0

DRAWN TYPE: PART DRAWING
STYLE:
VOLUME (CM³):
SYSTEM CODE: D

UNLESS OTHERWISE SPECIFIED

THIS DOCUMENT IS TO HOWEVER WITH ONE 15 NM OPEN AS AMENDED BY 15% OR MORE, STANDARDIZATION OF THE INFORMATION CONTAINED IN THIS DRAWING IS THE PROPERTY OF DELPHI AND MAY NOT BE REPRODUCED OR USED FOR ANY PURPOSE EXCEPT AS AUTHORIZED IN THE LICENSE AGREEMENT OR CONTRACT UNDER WHICH THIS DRAWING WAS FURNISHED. NEITHER THIS DRAWING NOR THE INFORMATION IT DISCLOSES SHALL BE USED FOR MANUFACTURE OR SALE OF EQUIPMENT OR PRODUCTS BY ANYONE WITHOUT THE EXPRESS WRITTEN PERMISSION OF DELPHI.

ALL DIMENSIONS ARE IN MILLIMETERS

REFERENCE

THIRD ANGLE PROJECTION

DO NOT SCALE

USE MATH DATA

DELPHI
DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE
WARREN, OH

DR		DATE
VP-01	JOSE TAPIA	14SEP99
VP-02	L.R MOYSEN	30NOV99
VP-03	L.R MOYSEN	30NOV99
VP-04		
VP-05		

SUBSTRATE OF ORDERING AND RECYCLED CONTENT PER DELPHI (294900).

DRAWING NAME: SEE CHART

DRAWING NAME: TAXI LOCK STRAIN RLF MIC/P 100W

DRAWING NUMBER: 12129857
SIZE A1x3 | SCALE 2:1 | PAGE 1 OF 2 | SHEET 1 OF 1 | REV R | CHG 05 | N/P -

12129857