1N4148W

Revision: A

Silicon Epitxial Planar Switching Diodes


Features

- SOD-123 package
- Fast switching
- These diodes are also available in other case style including the DO-35 case with the type designation 1N4148, the MiniMELF case with the type designation LL4148 and the MicroMELF case with the type designation MCL4148.

Marking Code : T4

PINNING

PIN	DESCRIPTION
1	Cathode
2	Anode



Top View
Marking Code: " T4 "
Simplified outline SOD-123 and symbol

Absolute Maximum Ratings (T_a = 25 °C)


Parameter	Symbol	Value	Unit
Peak Reverse Voltage	V_{RM}	100	V
Reverse Voltage	V_R	75	V
Average Rectified Forward Current	$I_{F(AV)}$	150	mA
Non-repetitive Peak Forward Surge Current at t = 1 μs	I_{FSM}	2	A
Power Dissipation	P_{tot}	400	mW
Thermal Resistance from Junction to Ambient Air	$R_{\theta JA}$	312	°C/W
Junction Temperature	T_j	150	°C
Storage Temperature Range	T_{stg}	- 65 to + 150	°C

Characteristics at T_a = 25 °C


Parameter	Symbol	Min.	Max.	Unit
Reverse Breakdown Voltage at I_R = 1 μA	$V_{(BR)R}$	75	-	V
Forward Voltage at I_F = 10 mA at I_F = 50 mA at I_F = 150 mA	V_F	 - - -	 0.855 1 1.25	V
Peak Reverse Current at V_R = 75 V at V_R = 20 V at V_R = 75 V, T_J = 150 °C at V_R = 25 V, T_J = 150 °C	I_R	 - - - -	 1 100 50 30	 μA nA μA μA
Total Capacitance at V_R = 0 V, f = 1 MHz	C_T	-	8	pF
Reverse Recovery Time at I_{rr} = 0.1 X I_R, I_F = I_R = 10 mA, R_L = 100 Ω	t_{rr}	-	4	ns


1N4148W


Silicon Epitxial Planar Switching Diodes





Rectification Efficiency Measurement Circuit












SHANGHAI SINO-IC
MICROELECTRONICS CO., LTD.

1N4148W

Silicon Epitxial Planar Switching Diodes

PACKAGE OUTLINE

Plastic surface mounted package; 2 leads **SOD-123**



UNIT	A	b_p	C	D	E	H_E	A_1	L_p
mm	1.20 0.90	0.60 0.50	0.135 0.100	2.75 2.55	1.65 1.55	3.85 3.55	0.10 0.01	0.50 0.20

The SINO-IC logo is a registered trademark of ShangHai Sino-IC Microelectronics Co., Ltd.
© 2005 SINO-IC – Printed in China – All rights reserved.

SHANGHAI SINO-IC MICROELECTRONICS CO., LTD

Add: Building 3, Room 3401-03, No.200 Zhangheng Road, ZhangJiang Hi-Tech Park, Pudong, Shanghai 201203, China
Phone: +86-0755-26063310
Fax: +86-0755-26063304
Email: szrxw002@sino-ic.net
Website: http://www.sino-ic.net