

Product Summary

$V_{(BR)DSS}$	$R_{DS(on)TYP}$	I_D
250V	16mΩ@10V	110A



合肥矽普半导体

Siliup Semiconductor Technology Co., Ltd

技术 品质 服务

www.siliup.com


Feature

- Fast Switching
- Low Gate Charge and $R_{DS(on)}$
- **100% UIS TESTED**
- **100% ΔV_{ds} TESTED**

Applications


- PWM Application
- Hard switched and high frequency circuits
- Power Management

Package




TOLL-8L

Circuit diagram



Marking



SP16HF25TO
**

:Device Code
:Week Code

Order Information

Device	Package	Unit/Tube
SP16HF25TO	TOLL-8L	2000

Absolute maximum ratings (Ta=25°C, unless otherwise noted)


Parameter	Symbol	Rating	Units
Drain-Source Voltage	V _{DS}	250	V
Gate-Source Voltage	V _{GS}	±20	V
Continuous Drain Current (Tc=25°C)	I _D	110	A
Continuous Drain Current (Tc=100°C)	I _D	73	A
Pulsed Drain Current	I _{DM}	440	A
Single Pulse Avalanche Energy ¹	E _{AS}	720	mJ
Power Dissipation (Tc=25°C)	P _D	575	W
Power Dissipation (Tc=100°C)	P _D	230	W
Thermal Resistance Junction-to-Case	R _{θJC}	0.22	°C/W
Recovery diode dv/dt	dv/dt	50	V/ns
Storage Temperature Range	T _{STG}	-55 to 150	°C
Operating Junction Temperature Range	T _J	-55 to 150	°C

Electrical characteristics (Ta=25°C, unless otherwise noted)


Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
Static Characteristics						
Drain-Source Breakdown Voltage	BV _{DSS}	ID=250uA , VGS=0V	250	285	-	V
Drain-Source Leakage Current	I _{DSS}	VDS=200V , VGS=0V , TJ=25℃	-	-	1	uA
Gate-Source Leakage Current	I _{GSS}	VGS=±20V , VDS=0V	-	-	±100	nA
Gate Threshold Voltage	V _{GS(th)}	VGS=VDS , ID=250uA	2.5	3.5	4.5	V
Static Drain-Source On-Resistance	R _{DS(ON)}	VGS=10V , ID=20A	-	16	20	mΩ
Gate Resistance	R _G	f=1MHz	-	2.4	-	Ω
Dynamic characteristics						
Input Capacitance	C _{iss}	VDS=50V , VGS=0V , f=1MHz	-	3080	-	pF
Output Capacitance	C _{oss}		-	138	-	
Reverse Transfer Capacitance	C _{rss}		-	2.8	-	
Total Gate Charge	Q _g	VDS=200V , VGS=10V , ID=40A	-	48	-	nC
Gate-Source Charge	Q _{gs}		-	12.5	-	
Gate-Drain Charge	Q _{gd}		-	10.2	-	
Gate Plateau Voltage	V _{plateau}		-	4.5	-	V
Switching Characteristics						
Turn-On Delay Time	T _{d(on)}	VDD=200V , VGS=10V , RG=5Ω , ID=40A	-	46	-	nS
Rise Time	T _r		-	58	-	
Turn-Off Delay Time	T _{d(off)}		-	78	-	
Fall Time	T _f		-	7	-	
Diode Characteristics						
Diode Forward Voltage	V _{SD}	VGS=0V , IS=1A , TJ=25℃	-	-	1.2	V
Maximum Body-Diode Continuous Current	I _S		-	-	110	A
Reverse recover time	T _{rr}	IS=20A , di/dt=100A/us , TJ=25℃	-	86	-	nS
Reverse recovery charge	Q _{rr}		-	0.2	-	uC

Note :
1. The test condition is VDD=100V, VGS=10V, L=10mH, RG=25Ω;


Typical Characteristics




Output Characteristics




Transfer Characteristics




Capacitance Characteristics




Gate Charge




Current dissipation




Power dissipation




$R_{DS(on)}$ VS Drain Current




Forward characteristics of reverse diode




Normalized breakdown voltage



Normalized Threshold voltage





Safe Operation Area





Test Circuit



Gate Charge





Resistive Load Switching Time




Un-clamped Inductive Load Switching



Drain-Source Body Diode Reverse Recovery



Temperature Profile for IR Reflow Soldering



Profile Feature	Sn-Pb Eutectic Assembly	Pb-Free Assembly
Preheat & Soak		
Temperature min (T _{smin})	100°C	150°C
Temperature max (T _{smax})	150°C	200°C
Time (T _{smin} to T _{smax}) (t _s)	60-120 seconds	60-120 seconds
Average ramp-up rate (T _{smax} to T _p)	3 °C/second max.	3°C/second max.
Liquidous temperature (T _L)	183 °C	217°C
Time at liquidous (t _L)	60-150 seconds	60-150 seconds
Peak package body Temperature e (T _p)*	See Classification Temp in table 1	See Classification Temp in table 2
Time (t _p)** within 5°C of the specified classification temperature (T _c)	20** seconds	30** seconds
Average ramp-down rate (T _p to T _{smax})	6 °C/second max.	6 °C/second max.
Time 25°C to peak temperature	6 minutes max.	8 minutes max.
* Tolerance for peak profile Temperature (T _p) is defined as a supplier minimum and a user maximum. ** Tolerance for time at peak profile temperature (t _p) is defined as a supplier minimum and a user maximum		

Table 1. SnPb Eutectic Process – Classification Temperatures (T_c)



Package Thickness	Volume mm ³ <350	Volume mm ³ ≥350
<2.5 mm	235 °C	220 °C
≥2.5 mm	220 °C	220 °C

Table 2. Pb-free Process – Classification Temperatures (T_c)


Package Thickness	Volume mm ³ <350	Volume mm ³ 350-2000	Volume mm ³ >2000
<1.6 mm	260 °C	260 °C	260 °C
1.6 mm – 2.5 mm	260 °C	250 °C	245 °C
≥2.5 mm	250 °C	245 °C	245 °C

TOLL-8L Reel Information

REEL DIMENSIONS




TAPE DIMENSIONS



- A0: Dimension designed to accommodate the component width
- B0: Dimension designed to accommodate the component length
- K0: Dimension designed to accommodate the component thickness
- W: Overall width of the carrier tape
- P0: Pitch between successive cavity centers and sprocket hole
- P1: Pitch between successive cavity centers
- P2: Pitch between sprocket hole
- T: Tape material thickness
- D1: Reel Diameter
- W1: Reel Width

DIMENSIONS										(Unit: mm)
Reel	D1	W1								Material
	330	24.4								Hips
Tape	P0	P1	P2	W	A0	B0	K0	T	Pin 1 Quadrant	Material
	2	4	12	24	10.3	12.1	2.6	0.35	Q1	PC

All dimensions are nominal

TOLL-8L Package Information


Symbol	Dimensions In Millimeters		
	Min.	Nom.	Max.
A	2.15	2.30	2.45
b	0.60	0.75	0.90
C	0.40	0.50	0.60
D	10.18	10.38	10.58
D1	3.15	3.3	3.45
E	9.70	9.90	10.10
E1	9.65	9.80	9.95
E2	7.90	--	9.15
E3	7.20	--	8.40
e	1.20 BSC		
F	1.05	1.20	1.35
H	11.45	11.70	11.95
H2	6.75	7.00	7.3
H3	3.00 BSC		
L	1.20	--	2.10
L1	0.50	0.75	0.90
L2	0.45	0.6	0.75
M	0.08 REF.		
β	8°	10°	12°