


Feature

- Fail-safe circuitry
- Low power consumption
- Up to 128 transceivers can be attached to the bus
- Maximum transmission rate: 10Mbps
- ESD: $\geq \pm 15\text{kV}$
- DIP-8, SOP-8, MSOP-8, DFN-8, Package

Applications

- RS-485 Communications
- Level Translators
- Security Equipment
- Industrial Control Equipment
- Watt-hour meter




Ordering Information

DEVICE	Package Type	MARKING	Packing	Packing Qty
H485EIN	DIP-8	H485EI	TUBE	2000pcs/reel
H485EIM/TR	SOP-8	H485EI	REEL	2500pcs/reel
H485EIMM/TR	MSOP-8	H485EI	REEL	3000pcs/reel
H485EIDQ/TR H485EIDQ3/TR	DFN-8 3*3	H485EI	REEL	5000pcs/reel
H485ECN	DIP-8	H485EC	TUBE	2000pcs/reel
H485ECM/TR	SOP-8	H485EC	REEL	2500pcs/reel
H485ECMM/TR	MSOP-8	H485EC	REEL	3000pcs/reel
H485ECDQ/TR H485ECDQ3/TR	DFN-8 3*3	H485EC	REEL	5000pcs/reel


General Description

The H485E is high-speed transceivers for RS-485 communication, which contain one driver and one receiver. The H485E feature fail-safe circuitry, which guarantees a logic-high receiver output when the receiver inputs are open or shorted. This means that the receiver output will be a logic high if all transmitters on a terminated bus are disabled (high impedance). The H485E driver slew rates are not limited, making transmit speeds up to 10Mbps possible.. And this device has a 1/8-unit-load receiver input impedance that allows up to 128 transceivers on the bus.

Pin Assignment



DIP-8/SOP-8/MSOP-8




DFN-8 3*3

Pin Description

PIN	NAME	FUNCTION
1	RO	Receiver Output, When RE is low and if $A - B \geq -50\text{mV}$, RO will be high; if $A - B \leq -200\text{mV}$, RO will below.
2	/RE	Receiver Output Enable. Drive RE low to enable RO; RO is high impedance when RE is high. Drive RE high and DE low to enter low-power shutdown mode.
3	DE	Driver Output Enable. Drive DE high to enable driver outputs. These outputs are high impedance when DE is low. Drive RE high and DE low to enter low-power shutdown mode.
4	DI	Driver Input. With DE high, a low on DI forces noninverting output low and inverting output high.
5	GND	Ground
6	A	Noninverting Receiver Input and Noninverting Driver Output
7	B	Inverting Receiver Input and Inverting Driver Output
8	VCC	Positive Supply

Typical application circuit



Absolute Maximum Ratings (TA=25°C)

PARAMETER		MIN	MAX	UNITS
Supply Voltage (V _{CC})		-	+7V	V
Control Input Voltage (/RE, DE)		-0.3	V _{CC} +0.3V	V
Driver Input Voltage (DI)		-0.3	V _{CC} +0.3V	V
Driver Output Voltage (A,B)		-13V	+13V	V
Receiver Input Voltage (A,B)		-13V	+13V	V
Receiver Output Voltage (R _O)		-0.3	V _{CC} +0.3V	V
Operating Temperature (T _{OPR})	H485EC	0	+70	°C
	H485EI	-40	+85	°C
Storage Temperature (T _{STG})		-65	+150	°C
Lead Temperature (Soldering, 10 seconds)		-	+260	°C

Absolute Maximum Ratings indicate limits beyond which damage to the device may occur. Operating Ratings indicate conditions for which the device is intended to be functional, but specific performance is not ensured.

DC ELECTRICAL CHARACTERISTICS ($V_{CC}=5V$, $T_A=25^{\circ}C$) ⁽¹⁾

PARAMETER	SYMBOL	CONDITIONS		MIN	TYP	MAX	UNITS
Differential Driver Output (no load)	V_{OD1}	$R=27\Omega$, Figure 1		-	-	V_{CC}	V
Differential Driver Output	V_{OD2}			1.8	-	-	V
Change in Magnitude of Differential Output Voltage	ΔV_{OD}			-	-	0.2	V
Driver Common-Mode Output Voltage	V_{OC}			1.0	-	3.0	V
Change in Magnitude of Common-Mode Voltage ⁽²⁾	ΔV_{OC}			-	-	0.2	V
Input High Voltage	V_{IH}	DE, DI, /RE		2.0	-	-	V
Input Low Voltage	V_{IL}	DE, DI, /RE		-	-	0.8	V
DI Input Hysteresis	V_{HYS}	-		-	100	-	mV
Driver Input Current (A And B)	I_{IN1}	$V_{IN}=12V$	DE=0V,	-	-	150	μA
		$V_{IN}=-7V$	$V_{CC}=0V/5.25V$	-150	-	-	μA
Driver Short-Circuit Output Current ⁽³⁾	I_{OSD}	A and B Short-Circuit		-100	-	100	mA
Receiver Differential Threshold Voltage	V_{TH}	$-7V \leq V_{CM} \leq 12V$		-200	-125	-50	mV
Receiver Input Hysteresis	ΔV_{TH}	-		-	40	-	mV
Receiver Output High Voltage	V_{OH}	$I_O=-4mA$, $V_{ID}=-50mV$		$V_{CC}-1$	-	-	V
Receiver Output Low Voltage	V_{OL}	$I_O=4mA$, $V_{ID}=-200mV$		-	-	0.4	V
Three-State Output Current at Receiver	I_{OZR}	$0.4V \leq V_O \leq 2.4V$		-	-	± 1	μA
Receiver Input Resistance	R_{IN}	$-7V \leq V_{CM} \leq 12V$		96	-	-	K Ω
Receiver Output Short -Circuit Current	I_{OSR}	$0V \leq V_{RO} \leq V_{CC}$		± 7	-	± 100	mA
Supply Current	I_{CC}	DE=VCC	No Load/ RE=DI	-	450	900	μA
		DE=GND	=VCC/GND	-	450	600	μA
Supply Current in Shutdown Mode	I_{SHDN}	DE=GND, /RE=VCC, DI=VCC/GND		-	-	10	μA

Note 1: All currents into the device are positive; all currents out of the device are negative. All voltages are referred to device ground unless otherwise noted.

Note 2: ΔV_{OD} and ΔV_{OC} are the changes in V_{OD} and V_{OC} , respectively, when the DI input changes state.

Note 3: Maximum current level applies to peak current just prior to foldback-current limiting; minimum current level applies during current limiting.

Switching Characteristics (VCC=5V, TA=25°C)

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNITS
Driver Input to Output	t_{DPLH}	Figure 3 and 5, $R_{DIFF}=54\Omega$ $C_{L1}=C_{L2}=100pF$	-	30	60	ns
	t_{DPHL}		-	30	60	ns
Driver Output Skew $ T_{DPLH} - T_{DPHL} $	t_{DSKEW}		-	-	20	ns
Driver Rise or Fall Time	t_{DR}, t_{DF}		-	30		ns
Maximum Data Rate	F_{MAX}	-	10	-	-	Mbps
Driver Enable to Output High	t_{DZH}	Figure 4 and 6, $C_L=100pF$ S2 closed	-	-	70	ns
Driver Disable Time from High	t_{DHZ}		-	-	70	ns
Driver Enable to Output Low	t_{DZL}	Figure 4 and 6, $C_L=100pF$ S1 closed	-	-	70	ns
Driver Disable Time from Low	t_{DLZ}		-	-	70	ns
Receiver Input to Output	t_{RPLH} t_{RPHL}	Figure 7 and 9, $ V_{ID} \geq 2.0V$, rise and fall time of $V_{ID} \leq 15ns$	-	90	250	ns
$ T_{RPLH} - T_{RPHL} $ Differential Receiver Skew	t_{RSKD}		-	30	-	ns
Receiver Enable to Output Low	t_{RZL}	Figure 2 and 8, $C_{RL}=15pF$ S1 closed	-	30	70	ns
Receiver Disable Time from Low	t_{RLZ}		-	30	70	ns
Receiver Enable to Output High	t_{RZH}	Figure 2 and 8, $C_{RL}=15pF$ S2 closed	-	30	70	ns
Receiver Disable Time from High	t_{RHZ}		-	30	70	ns
Time to Shutdown	t_{SHDN}	-	-	200	600	ns

Function Tables

Transmitting

INPUTS			OUTPUTS	
/RE	DE	DI	A	B
X	1	1	1	0
X	1	0	0	1
0	0	X	High-Z	High-Z
1	0	X	Shutdown	

Receiving

INPUTS			OUTPUT
/RE	DE	A-B	RO
0	X	$\geq -0.05V$	1
0	X	$\leq -0.2V$	0
0	X	Open/shorted	1
1	1	X	High-Z
1	0	X	Shutdown

Test circuit




Figure 1. Driver DC Test Load




Figure 2. Receiver Enable/Disable Timing Test Load




Figure 3. Driver Timing Test Circuit




Figure 4. Driver Enable/Disable Timing Test Load




Figure 5. Driver Propagation Delays




Figure 6. Driver Enable and Disable Times




Figure 7. Receiver Propagation Delays





Figure 8. Receiver Enable and Disable Times

Physical Dimensions


DIP-8



Dimensions In Millimeters(DIP-8)

Symbol:	A	B	D	D1	E	L	L1	a	b	c	d
Min:	6.10	9.00	8.10	7.42	3.10	0.50	3.00	1.50	0.85	0.40	2.54 BSC
Max:	6.68	9.50	10.9	7.82	3.55	0.70	3.60	1.55	0.90	0.50	

SOP-8




△ Package top mark may be in lower left corner or unmark

Dimensions In Millimeters(SOP-8)

Symbol:	A	A1	B	C	C1	D	Q	a	b
Min:	1.35	0.05	4.90	5.80	3.80	0.40	0°	0.35	1.27 BSC
Max:	1.55	0.20	5.10	6.20	4.00	0.80	8°	0.45	

Physical Dimensions


MSOP-8



Dimensions In Millimeters(MSOP-8)

Symbol:	A	A1	B	C	C1	D	Q	a	b
Min:	0.80	0.05	2.90	4.75	2.90	0.35	0°	0.25	0.65 BSC
Max:	0.90	0.20	3.10	5.05	3.10	0.75	8°	0.35	

DFN-8 3*3_0.65 Pin spacing



Dimensions In Millimeters(DFN-8 3*3)

Symbol:	A	A1	B	B1	E	F	G	H	a	b
Min:	0.85	0.00	2.90	2.90	0.20	0.30	2.1	1.3	0.20	0.65 BSC
Max:	0.95	0.05	3.10	3.10	0.25	0.50	2.5	1.7	0.34	

Revision History

REVISION NUMBER	DATE	REVISION	PAGE
V1.0	2014-10	New	1-11
V1.1	2020-9	Updated DIP-8 dimension、Add annotation for Maximum Ratings.	3、 8
V1.2	2024-11	Add the DFN-8 package device、Update Lead Temperature	1、 3
V1.3	2025-11	Update important statements、Update SOP-8 Dimension drawing	8、 11
V1.4	2026-9	Update DFN-8 Dimension drawing	9

IMPORTANT STATEMENT:

Huaguan Semiconductor reserves the right to change products and services offered without prior notice. Customers should obtain the latest relevant information before placing orders and verify that such information is current and complete. Huaguan Semiconductor assumes no responsibility or liability for altered documents.

Customers are responsible for complying with safety standards and implementing safety measures when using Huaguan Semiconductor products in system design and end-product manufacturing. You assume full responsibility for: selecting the appropriate Huaguan Semiconductor products for your application; designing, validating, and testing your application; and ensuring that your application complies with applicable standards and all other safety, security, or other requirements. This is to prevent potential risks that may lead to personal injury or property damage.

Huaguan Semiconductor products are not approved for use in life support, military, aerospace, or other high-risk applications. Huaguan products are neither intended nor warranted for use in such systems or equipment. Any failure or malfunction may lead to personal injury or severe property damage. Such applications are deemed "Unsafe Use." Unsafe Use includes, but is not limited to: surgical and medical equipment, nuclear energy control equipment, aircraft or spacecraft instruments, control or operation of vehicle power, braking, or safety systems, traffic signal instruments, all types of safety devices, and any other applications intended to support or sustain life. Huaguan Semiconductor shall not be liable for consequences resulting from Unsafe Use in these fields. Users must independently evaluate and assume all risks. Any issues, liabilities, or losses arising from the use of products beyond their approved applications shall be solely borne by the user. Users may not claim any compensation from Huaguan Semiconductor based on these terms. If any third party claims against Huaguan Semiconductor due to such Unsafe Use, the user shall compensate Huaguan Semiconductor for all resulting damages and liabilities.

Huaguan Semiconductor provides technical and reliability data (including datasheets), design resources (including reference designs), application or other design advice, web tools, safety information, and other resources for its semiconductor products. However, no guarantee is made that these resources are free from defects, and no express or implied warranties are provided. The use of testing and other quality control techniques is limited to Huaguan Semiconductor's quality assurance scope. Not all parameters of each device are tested.

Huaguan Semiconductor's documentation authorizes you to use these resources only for developing applications related to the products described herein. You are not granted rights to any other intellectual property of Huaguan Semiconductor or any third party. Any other reproduction or display of these resources is strictly prohibited. You shall fully indemnify Huaguan Semiconductor and its agents against any claims, damages, costs, losses, and liabilities arising from your use of these resources. Huaguan Semiconductor shall not be held responsible.