

CUSTOMER DRAWING


REV. 版本	ECN NO. ECN编号	DATE 日期	DESCRIPTION 内容描述	APPROVED BY 核准
A0	——	2026/09/14	NEW RELEASE	APLIN





LED COLOR					
Red	Yellow	Green	Blue	White	Orange Blue


NOTES:
1.RATING: 12VDC 50mA
2.CONTACT RESISTANCE: 100mΩ Max
3.INSULATION RESISTANCE: 100MΩ 250VDC FOR 1MIN
4.DIELECTRIC STRENGTH: 250VAC(50/60Hz) FOR 1MIN
5.LIFE TEST:100,000 CYCLES
6.OPERATION FORCE&TRAVEL: SEE SPECIFICATION














5	LED	GaAsP/GaP
4	TERMINAL	Bronze Silver Plated
3	CONTACT	PBS/SUS
2	BUTTON	POM
1	HOUSING	PA66
ITEM	PART NAME	MATERIAL

佛山市皓通电子有限公司
FoShan Haoswitch Electronic Co.,Ltd.

DRAWN BY 制 图	YUAN	2026/09/14	SCALE 比 例	FREE	PRODUCT NAME 产品名称	tact SWITCH
CHECKED BY 核 对	APLIN	2026/09/14	PAGE 页 面	1/1	DESCRIPTION 产品描述	
APPROVED BY 批 准	ZHANG	2026/09/14	UNIT 单 位	mm		
TOLERANCE 未标注公差	X: ±0.5 .X: ±0.3 .XX: ±0.2	X°: ±5° .X°: ±2°	PROJECTED 投影		PART NO. 物料编号	H26-TC03-1L-W-PO
					SIZE 尺寸 A4	DRAWN NO. 图纸编号 HTDW20260914031

https://www.howswitch.com