

Specifications

备注(Remark)

1. 材料(MATERIAL)

胶芯: PA9T+30%G. F UL94V-0, 颜色: 黑色.

Housing: PA9T+30%G. F UL94V-0, Color: Black

端子: 磷铜, 镍底30u", 表面镀半金高温亮锡10U"

Contact: Phosphor, 10u" SEMI-GOLD PLATED WITH HIGH

TEMPRETURE BRIGHT TIN

30u" NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电压: 250V AC/DC

Rated Voltage: 250V AC/DC

额定电流: 3 AMP

Raring Current: 3 AMP.

接触阻抗: 20 mΩ MAX.

Contact Resistance: 20 mΩ MAX.

绝缘阻抗: 1000 MΩ MIN.


Insulating Resistance: 1000 MΩ MIN.

耐电压: AC 500V/分钟.




Withstanding Voltage: AC 500V/Minute.

温度范围: -40° C to +105° C

Temperture Range: -40° C to +105° C



Recommended P.C.B LAYOUT
General Tolerance ±0.05



Ordering Information

F171-12 06 B6 C MU B 1

NO. OF PINS
PER ROW
2~40P

Contact Plating
Full Of Gold
A0=0.8u"
A1=1u"
A2=1.5u"
A3=2u"
A4=3u"
A5=5u"
A6=10u"
A7=15u"
A8=20u"
A9=30u"

Semi-gold
B0=0.8U"
B1=1U"
B2=1.5U"
B3=2U"
B4=3U"
B5=5U"
B6=10U"
B7=15U"
B8=20U"
B9=30U"

INSULATOR
MATERIAL:
B: PA6T
C: PA9T
D: LCP

PACKING
A: PE Bag
B: Tape & Reel
C: Tube
D: Tube+CAP
E: Tray

S1=Ordinary Tin Plated
S2=Matte Tin Plated
S3=Tin-plated High-temperature
C1=1u" MIN GOLD PLATED WITH HIGH
TEMPRETURE MATTE TIN

				OPERATION		SCALE		Fit				
--	--	--	--	-----------	--	-------	--	-----	--	--	--	--