



深圳市佑驰电子有限公司

Specification for Approval

产品名称: 一体系列电感
规格型号: TCHC-1080-XXX-MM-6A
产品编号:
日期: 2026-05-19

1、本承诺书的内容更改需经过双方确认，任一方单独的修改均视为无效。


2、本承诺书在送达客户后，请给予承认并即签回，如无签回下订单的，我司有权以此承认书标准生产，并表示购买方默认许可。

核准	审核	制作
Darren	Wangkai	Kalyn

REVISION					
REV	DESCRIPTION	DATE	DESIGNED	CHECKED	APPROVED
A0	Initial Release	2026/05/19	Kalyn	Wangkai	Darren

High Current, Power Inductors

TCHC-1080-XXX-MM-6A Power Choke



Description

- AEC-Q200 qualified
- Halogen Free
- 165°C maximum total temperature operation
- 11.15x10.3x8.0mm maximum surface mount package
- Magnetically shielded, low EMI
- High current carrying capacity, Low core losses
- RoHS compliant

Applications

- Automotive applications

Environmental Data


- Storage temperature range: -55°C to +165°C
- Operating temperature range: -55°C to +165°C (ambient plus self-temperature rise)
- Solder reflow temperature: J-STD-020 compliant

Description													
TCHC-1080-100-MM-6A				10.0μH				±20%					
Model				Inductance Value				Inductance Tolerance					
Global Part Number													
T	C	H	C	1	0	8	0	1	0	0	M	M	6A
Product Series				Dimensions				Inductance Value		Tolerance	Special Marking		165°C

Part No.	Inductance	DC Resistance		Heating Rating Current		Saturation Current		Rated Voltage
	L0 (μH)	DCR (mΩ)		Idc (A)		Isat (A)		V
	±20%, 100kHz, 1.0V	TYP.	MAX.	TYP.	MAX.	TYP.	MAX.	MAX.
TCHC-1080-100-MM-6A	10.0	31.0	37.2	5.3	4.8	12.4	10.6	75
TCHC-1080-150-MM-6A	15.0	39.0	46.8	5.0	4.6	10.6	9.1	75
TCHC-1080-220-MM-6A	22.0	83.0	99.0	3.4	3.1	8.3	7.1	75
TCHC-1080-330-MM-6A	33.0	85.0	114.0	4.8	4.5	7.6	6.5	75
TCHC-1080-470-MM-6A	47.0	108.0	129.6	2.9	2.6	6.1	5.2	55

Notes

1. All test data is referenced to 25°C ambient
2. Operating temperature range - 55°C to + 165°C
3. Idc(A): DC current (A) that will cause an approximate ΔT of 40°C (reference ambient temperature is 25°C)
4. Isat(A): DC current (A) that will cause L0 to drop approximately 30%
5. The part temperature (ambient + temp rise) should not exceed 165°C under worst case operating conditions. Circuit design, component placement, PWB trace size and thickness, airflow and other cooling provisions all affect the part temperature. Part temperature should be verified in the end application.

• Dimensions-mm

• **Marking**

The inductor is marked with a 3-digit code

Example - $-10.0\mu\text{H} \rightarrow 100$

Y W W

(1) (2)

XXX

(3)

Where (1) Year code


Ex: 2025=5

(2) Weekly code



Serial number: 01~53

(3) Lot No. Last three digits

Note: Using Laser for marking



• **Schematics**



• Solder Reflow Profile




Table 1-Standard SnPb Solder(T_c)

Package Thickness	Volume mm ³ <350	Volume mm ³ <350
<2.5mm	235°C	220°C
≥2.5mm	220°C	220°C

Table 2-Lead(Pb) Free Solder(T_c)

Package Thickness	Volume mm ³ <350	Volume mm ³ 350-2000	Volume mm ³ >2000
<1.6mm	260°C	260°C	260°C
1.6-2.5mm	260°C	250°C	245°C
>2.5mm	250°C	245°C	245°C


Reference JDEC J-STD-020

Profile Feature	Standard SnPb Solder	Lead (Pb) Free Solder
Preheat and Soak		
• Temperature min. (T _{smmin})	100°C	150°C
• Temperature max.(T _{smmax})	150°C	200°C
• Time (T _{smmin} to T _{smmax})(t _s)	60-120 Seconds	60-120 Seconds
Average ramp up rate T _{smmax} to T _p	3°C/Second Max.	3°C/Second Max.
Liquidous temperature (T _L)	183°C	217°C
Time at liquidous(t _L)	60-150 Seconds	60-150 Seconds
Peak package body temperaure (T _p)*	Table 1	Table 2
Time (t _p)** within 5°C of the specified classification temperature(T _c)	20 Seconds**	30 Seconds**
Average ramp-down rate (T _p to T _{smmax})	6°C/Second Max.	6°C/Second Max.
Time 25°C to Peak Temperature	6 Minutes Max.	8 Minutes Max.

* Tolerance for peak profile temperature (T_p) is defined as a supplier minimum and a user maximum.


** Tolerance for time at peak profile temperature (t_p) is defined as a supplier minimum and a user maximum.

Tape Packaging Dimensions-mm




A0	B0	K0	t
10.7±0.10	12.0±0.10	8.5±0.10	0.5±0.05

Taping dimension and tape direction, Leader, Trailer, section dimension



Leader section	Min.400mm
Carrier tape start size	Min.100mm
Trailer section size	Min.160mm


Reel Dimensions-mm



• Peel force of top cover tape

The peel speed shall be about 300mm/minute

The peel force of top cover tape shall be between 0.1 to 1.3 N



Numbers of taping
400pieces/reel