




REVISIONS (修正)			
NO. (序号)	DESCRIPTION(描述)	DCN NO.(变更号)	DATE(日期)
D.0	NEW RELEASE		

- NOTE;
- Material
Plunger: C6801
Barrel: C6801
Spring: SUS
 - Plating
Plunger: 3 micro-inch minimum Au
over 50~100 micro-inch nickel
Barrel : 1 micro-inch minimum Au
over 50~100 micro-inch nickel
Spring: 1 micro-inch minimum Au
over 30~80 micro-inch nickel
 - Electrical
Rated current & voltage: DC12V; 1.0A.
Contact resistance: 50 mohm maximum
at working height(quiescence)
 - Mechanical
Spring force:50g±20g at Normal working height
Durability: 10,000 cycles(minimum)
 - When the current is greater than 2A then need
to increase the time delaycircuit(3 second)
 - To ensure the best usage,please operate it based
on the working height
Based on the engineering drawings,shall not
exceed the maximum allowed compression
 - Products comply with ROHS standards

DRAW (设计)	LIAOYI	SCALE (比例)	10 : 1	UNIT (单位)	mm	DRAWING NO. (图号)	KTT50003UT01-R
COUNTER SIGN (会签)		SHEET (页数)	1 of 1	PROJECT (视图)		MATERIAL (材质)	Seeing notes (见备注)
AUDIT (审核)		DATE (日期)	2024.9.25	VER (版次)	D.0	TITLE (品名)	Pogo pin
APPROVE (核准)		PLATE (镀层)	Seeing notes(见备注)				
THE UNMARKED TOLERANCE ARE AS BELOW : (未标记的公差) LENGTH (尺寸)				东莞市柯睿电子有限公司 Dong Guan KeRui Electronics Co,Ltd			
0~6.0		±0.05mm	0.	±2.0°			
>6~30		±0.10mm	0.0	±1.0°			
>30~120		±0.15mm	0.00	±0.50°			
The information in this document is property of KeRui company and should not be copied or reproduced in any other way, without written permission.							