Interface Transceiver of RS-232 Standard with One Supply Voltage

Features

- 300 μA SUPPLY CURRENT
- 120Kbps MAX GUARENTEED DATA RATE
- 3V/μs MINIMUM GUARANTEED SLEW RATE
- ENHANCED ESD SPECIFICATIONS:
  - ±15kV IEC61000-4-2 Air Discharge
  - ±8kV IEC61000-4-2 Contact Discharge
- AVAILABLE IN DIP-16, SOP-16 AND TSSOP16



DIP-16



SOP-16



TSSOP-16

Ordering Information


Device	Package Type	Marking	Packing	Packing Qty
SP3232ECN	DIP-16	SP3232EC	TUBE	1000pcs/box
SP3232ECM/TR	SOP-16	SP3232EC	REEL	2500pcs/reel
SP3232ECMT/TR	TSSOP-16	3232EC	REEL	2500pcs/reel
SP3232EIN	DIP-16	SP3232EI	TUBE	1000pcs/box
SP3232EIM/TR	SOP-16	SP3232EI	REEL	2500pcs/reel
SP3232EIMT/TR	TSSOP-16	3232EI	REEL	2500pcs/reel

Description

The SP3232E is a 3.3V powered EIA/TIA-232 and V.28/V.24 communication interface with low power requirements, high data-rate capabilities. SP3232E has a proprietary low dropout transmitter output stage providing true RS-232 performance from 3.3V to 5.5V supplies. The device requires only four small 0.1 μF standard external capacitors for operations from 3.3V supply.

The SP3232E has two receivers and two drivers. The device is guaranteed to run at data rates of 120Kbps while maintaining RS-232 output levels. Typical applications are Notebook, Subnotebook and Palmtop Computers, Battery Powered Equipment, Hand-Held Equipment, Peripherals and Printers.

Pin Configuration



DIP-16/SOP-16/TSSOP-16

Pin Description

PIN N°	SYMBOL	NAME AND FUNCTION
1	C1+	Positive Terminal for the first Charge Pump Capacitor
2	V+	Doubled Voltage Terminal
3	C1-	Negative Terminal for the first Charge Pump Capacitor
4	C2+	Positive Terminal for the second Charge Pump Capacitor
5	C2-	Negative Terminal for the second Charge Pump Capacitor
6	V-	Inverted Voltage Terminal
7	T2OUT	Second Transmitter Output Voltage
8	R2IN	Second Receiver Input Voltage
9	R2OUT	Second Receiver Output Voltage
10	T2IN	Second Transmitter Input Voltage
11	T1IN	First Transmitter Input Voltage
12	R1OUT	First Receiver Output Voltage
13	R1IN	First Receiver Input Voltage
14	T1OUT	First Transmitter Output Voltage
15	GND	Ground
16	V_{CC}	Supply Voltage

Absolute Maximum Rating

Symbol	Parameter		Value	Unit
V_{CC}	Supply Voltage		-0.3 to 6	V
V+	Doubled Voltage Terminal		(V_{CC} - 0.3) to 7	V
V-	Inverted Voltage Terminal		0.3 to -7	V
V_+ + |V-|			13	V
T_{IN}	Transmitter Input Voltage Range		-0.3 to 6	V
R_{IN}	Receiver Input Voltage Range		± 25	V
T_{OUT}	Transmitter Output Voltage Range		± 13.2	V
R_{OUT}	Receiver Output Voltage Range		-0.3 to (V_{CC} + 0.3)	V
Ta	Operating Temerature	SP3232EC	0 to 70	°C
		SP3232EI	-40 to 85	°C
Ts	Storage Temperature		-60 to 150	°C
TL	Lead Temperature (Soldering, 10 seconds)		260	°C
t_{SHORT}	Transmitter Output Short to GND Time		Continuous	

* Stresses beyond those listed under “absolute maximum ratings” may cause permanent damage to the device.
These are stress ratings only and functional operation of the device at these or any other conditions beyond those indicated under “recommended operating conditions” is not implied.
Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.
V+ and V-can have a maximum magnitude of +7V, but their absolute addition cannot exceed 13 V.

Electrical Characteristics

(C_1 - C_4 = 0.1μF, V_{CC} = 3.3V to 5.5V, T_A = -40 to 85°C, unless otherwise specified. Typical values are referred to T_A = 25°C)

Symbol	Parameter	Test Conditions	Min.	Typ.	Max.	Unit
I_{SUPPLY}	VCC Power Supply Current	No Load V_{CC} = 3.3V ±10% T_A = 25°C		2.5	5	mA
		No Load V_{CC} = 5V ±10% T_A = 25°C		6	10	mA

Logic Input Electrical Characteristics

(C1 - C4 = 0.1μF,V_{CC} = 3.3V to 5.5V, T_A = -40 to 85°C, unless otherwise specified. Typical values are referred to T_A = 25°C)

Symbol	Parameter	Test Conditions	Min.	Typ.	Max.	Unit
V_{TIL}	Input Logic Threshold Low	T-IN (Note 1)			0.8	V
V_{TIH}	Input Logic Threshold High	V_{CC} = 3.3V V_{CC} = 5V	2 2.4			V V
I_{IL}	Input Leakage Current	T-IN		± 0.01	± 1	μA

Note1: Transmitter input hysteresis is typically 250mV

Transmitter Electrical Characteristics

(C_1 - C_4 =0.1μF tested at V_{CC}= 3.3V to 5.5V,T_A =-40 to 85°C,unless otherwise specified.Typical values are referred to T_A = 25°C)

Symbol	Parameter	Test Conditions		Min.	Typ.	Max.	Unit
V_{TOUT}	Output Voltage Swing	All Transmitter outputs are loaded with 3KΩ to GND	V_{CC} = 5.0V	± 5	± 5.4		V
			V_{CC} = 3.3V	± 3.5	± 4.0		V
R_{TOUT}	Transmitter Output Resistance	V_{CC} = V+ = V- = 0V V_{OUT} = ± 2V		300	10M		Ω
I_{TSC}	Output Short Circuit Current	V_{CC} = 3.3V to 5V V_{OUT} = 0V				± 60	mA

Receiver Electrical Characteristics

(C_1 - C_4 = 0.1μF tested at V_{CC} = 3.3V to 5.5V, T_A = -40 to 85°C, unless otherwise specified. Typical values are referred to T_A = 25°C)

Symbol	Parameter	Test Conditions	Min.	Typ.	Max.	Unit
V_{RIN}	Receiver Input Voltage Operating Range		-25		25	V
V_{RIL}	RS-232 Input Threshold Low	T_A = 25°C V_{CC} = 3.3V T_A = 25°C V_{CC} = 5V	0.6 0.8	1.2 1.5		V
V_{RIH}	RS-232 Input Threshold High	T_A = 25°C V_{CC} = 3.3V T_A = 25°C V_{CC} = 5V		1.5 1.8	2.4 2.4	V
V_{RIHYS}	Input Hysteresis			0.3		V
R_{RIN}	Input Resistance	T_A = 25°C	3	5	7	kΩ
V_{ROL}	TTL/CMOS Output Voltage Low	I_{OUT} = 1.6mA V_{CC} = 3.3V			0.4	V
		I_{OUT} = 3.2mA V_{CC} = 5.5V				
V_{ROH}	TTL/CMOS Output Voltage High	I_{OUT} = -0.5mA V_{CC} = 3.3V	V_{CC}-0.6	V_{CC}-0.1		V
		I_{OUT} = -1mA V_{CC} = 5.5V				


Timing Characteristics

(C_1 - C_4 = 0.1μF, V_{CC} = 3.3V to 5.5V, T_A = -40 to 85°C, unless otherwise specified. Typical values are referred to T_A = 25°C)

Symbol	Parameter	Test Conditions		Min.	Typ.	Max.	Unit
D_R	Data Transfer Rate	R_L = 3KΩ	C_{L2}= 1000pF one transmitter switching	V_{CC}=3.3V		120	Kbps
t_{PHLR} t_{PLHR}	Propagation Delay Input to Output	R_{XIN} = R_{XOUT}	C_L = 150pF		4.0	9.7	μs
t_{PHLT} t_{PLHT}	Propagation Delay Input to Output	RL = 3KΩ	C_L = 2500pF		2.0	5.0	μs
$\|t_{PHLR} - t_{PLHR}\|$	Receiver Propagation Delay Difference				300		ns
$\|t_{PHLT} - t_{PLHT}\|$	Transmitter Propagation Delay Difference				300		ns
S_{RT}	Transition Slew Rate	T_A = 25°C R_L = 3KΩ to 7KΩ V_{CC} =3.3V measured from +3V to -3V or -3V to +3V C_L = 150pF to 1000pF		3		30	V/μs

Transmitter Skew is measured at the transmitter zero cross points

Application Circuits




Capacitance Value (μf)


Vcc	C1	C2	C3	C4	Cbypass
3.0 to 5.5	1.0	1.0	1.0	1.0	1.0

Typical Operating Characteristics

(V_{CC} = +3.3V, 120kbps data rate, 0.1μF capacitors, all transmitters loaded with 3kΩ, TA = +25°C, unless otherwise noted.)



TRANSMITTER OUTPUT VOLTAGE
vs. LOAD CAPACITANCE



SLEW RATE
vs. LOAD CAPACITANCE

ESD Protection

The SP3232E incorporates ruggedized ESD cells on all driver output and receiver input pins. The ESD structure is for rugged applications and environments sensitive to electro-static discharges and associated transients. The ESD tolerance is at least ±15kV without damage or latch-up.

There are different methods of ESD testing applied:
a) MIL-STD-883, Method 3015.7
b) IEC1000-4-2 Air-Discharge

The Human Body Model has been the generally accepted ESD testing method for semiconductors. This method is also specified in MIL-STD- 883, Method 3015.7 for ESD testing. The premise of this ESD testi s to simulate the human body's potential to store electro-static energy and discharge it to an integrated circuit. The simulation is performed by using a test model as shown in Figure 1. This method will test the IC's capability to withstand an ESD transient during normal handling such as in manufacturing areas where the ICs tend to be handled frequently.

The IEC-1000-4-2, formerly IEC801-2, is generally used for testing ESD on equipment and systems. For system manufacturers, they must guarantee a certain amount of ESD protection since the system itself is exposed to the outside environment and human presence. The premise with IEC1000-4-2 is that the system is required to withstand an amount of static electricity when ESD is applied to points and surfaces of the equipment that are accessible to personnel during normal usage. The transceiver IC receives most of the ESD current when the ESD source is applied to the connector pins. The test circuit for IEC1000-4-2 is shown on Figure 2. There are two methods within IEC1000-4-2, the Air Discharge method and the Contact Discharge method.

With the Air Discharge Method, an ESD voltage is applied to the equipment under test (EUT) through air. This simulates an electrically charged person ready to connect a cable onto the rear of the system only to find an unpleasant zap just before the person touches the back panel. The high energy potential on the person discharges through an arcing path to the rear panel of the system before he or she even touches the system. This energy, whether discharged directly or through air, is predominantly a function of the discharge current rather than the discharge voltage. Variables with an air discharge such as approach speed of the object carrying the ESD potential to the system and humidity will tend to change the discharge current. For example, the rise time of the discharge current varies with the approach speed.




Fig. 1 ESD Test Circuit for Human Body Model

The Contact Discharge Method applies the ESD current directly to the EUT. This method was devised to reduce the unpredictability of the ESD arc. The discharge current rise time is constant since the energy is directly transferred without the air-gap arc. In situations such as hand held systems, the ESD charge can be directly discharged to the equipment from a person already holding the equipment. The current is transferred on to the keypad or the serial port of the equipment directly and then travels through the PCB and finally to the IC.

The circuit models in Figures 1 and 2 represent the typical ESD testing circuits used for these methods. The CS is initially charged with the DC power supply when the first switch (SW1) is on. Now that the capacitor is charged, the second switch (SW2) is on while SW1 switches off. The voltage stored in the capacitor is then applied through RS, the current limiting resistor, onto the device under test (DUT). In ESD tests, the SW2 switch is pulsed so that the device under test receives a duration of voltage.




Fig. 2. ESD Test Circuit for IEC1000-4-2





Fig. 3. ESD Test Waveform for IEC1000-4-2

For the Human Body Model, the current limiting resistor (R_S) and the source capacitor (C_S) are 1.5kΩ an 100pF, respectively. For IEC-1000-4-2, the current limiting resistor (R_S) and the source capacitor (C_S) are 330Ω an 150pF, respectively. The higher C_S value and lower R_S value in the IEC1000-4-2 model are more stringent than the Human Body Model. The larger storage capacitor injects a higher voltage to the test point when SW2 is switched on. The lower current limiting resistor increases the current charge onto the test point.

Device Pin Tested	IEC1000-4-2	
	Air Discharge	Level
Driver Outputs Receiver Inputs	±15kV ±15kV	4 4


Physical Dimensions

DIP-16



Dimensions In Millimeters(DIP-16)											
Symbol:	A	B	D	D1	E	L	L1	a	b	c	d
Min:	6.10	18.94	8.10	7.42	3.10	0.50	3.00	1.50	0.85	0.40	2.54 BSC
Max:	6.68	19.56	10.9	7.82	3.55	0.70	3.60	1.55	0.90	0.50	


SOP-16



Dimensions In Millimeters(SOP-16)									
Symbol:	**A**	**A1**	**B**	**C**	**C1**	**D**	**Q**	**a**	**b**
Min:	1.35	0.05	9.80	5.80	3.80	0.40	0°	0.35	1.27 BSC
Max:	1.55	0.20	10.0	6.20	4.00	0.80	8°	0.45	

Physical Dimensions

TSSOP-16



Dimensions In Millimeters(TSSOP-16)									
Symbol:	A	A1	B	C	C1	D	Q	a	b
Min:	0.85	0.05	4.90	6.20	4.30	0.40	0°	0.20	0.65 BSC
Max:	0.95	0.20	5.10	6.60	4.50	0.80	8°	0.25	

Revision History

REVISION NUMBER	DATE	REVISION	PAGE
V1.0	2014-8	New	1-12
V1.1	2016-10	Document Reformatting	1-12
V1.2	2024-11	Update Lead Temperature	3
V1.3	2025-9	Update important statements	12
V1.4	2025-12	Update SOP-16 Dimension drawing	9

IMPORTANT STATEMENT:

Huaguan Semiconductor reserves the right to change products and services offered without prior notice. Customers should obtain the latest relevant information before placing orders and verify that such information is current and complete. Huaguan Semiconductor assumes no responsibility or liability for altered documents.

Customers are responsible for complying with safety standards and implementing safety measures when using Huaguan Semiconductor products in system design and end-product manufacturing. You assume full responsibility for: selecting the appropriate Huaguan Semiconductor products for your application; designing, validating, and testing your application; and ensuring that your application complies with applicable standards and all other safety, security, or other requirements. This is to prevent potential risks that may lead to personal injury or property damage.

Huaguan Semiconductor products are not approved for use in life support, military, aerospace, or other high-risk applications. Huaguan products are neither intended nor warranted for use in such systems or equipment. Any failure or malfunction may lead to personal injury or severe property damage. Such applications are deemed "Unsafe Use." Unsafe Use includes, but is not limited to: surgical and medical equipment, nuclear energy control equipment, aircraft or spacecraft instruments, control or operation of vehicle power, braking, or safety systems, traffic signal instruments, all types of safety devices, and any other applications intended to support or sustain life. Huaguan Semiconductor shall not be liable for consequences resulting from Unsafe Use in these fields. Users must independently evaluate and assume all risks. Any issues, liabilities, or losses arising from the use of products beyond their approved applications shall be solely borne by the user. Users may not claim any compensation from Huaguan Semiconductor based on these terms. If any third party claims against Huaguan Semiconductor due to such Unsafe Use, the user shall compensate Huaguan Semiconductor for all resulting damages and liabilities.

Huaguan Semiconductor provides technical and reliability data (including datasheets), design resources (including reference designs), application or other design advice, web tools, safety information, and other resources for its semiconductor products. However, no guarantee is made that these resources are free from defects, and no express or implied warranties are provided. The use of testing and other quality control techniques is limited to Huaguan Semiconductor's quality assurance scope. Not all parameters of each device are tested.

Huaguan Semiconductor's documentation authorizes you to use these resources only for developing applications related to the products described herein. You are not granted rights to any other intellectual property of Huaguan Semiconductor or any third party. Any other reproduction or display of these resources is strictly prohibited. You shall fully indemnify Huaguan Semiconductor and its agents against any claims, damages, costs, losses, and liabilities arising from your use of these resources. Huaguan Semiconductor shall not be held responsible.