TPCDSOD323-T36S

1-LineUnI-directional TVS Diode

WWW.TECHPUBLIC.COM

Features

* 350W peak pulse power (8/20μs)
* Protects one data or power line
* Ultra low leakage：nA level
* Operating voltage：36V
* Ultra low clamping voltage
* Complies with following standards:
  – IEC 61000-4-2 (ESD) immunity test
  Air discharge: ±30kV
  Contact discharge: ±30kV
  –IEC61000-4-5 (Lightning) 5A (8/20μs)
  – IEC61000-4-4 (EFT) 40A (5/50ns)
* RoHS Compliant

Mechanical Characteristics


* Package: SOD-323
* Lead Finish: Matte Tin
* Case Material: “Green” Molding Compound.
* UL Flammability Classification Rating 94V-0
* Moisture Sensitivity: Level 3 per J-STD-020
* Terminal Connections: See Diagram Below
* Shipping Qty :3000 /7Inch Tape & Reel

Applications

* Cellular Handsets and Accessories
* Personal Digital Assistants
* Notebooks and Handhelds
* Portable Instrumentation
* Peripherals
* Pagers Peripherals
* Desktop and Servers

Dimensions and Pin Configuration

SOD-323



Absolute Maximum Ratings (Tamb=25°C unless otherwise specified)

Parameter	Symbol	Value	Unit
Peak Pulse Power (8/20μs)	Ppk	350	W
Peak Pulse Current (8/20μs)	I_{PP}	5	A
ESD per IEC 61000−4−2 (Air) ESD per IEC 61000−4−2 (Contact)	V_{ESD}	±30 ±30	kV
Operating Temperature Range	T_J	−55 to +125	°C
Storage Temperature Range	Tstg	−55 to +150	°C

Electrical Characteristics (TA=25°C unless otherwise specified)

Parameter	Symbol	Min	Typ	Max	Unit	Test Condition
Reverse Working Voltage	V_{RWM}			36	V	
Breakdown Voltage	V_{BR}	40			V	I_T = 1mA
Reverse Leakage Current	I_R			0.5	μA	V_{RWM} = 36V
Forward Voltage	V_F		0.8	1.2	V	I_F=10mA
Clamping Voltage	V_C			9	V	I_{PP} = 1A (8 x 20μs pulse)
Clamping Voltage	V_C		50	60	V	I_{PP} = 5A (8 x 20μs pulse)
Junction Capacitance	C_J			50	pF	VR = 0V, f = 1MHz

Typical Performance Characteristics (T_A=25℃ unless otherwise Specified)

Fig1. 8/20μs Pulse Waveform




Fig2. ESD Pulse Waveform (according to IEC 61000-4-2)






Fig3. Power Derating Curve




Outline Drawing - SOD-323



SYM	DIMENSIONS			
	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	1.50	1.80	0.060	0.071
B	1.20	1.40	0.045	0.054
C	2.30	2.70	0.090	0.107
D	-	1.10	-	0.043
E	0.30	0.40	0.012	0.016
F	0.10	0.25	0.004	0.010
H	-	0.10	-	0.004

Land Pattern - SOD-323



SYM	DIMENSIONS	
	MILLIMETERS	INCHES
A	3.15	0.120
B	0.80	0.031
C	0.80	0.031