
N-Channel MOSFET

$V_{(BR)DSS}$	$R_{DS(on)}$Typ	I_D
60 V	1.5Ω@10V	340mA
	2Ω@4.5V	




FEATURE

- High density cell design for low $R_{DS(ON)}$
- Voltage controlled small signal switch
- Rugged and reliable
- High saturation current capability


APPLICATION

- Load Switch for Portable Devices
- DC/DC Converter

MARKING




Equivalent Circuit



(Top View)

SOT-523



1. GATE
2. SOURCE
3. DRAIN

MOSFET MAXIMUM RATINGS (T_a=25℃ unless otherwise noted)

Symbol	Parameter	Value	Unit
V_{DS}	Drain-Source Voltage	60	V
V_{GS}	Gate-Source Voltage	±20	V
I_D	Continuous Drain Current	340	mA
I_{DM}	Pulsed Drain Current(note1)	800	mA
P_D	Power Dissipation	0.2	W
T_J,T_{stg}	Operation Junction and Storage Temperature Range	-55~+150	℃
$R_{\theta JA}$	Thermal Resistance from Junction to Ambient	625	℃/W

WPMtek

MOSFET ELECTRICAL CHARACTERISTICS

T_a=25℃ unless otherwise specified

Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
STATIC PARAMETERS						
Drain-source Breakdown Voltage	$V_{(BR)DSS}$	V_{GS} = 0V, I_D =250μA	60			V
GateThreshold Voltage (note 2)	$V_{GS(th)}$	V_{DS} =V_{GS}, I_D =1mA	1	1.5	2.5	V
Zero Gate Voltage Drain Current	I_{DSS}	V_{DS} =48V,V_{GS} = 0V			1	μA
Gate-Source Leakage Current	I_{GSS}	V_{GS} =±20V, V_{DS} = 0V			±10	μA
Drain-Source On-Resistance (note 2)	$R_{DS(on)}$	V_{GS} =4.5V, I_D =200mA		2	3	Ω
		V_{GS} =10V, I_D =500mA		1.5	2.5	Ω
DYNAMIC PARAMETERS (note 3)						
Input Capacitance	C_{iss}	V_{DS} =10V,V_{GS} =0V,f =1MHz			40	pF
Output Capacitance	C_{oss}				30	pF
Reverse Transfer Capacitance	C_{rss}				10	pF
SWITCHING PARAMETERS(note 3)						
Turn-on Delay Time	$t_{d(on)}$	V_{GS}=10V,V_{DD}=50V, R_G=50Ω			10	ns
Turn-off Delay Time	$t_{d(off)}$	R_{GS}=50Ω, R_L=250Ω			15	ns
Reverse Recovery Time	t_{rr}	V_{GS}=0V,I_S=300mA,V_R=25V, dIs/dt=-100A/us		30		ns
Recovered Charge	Qr	V_{GS}=0V,I_S=300mA,V_R=25V dIs/dt=-100A/us		30		nC
GATE-SOURCE ZENER DIODE						
Gate-Source Breakdown Voltage	BV_{GSO}	Igs=±1mA(Open Drain)	±21.5		±30	V
DRAIN-SOURCE DIODE						
Diode Forward Voltage(note 2)	V_{SD}	I_S=300mA, V_{GS} = 0V			1.5	V
Continuous Diode Forward Current	I_S				0.2	A
Pulsed Diode Forward Current(note1)	I_{SM}				0.53	A


Notes :

1. Repetitive rating：Pluse width limited by junction temperature.
2. Pulse Test : Pulse width≤300μs, duty cycle≤2%.
3. Guaranteed by design, not subject to production testing.


WPMtek

Typical Characteristics


Output Characteristics




Transfer Characteristics




$R_{DS(ON)}$ — I_D




$R_{DS(ON)}$ — V_{GS}



I_S — V_{SD}




Threshold Voltage



WPMtek


SOT-523 Package Outline



DIM	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	0.70	0.90	0.028	0.035
A1	0.00	0.10	0.000	0.004
A2	0.70	0.80	0.028	0.031
b1	0.15	0.25	0.006	0.010
b2	0.25	0.35	0.010	0.014
c	0.10	0.20	0.004	0.008
D	1.50	1.70	0.059	0.067
E	0.70	0.90	0.028	0.035
E1	1.45	1.75	0.057	0.069
e	0.50 TYP.		0.020 TYP.	
e1	0.90	1.10	0.035	0.043
L	0.40 REF.		0.016 REF.	
L1	0.10	0.30	0.004	0.012
θ	0^{o}	8^{o}	0^{o}	8^{o}

NOTES:
1. Above package outline conforms to JEITA EAIJ ED-7500A SC-75A.
2. Dimensions are exclusive of Burrs, Mold Flash & Tie Bar extrusions.

Typical Soldering Pattern:



WPMtek reserves the right to make changes to the product specification and data in this document without notice. WPMtek makes no warranty, representation or guarantee regarding the suitability of its products for any particu lar purpose, nor does WPMtek assume any liability arising from the application or use of any products or circuits, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Any enquiry ,please write to sales@wpmtek.com for futher information.

WPMtek