SPTECH Silicon NPN Power Transistor

DESCRIPTION


- DC Current Gain -h_{FE} =30(Min)@ I_C= 0.3A
- Collector-Emitter Sustaining Voltage-
  : $V_{CEO(SUS)}$ = 45V(Min)- BD243; 60V(Min)- BD243A
  80V(Min)- BD243B; 100V(Min)- BD243C
- Complement to Type BD244/A/B/C

APPLICATIONS

- Designed for use in general purpose power amplifier and switching applications




1 2 3



PIN 1. BASE
2.COLLECTOR
3. EMITTER
TO-220C package

ABSOLUTE MAXIMUM RATINGS(T_a=25℃)

SYMBOL	PARAMETER		VALUE	UNIT
V_{CBO}	Collector-Base Voltage	BD243	55	V
		BD243A	70	
		BD243B	90	
		BD243C	110	
V_{CEO}	Collector-Emitter Voltage	BD243	45	V
		BD243A	60	
		BD243B	80	
		BD243C	100	
V_{EBO}	Emitter-Base Voltage		5	V
I_C	Collector Current-Continuous		6	A
I_{CM}	Collector Current-Peak		10	A
I_B	Base Current		3	A
P_C	Collector Power Dissipation @ T_C=25℃		65	W
T_J	Junction Temperature		150	℃
T_{stg}	Storage Temperature Range		-65~150	℃



DIM	mm MIN	MAX
A	15.50	15.90
B	9.90	10.20
C	4.20	4.50
D	0.70	0.90
F	3.40	3.70
G	4.98	5.18
H	2.68	2.90
J	0.44	0.60
K	13.00	13.40
L	1.20	1.45
Q	2.70	2.90
R	2.30	2.70
S	1.29	1.35
U	6.45	6.65
V	8.66	8.86

THERMAL CHARACTERISTICS

SYMBOL	PARAMETER	MAX	UNIT
$R_{th\ j\text{-}c}$	Thermal Resistance, Junction to Case	1.92	℃/W

SPTECH Silicon NPN Power Transistor

ELECTRICAL CHARACTERISTICS

T_C=25℃ unless otherwise specified

SYMBOL	PARAMETER		CONDITIONS	MIN	MAX	UNIT
$V_{CEO(SUS)}$	Collector-Emitter Sustaining Voltage	BD243	I_C= 30mA ;I_B=0	45		V
		BD243A		60		
		BD243B		80		
		BD243C		100		
$V_{CE(sat)}$	Collector-Emitter Saturation Voltage		I_C= 6A; I_B= 1A		1.5	V
$V_{BE(on)}$	Base-Emitter On Voltage		I_C= 6A ; V_{CE}= 4V		2.0	V
I_{CBO}	Collector Cutoff Current	BD243	V_{CB}= 55V; V_{BE}= 0		0.4	mA
		BD243A	V_{CB}= 70V; V_{BE}= 0			
		BD243B	V_{CB}= 90V; V_{BE}= 0			
		BD243C	V_{CB}= 110V; V_{BE}= 0			
I_{CEO}	Collector Cutoff Current	BD243/A	V_{CE}= 30V;I_B= 0		0.7	mA
		BD243B/C	V_{CE}= 60V;I_B= 0			
I_{EBO}	Emitter Cutoff Current		V_{EB}= 5V; I_C=0		1.0	mA
h_{FE-1}	DC Current Gain		I_C= 0.3A ; V_{CE}= 4V	30		
h_{FE-2}	DC Current Gain		I_C= 3A ; V_{CE}= 4V	15		
f_T	Current-Gain—Bandwidth Product		I_C= 0.5A ; V_{CE}= 10V, f_{test}= 1.0MHz	3.0		MHz