
$V_{(BR)DSS}$	$R_{DS(on)}$MAX	I_D
60 V	3Ω@10V	300mA
	4Ω@4.5V	

SOT-363



FEATURE

- High density cell design for Low $R_{DS(on)}$
- Voltage controlled small signal switch
- Rugged and reliable
- High saturation current capability
- ESD protected


APPLICATION

- Load Switch for Portable Devices
- DC/DC Converter

Order Information

Product	Marking	Package	Packing
2N7002KDW	72K	SOT-363	3000PCS/Reel

Equivalent Circuit



MOSFET MAXIMUM RATINGS (T_a = 25℃ unless otherwise noted)

Symbol	Parameter	Value	Unit
V_{DS}	Drain-Source voltage	60	V
V_{GS}	Gate-Source voltage	±20	V
I_D	Drain Current	300	mA
P_D	Power Dissipation	0.15	W
T_J	Junction Temperature	150	℃
T_{stg}	Storage Temperature	-55-150	℃
$R_{\theta JA}$	Thermal Resistance fromJunction to Ambient	833	℃ /W

T_a=25℃ unless otherwise specified


Parameter	Symbol	Test Condition	Min	Typ	Max	Units
Static Characteristics						
Drain-Source Breakdown Voltage	V_{DS}	V_{GS} = 0V, I_D =250μA	60			V
Gate Threshold Voltage*	$V_{GS(th)}$	V_{DS} =V_{GS}, I_D =250uA	0.7	1.3	2.5	V
Zero Gate Voltage Drain Current	I_{DSS}	V_{DS} =48V,V_{GS} = 0V			1	μA
Gate –Source leakage current	I_{GSS1}	V_{GS} =±20V, V_{DS} = 0V			±10	μA
Drain-Source On-Resistance*	$R_{DS(on)}$	V_{GS} = 4.5V, I_D =200mA		1.3	4	Ω
		V_{GS} =10V,I_D =500mA		1	3	Ω
Diode Forward Voltage	V_{SD}	V_{GS}=0V, I_S=300mA			1.5	V
Recovered charge	Q_r	V_{GS}=0V,I_S=300mA,V_R=25V, dI_S/dt=-100A/μs		30		nC
Dynamic Characteristics**						
Input Capacitance	C_{iss}	V_{DS} =10V,V_{GS} =0V,f =1MHz			40	pF
Output Capacitance	C_{oss}				30	pF
Reverse Transfer Capacitance	C_{rss}				10	pF
Switching Characteristics**						
Turn-On Delay Time	$t_{d(on)}$	V_{GS}=10V,V_{DD}=50V,R_G=50Ω, R_{GS}=50Ω, R_L=250Ω			10	ns
Turn-Off Delay Time	$t_{d(off)}$				15	ns
Reverse recovery Time	t_{rr}	V_{GS}=0V,I_S=300mA,V_R=25V, dI_S/dt=-100A/μs		30		ns
GATE-SOURCE ZENER DIODE						
Gate-Source Breakdown Voltage	BV_{GSO}	I_{gs}=±1mA (Open Drain)	±21.5		±30	V

Notes :
*Pulse Test : Pulse Width ≤300μs, Duty Cycle ≤2%.


WPMtek

Typical Characteristics


Output Characteristics




Transfer Characteristics




$R_{DS(ON)}$ —— I_D




$R_{DS(ON)}$ —— V_{GS}



I_S —— V_{SD}




Threshold Voltage




WPMtek


SOT-363 Package Outline Dimensions




TOP VIEW



SIDE VIEW



SIDE VIEW



DETAIL E

COMMON DIMENSIONS (UNITS OF MEASURE IS mm)			
	MIN	NORMAL	MAX
A	2.000	2.100	2.200
B	1.150	1.250	1.350
C	0.900	0.950	1.000
C1	0.500	0.550	0.600
D	2.100	2.300	2.500
L	0.220	0.360	0.500
b	0.200	0.250	0.400
h	0.020	0.050	0.100
e	0.650 TYPE		
θ_1	8° TYPE		
θ_2	8° TYPE		
θ_3	8° TYPE		
θ_4	8° TYPE		
θ	0~8° TYPE		

WPMtek reserves the right to make changes to the product specification and data in this document without notice. WPMtek makes no warranty, representation or guarantee regarding the suitability of its products for any particu lar purpose, nor does WPMtek assume any liability arising from the application or use of any products or circuits, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Any enquiry ,please write to sales@wpmtek.com for futher information.