
Schottky Barrier Diode

PINNING

PIN	DESCRIPTION
1	Cathode
2	Anode



Top View
Marking Code: "**SH**"
Simplified outline SOD-323 and symbol

FEATURES

- Guard ring protection
- Low forward voltage drop
- For use in low voltage, high frequency inverters
- High surge current capability

Marking: SH

MAXIMUM RATINGS(Ta=25℃ unless otherwise noted)

Symbol	Parameter	Value	Unit
V_{RRM}	Maximum recurrent peak reverse voltage	60	V
V_{RMS}	Maximum RMS voltage	42	
V_{DC}	Maximum DC blocking voltage	60	
I_F	Continuous forward current	1	A
I_{FSM}	Non-repetitive Peak forward surge current@t=8.3ms	10	
P_{tot}	Total power disspation	250	mW
$R_{\theta JA}$	Thermal resistance junction to ambient air	400	℃/W
T_J	Junction temperature	125	℃
T_{stg}	storage temperature	-55~+150	℃


ELECTRICAL CHARACTERISTICS(Ta=25℃ unless otherwise specified)

Parameter	Symbol	Test conditions	Min	Typ	Max	Unit
Maximum instantaneous forward voltage	V_F	I_F=1A			0.7	V
Maximum DC reverse current at rated DC blocking voltage	I_R	V_R=60V			0.1	mA
Total capacitance	C_{tot}	V_R=4V,f=1MHz			120	pF


WPMtek

Typical Characteristics


Forward Characteristics




Reverse Characteristics



Capacitance Characteristics




Power Derating Curve



WPMtek

PACKAGE OUTLINE

Plastic surface mounted package; 2 leads **SOD-323**



UNIT	A	b_p	C	D	E	H_E	A_1	L_p
mm	1.20 0.90	0.40 0.25	0.15 0.10	1.80 1.60	1.35 1.15	2.80 2.30	0.10 0.01	0.50 0.20

WPMtek reserves the right to make changes to the product specification and data in this document without notice. WPMtek makes no warranty, representation or guarantee regarding the suitability of its products for any particu lar purpose, nor does WPMtek assume any liability arising from the application or use of any products or circuits, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Any enquiry ,please write to sales@wpmtek.com for futher information.