
SPTECH Silicon NPN Power Transistor

DESCRIPTION

- High Collector-Emitter Sustaining Voltage-
  : $V_{CEO(SUS)}$= 400V (Min)
- High Switching Speed

APPLICATIONS

- Power switching
- Power amplification
- Power driver




ABSOLUTE MAXIMUM RATINGS(T_a=25℃)

SYMBOL	PARAMETER	MAX	UNIT
V_{CBO}	Collector-Base Voltage	450	V
V_{CEO}	Collector-Emitter Voltage	400	V
V_{EBO}	Emitter-Base Voltage	5	V
I_C	Collector Current-Continuous	15	A
I_{CM}	Collector Current-Peak	30	A
I_B	Base Current-Continuous	6	A
P_C	Collector Power Dissipation @T_C=25℃	100	W
T_j	Junction Temperature	200	℃
T_{stg}	Storage Temperature Range	-65~200	℃

THERMAL CHARACTERISTICS

SYMBOL	PARAMETER	MAX	UNIT
$R_{th\ j\text{-}c}$	Thermal Resistance,Junction to Case	1.0	℃/W



DIM	mm MIN	MAX
A	39.00	41.00
B	25.30	26.00
C	9.50	11.00
D	0.90	1.10
E	2.50	3.50
G	10.92	
H	5.46	
K	11.50	12.00
L	16.75	17.05
N	19.40	19.62
Q	4.00	4.20
U	30.00	30.40
V	4.30	4.50

SPTECH Silicon NPN Power Transistor

ELECTRICAL CHARACTERISTICS

T_C=25℃ unless otherwise specified

SYMBOL	PARAMETER	CONDITIONS	MIN	TYP.	MAX	UNIT
$V_{CEO(SUS)}$	Collector-Emitter Sustaining Voltage	I_C= 50mA; L= 25mH	400			V
$V_{CE(sat)}$	Collector-Emitter Saturation Voltage	I_C= 6A; I_B= 1.2A			1.2	V
$V_{BE(sat)}$	Base-Emitter Saturation Voltage	I_C= 6A; I_B= 1.2A			1.5	V
h_{FE}	DC Current Gain	I_C= 5A; V_{CE}= 2V	12		60	
h_{FE}	DC Current Gain	I_C= 10A; V_{CE}= 2V	6		30	
I_{CBO}	Collector Cutoff Current	V_{CB}= 450V; I_E= 0 T_C=125℃			1.0 4.0	mA
I_{CEO}	Collector Cutoff Current	V_{CE}= 400V; I_B= 0			5.0	mA
I_{EBO}	Emitter Cutoff Current	V_{EB}= 5V; I_C= 0			1.0	mA

Switching Times

t_r	Rise Time	I_C= 6A; I_{B1}=- I_{B2}= 1.2A			1.0	μs
t_{stg}	Storage Time				2.0	μs
t_f	Fall Time				1.0	μs