
SPTECH Silicon PNP Power Transistor



DESCRIPTION


- High Current Capability
- High Power Dissipation
- High Collector-Emitter Breakdown Voltage-
  : $V_{(BR)CEO}$= -260V(Min)
- Complement to Type MN1526

APPLICATIONS

- Power amplifier applications
- Recommend for 150W high fidelity audio frequency amplifier output stage applications

ABSOLUTE MAXIMUM RATINGS(Ta=25℃)

SYMBOL	PARAMETER	VALUE	UNIT
V_{CBO}	Collector-Base Voltage	-260	V
V_{CEO}	Collector-Emitter Voltage	-260	V
V_{EBO}	Emitter-Base Voltage	-5	V
I_C	Collector Current-Continuous	-15	A
I_B	Base Current-Continuous	-4	A
P_C	Collector Power Dissipation @ T_C=25℃	150	W
T_J	Junction Temperature	150	℃
T_{stg}	Storage Temperature Range	-55~150	℃



DIM	mm MIN	MAX
A	19.60	20.30
B	15.50	15.70
C	4.70	4.90
D	0.90	1.10
E	1.90	2.10
F	3.40	3.60
G	2.90	3.20
H	3.20	3.40
J	0.595	0.605
K	19.80	20.70
L	1.90	2.20
N	10.89	10.91
Q	4.90	5.10
R	3.35	3.45
S	1.995	2.100
U	5.90	6.20
Y	9.90	10.10

SPTECH Silicon PNP Power Transistor

ELECTRICAL CHARACTERISTICS

T_C=25℃ unless otherwise specified

SYMBOL	PARAMETER	CONDITIONS	MIN	TYP.	MAX	UNIT
$V_{(BR)CEO}$	Collector-Emitter Breakdown Voltage	I_C= -50mA ; I_B= 0	-260			V
$V_{CE(sat)}$	Collector-Emitter Saturation Voltage	I_C=- 8.0A; I_B= -0.8A			-3.0	V
$V_{BE(on)}$	Base-Emitter On Voltage	I_C= -7A ; V_{CE}= -5V			-1.5	V
I_{CBO}	Collector Cutoff Current	V_{CB}= -260V ; I_E= 0			-5	μA
I_{EBO}	Emitter Cutoff Current	V_{EB}= -5V; I_C= 0			-5	μA
h_{FE-1}	DC Current Gain	I_C= -1A ; V_{CE}= -5V	40		140	
h_{FE-2}	DC Current Gain	I_C= -7A ; V_{CE}= -5V	35			
C_{OB}	Output Capacitance	I_E=0 ; V_{CB}= -10V;f= 1.0MHz		250		pF
f_T	Current-Gain—Bandwidth Product	I_C=-1A ; V_{CE}= -5V		60		MHz

◆ **h_{FE-1} Classifications**

R	O	P
40-80	50-100	70－140