

SOD-523 Plastic-Encapsulate ESD Protection Diodes


Features

- Low leakage current
- SOD-523 surface mount package
- IEC 61000-4-2 (ESD Air): ±25kV
- IEC 61000-4-2 (ESD Contact): ±20kV
- IEC 61000-4-5 (Lightning 8/20μs): 8A

Applications


- Cellular Handsets and Accessories
- Personal Digital Assistants
- Notebooks and Handhelds
- Portable Instrumentation, Digital Cameras
- Peripherals, Audio Players, Industrial Equipment

Function Diagram



Reverse Working Voltage
3.3V Max.
Low Capacitance
12.5pF(Typ.)

SOD-523




Maximum Ratings (Ta=25°C Unless otherwise specified)

SYMBOL	PARAMETER	CONDITIONS	VALUE	UNIT
VESD	Electrostatic Discharge Voltage	ESD per IEC 61000-4-2(Air)	±25	KV
		ESD per IEC 61000-4-2(Contact)	±20	KV
P _{PP}	Peak Pulse Power	tp = 8/20 μs	100	W
I _{PP}	Rated Peak Pulse Current	tp = 8/20 μs	8	A
T _J	Operating JunctionTemperature Range	—	-55 to +125	°C
T _{STG}	Storage Temperature Range	—	-55 to +150	°C

Electrical Parameter





SYMBOL	PARAMETER
V _C	Clamping Voltage @ I _{PP}
V _{BR}	Breakdown Voltage @ I _T
I _{PP}	Peak Pulse Current
I _T	Test Current
I _R	Reverse Leakage Current @ VRWM
V _{RWM}	Peak Reverse Working Voltage
P _{PP}	Peak Pulse Power Dissipation
C _J	Junction Capacitance @ V _R =0V,f=1MHz
I _F	Forward Current
V _F	Forward Voltage @I _F



● Electrical Characteristics (Ta=25°C Unless otherwise specified)

PARAMETER	SYMBOL	CONDITION	Min	Typ	Max	UNIT
Peak Reverse Working Voltage	V_{RWM}	$T_a=25^{\circ}\text{C}$	—	—	3.3	V
Breakdown Voltage	V_{BR}	$I_R=1\text{mA}, T_a=25^{\circ}\text{C}$	3.5	—	6.5	V
Reverse Leakage Current	I_R	$V_R=3.3\text{V}, T_a=25^{\circ}\text{C}$	—	—	0.2	μA
Clamping Voltage	V_C	$I_{PP}=1.0\text{A}, t_p=8/20\mu\text{s}$	—	—	6	V
		$I_{PP}=8\text{A}, t_p=8/20\mu\text{s}$	—	—	12	
Junction Capacitance	C_J	$V_R=0\text{V}, f=1\text{MHz}$	—	12.5	25	pF

● Ratings And Characteristics Curves (Ta=25°C Unless otherwise specified)




H3V3LD5B

Bi-directional 3.3V Low Capacitance ESD


Ordering Information

PREFERRED P/N	PACKAGE CODE	PACKAGE	SIZE(mm)	DELIVERY MODE	MPQ(PCS)
H3V3LD5B	R1	SOD-523	0.30×0.80×0.115	7"REEL	3000
	R1H	SOD-523	0.30×0.80×0.115	7"REEL	8000

Recommended Soldering Conditions



Package Outline Dimensions (SOD-523)



Suggested Pad Layout

