KUU4884A

Dual N-Channel MOSFET

Datasheet

Features


- Trench Power LV MOSFET technology
- High Density Cell Design for Low $R_{DS(ON)}$
- High Speed switching

Product Summary


V_{DS}	$R_{DS(ON)}$ TYP	I_D
40V	13mΩ@10V	10A
	19mΩ@4.5V	

Application


- Battery protection
- Load switch
- Power management



SOP-8 top view



Schematic diagram



4884A: Device code
XXXX: Code

Marking and pin assignment

Absolute Maximum Ratings (TA=25℃unless otherwise noted)				
Symbol	**Parameter**		**Rating**	**Unit**
Common Ratings (TC=25°C Unless Otherwise Noted)				
V_{DS}	Drain-Source Breakdown Voltage		40	V
V_{GS}	Gate-Source Voltage		±20	V
T_J	Maximum Junction Temperature		150	°C
T_{STG}	Storage Temperature Range		-55 to 150	°C
I_S	Diode Continuous Forward Current	Tc=25°C	10	A
Mounted on Large Heat Sink				
I_{DM}	Pulse Drain Current Tested	Tc=25°C	50	A
I_D	Continuous Drain Current	Tc=25°C	10	A
P_D	Maximum Power Dissipation	Tc=25°C	2	W
$R_{\theta JA}$	Thermal Resistance Junction-Ambient		60	°C/W

Electrical Characteristics (TJ=25℃ unless otherwise noted)						
Symbol	**Parameter**	**Condition**	**Min**	**Typ**	**Max**	**Unit**
Static Electrical Characteristics @ TJ = 25°C (unless otherwise stated)						
$BV_{(BR)DSS}$	Drain-Source Breakdown Voltage	V_{GS}=0V，I_D=250μA	40	--	--	V
I_{DSS}	Zero Gate Voltage Drain Current	V_{DS}=40V，V_{GS}=0V	--	--	1	μA
I_{GSS}	Gate-Body Leakage Current	V_{GS}=±20V，V_{DS}=0V	--	--	±100	nA
$V_{GS(th)}$	Gate Threshold Voltage	V_{DS}=V_{GS}，I_D=250μA	1.0	1.5	2.5	V
$R_{DS(on)}$	Drain-Source On-State Resistance	V_{GS}=10V， I_D=10A	--	13	17	mΩ
		V_{GS}=4.5V，I_D=10A	--	19	25	mΩ
Dynamic Electrical Characteristics @ TJ = 25°C (unless otherwise stated)						
C_{ISS}	Input Capacitance	V_{DS}=20V，V_{GS}=0V， f=1MHz	--	965	--	pF
C_{OSS}	Output Capacitance		--	110	--	pF
C_{RSS}	Reverse Transfer Capacitance		--	95	--	pF
Switching Characteristics						
Q_g	Total Gate Charge	V_{DS}=20V，I_D=10A，V_{GS}=10V	--	23	--	nC
Q_{gs}	Gate Source Charge		--	3.5	--	nC
Q_{gd}	Gate Drain Charge		--	5.5	--	nC
$t_{d(on)}$	Turn-on Delay Time	V_{DS}=20V，R_L=2.5Ω，V_{GS}=10V，R_G=3Ω	--	5.5	--	nS
t_r	Turn-on Rise Time		--	15	--	nS
$t_{d(off)}$	Turn-Off Delay Time		--	25	--	nS
t_f	Turn-Off Fall Time		--	12	--	nS
Source- Drain Diode Characteristics						
V_{SD}	Forward on voltage	Tj=25℃，Is=10A	--	--	1.2	V

Typical Operating Characteristics




Fig1. Typical Output Characteristics




Fig2. Typical Gate Charge Vs.Gate-Source Voltage




Fig3. Normalized On-Resistance Vs. Temperature




Fig4. On-Resistance Vs. Drain-Source Current




Fig5. Maximum Safe Operating Area





Fig6 Typical Capacitance Vs.Drain-Source Voltage

SOP-8 Package information



Symbol	Dimensions in Millimeters(mm)		Dimensions In Inches	
	Min	Max	Min	Max
A	1.450	1.750	0.057	0.068
A1	0.100	0.250	0.003	0.009
A2	1.350	1.550	0.053	0.061
b	0.330	0.510	0.012	0.020
c	0.170	0.250	0.006	0.009
D	4.700	5.100	0.185	0.200
e	1.270(BSC)		0.050(BSC)	
E	3.800	4.000	0.149	0.157
E1	5.800	6.200	0.228	0.244
L	0.400	1.270	0.015	0.050
θ	0°	8°	0°	8°