
P-Channel 20-V(D-S) MOSFET

$V_{(BR)DSS}$	$R_{DS(on)}$ Typ	I_D
-20V	0.090Ω@-4.5V	-2.3A
	0.120Ω@-2.5V	

SOT-23



1.GATE
2.SOURCE
3.DRAIN


General FEATURE

- ●TrenchFET Power MOSFET
- ●Lead free product is acquired
- ●Surface mount package

APPLICATION


- ●Load Switch for Portable Devices
- ●DC/DC Converter

MARKING



*w： week code

Equivalent Circuit



Maximum ratings (T_a=25℃ unless otherwise noted)

Parameter	Symbol	Value	Unit
Drain-Source Voltage	V_{DS}	-20	V
Gate-Source Voltage	V_{GS}	±12	
Continuous Drain Current	I_D	-2. 3	A
Pulsed Drain Current	I_{DM}	-10	
Continuous Source-Drain Diode Current	I_S	-1.30	
Maximum Power Dissipation	P_D	1.0	W
Thermal Resistance from Junction to Ambient(t ≤5s)	$R_{\theta JA}$	178	℃/W
Junction Temperature	T_J	150	℃
Storage Temperature	T_{stg}	-55 ~+150	

MOSFET ELECTRICAL CHARACTERISTICS

T_a =25 ℃ unless otherwise specified

Parameter	Symbol	Test Condition	Min	Typ	Max	Units
Static						
Drain-source breakdown voltage	$V_{(BR)DSS}$	V_{GS} = 0V, I_D =-250μA	-20			V
Gate-source threshold voltage	$V_{GS(th)}$	V_{DS} =V_{GS}, I_D =-250μA	-0.5	-0.7	-1	
Gate-source leakage	I_{GSS}	V_{DS} =0V, V_{GS} =±10 V			±100	nA
Zero gate voltage drain current	I_{DSS}	V_{DS} =-20V, V_{GS} =0V			-1	μA
Drain-source on-state resistance [a]	$R_{DS(on)}$	V_{GS} =-4.5V, I_D =-2.3A		0.090	0.110	Ω
		V_{GS} =-2.5V, I_D =-1.8A		0.120	0.150	
Forward transconductance [a]	g_{fs}	V_{DS} =-5V, I_D =-2.0A	4.0	6.5		S
Dynamic[b]						
Input capacitance	C_{iss}	V_{DS} =-10V,V_{GS} =0V,f =1MHz		185		pF
Output capacitance	C_{oss}			35		
Reverse transfer capacitance	C_{rss}			25		
Total gate charge	Q_g	V_{DS} =-10V,V_{GS} =-4.5V,I_D =-3A		5.5	10	nC
		V_{DS} =-10V,V_{GS} =-2.5V,I_D =-2A		2.9	6	
Gate-source charge	Q_{gs}			045		
Gate-drain charge	Q_{gd}			0.75		
Gate resistance	R_g	f =1MHz		6.0		Ω
Turn-on delay time	$t_{d(on)}$	V_{DD}=-10V, R_L=5Ω, I_D =-1A, V_{GEN}=-4.5V,Rg=3Ω		9.8	20	ns
Rise time	t_r			4.9	60	
Turn-off delay time	$t_{d(off)}$			20.5	50	
Fall time	t_f			7.0	20	
Drain-source body diode characteristics						
Continuous source-drain diode current	I_S	T_C=25℃			-1.3	A
Pulse diode forward current [a]	I_{SM}				-10	
Body diode voltage	V_{SD}	I_S=-1.0A		-0.8	-1.2	V

Notes :

a.Pulse Test : Pulse Width < 300μs, Duty Cycle ≤2%.

b.Guaranteed by design, not subject to production testing.

Typical Electrical and Thermal Characteristics




Figure 1:Switching Test Circuit




Figure 2:Switching Waveforms




Figure 3 Power Dissipation




Figure 4 Drain Current




Figure 5 Output Characteristics




Figure 6 Drain-Source On-Resistance




Figure 7 Transfer Characteristics




Figure 8 Drain-Source On-Resistance




Figure 9 Rdson vs Vgs




Figure 10 Capacitance vs Vds




Figure 11 Gate Charge




Figure 12 Source- Drain Diode Forward




Figure 13 Safe Operation Area






Figure 14 Normalized Maximum Transient Thermal Impedance

SOT-23 Package Outline Dimensions



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	0.900	1.150	0.035	0.045
A1	0.000	0.100	0.000	0.004
A2	0.900	1.050	0.035	0.041
b	0.300	0.500	0.012	0.020
c	0.080	0.150	0.003	0.006
D	2.800	3.000	0.110	0.118
E	1.200	1.400	0.047	0.055
E1	2.250	2.550	0.089	0.100
e	0.950 TYP		0.037 TYP	
e1	1.800	2.000	0.071	0.079
L	0.550 REF		0.022 REF	
L1	0.300	0.500	0.012	0.020
θ	0°	8°	0°	8°

SOT-23 Suggested Pad Layout



Note:
1.Controlling dimension:in millimeters.
2.General tolerance:±0.05mm.
3.The pad layout is for reference purposes only.