FUXINSEMI
INNOVATOR IN SEMICONDUCTOR

P4FL3.3A / P4FL3.3CA

400W Surface Mount Unidirectional and Bidirectional Transient Voltage Suppressors Diodes- 3.3V

Features

- For surface mounted applications in order to optimize board space.
- Low profile package.
- Excellent clamping capability.
- IEC61000-4-2 ESD 30kV Air,30kV contact compliance
- Protects one I/O line
- Lead-free parts meet RoHS requirments.
- Compliant to Halogen-free

Applications


- Personal digital assistants (PDA)
- Cellular handsets & Accessories
- Portable devices
- Portable instrumentation
- Handhelds and notebooks
- Digital cameras

Mechanical data

- Epoxy : UL94-V0 rated flame retardant
- Case : Molded plastic, SOD-123FL
- Terminals :Plated terminals, solderable per MIL-STD-750, Method 2026
- Polarity : Indicated by cathode band
- Mounting Position : Any

Package outline

SOD-123FL



Dimensions in inches and (millimeters)

Maximum ratings and Electrical Characteristics (AT T_A=25°C unless otherwise noted)

PARAMETER	CONDITIONS	Symbol	Value	UNIT
Peak Power Dissipation	Peak Pulse Power Dissipation at TA=25°C by 10x1000us (Note 1)	P_{PPM}	400	W
Operating junction temperature range		T_J	-55 to +150	°C
Storage temperature range		T_{STG}	-55 to +150	°C

Note: 1. Non-repetitive current pulse, per Fig. 2 and derated above TA=25°C per Fig. 1

Electrical Characteristics (T_A = 25°C)

Part Number (Uni)	Part Number (Bi)	Device Marking Code		Breakdown Voltage V_{BR} @I_T			Maximum Reverse Leakage I_R @V_{RWM} (uA)	Working Peak Reverse Voltage V_{RWM} (V)	Maximum Reverse Surge Current I_{PP} (A)	Maximum Clamping Voltage V_C @I_{PP} (V)
		Uni	Bi	Min (V)	Max (V)	I_T (mA)				
P4FL3.3A	P4FL3.3CA	A1	CA1	5.40	6.00	10	500	3.3	47.0	8.50

Rating and characteristic curves

FIG.1 - PULSE DERATING CURVE




FIG.2 - 10X1000us PULSE WAVEFORM




FIG.3 - 8X20us PULSE WAVEFORM




FIG.4 - PEALK PULSE POWER RATING CURVE





FIG.5 - TYPICAL JUNCTION CAPACITANCE




P4FL3.3A / P4FL3.3CA

400W Surface Mount Unidirectional and Bidirectional Transient Voltage Suppressors Diodes-3.3V

Pinning information

Pin	Simplified outline	Symbol
Uni-Directional Pin1 cathode Pin2 anode		
Bi-Directional		

Suggested solder pad layout




Dimensions in inches and (millimeters)

PACKAGE	A	B	C
SOD-123FL	0.044 (1.10)	0.040 (1.00)	0.079 (2.00)

Suggested thermal profiles for soldering processes

1.Storage environment: Temperature=5°C~40°C Humidity=55%±25%
2.Reflow soldering of surface-mount devices



3.Reflow soldering

Profile Feature	Soldering Condition
Average ramp-up rate(T_L to T_P)	<3°C/sec
Preheat -Temperature Min(Tsmin) -Temperature Max(Tsmax) -Time(min to max)(t_s)	 150°C 200°C 60~120sec
Tsmax to T_L -Ramp-upRate	 <3°C/sec
Time maintained above: -Temperature(T_L) -Time(t_L)	 217°C 60~260sec
Peak Temperature(T_P)	255°C-0/+5°C
Time within 5°C of actual Peak Temperature(t_P)	10~30sec
Ramp-down Rate	<6°C/sec
Time 25°C to Peak Temperature	<6minutes