


Rohs 2.0 Compliant | Pb Lead-free | HF


REV.	ECN NUMBER	DESCRIPTION	DAET	DRAWN	CHECKED	APPROVED
A	/	NEW	2023.01.04	QIANG	GONG	LEO






RECOMMENDED FPC







Detail A
Scale 4:1

Note:
1. Material:
1.1 Housing: thermoplastic high temp.UL94V-0;
1.2 Latch: thermoplastic high temp.UL94V-0;
1.3 Terminal: copper alloy.
1.4 Fitting Nail: copper alloy.
2. Finsh:
2.1 Terminal:
50~100u" Nickel under plating over all
Gold flash on contact and solder area.
2.2 Fitting Nail:
50~100u" Nickel under plating over all
80~150u" Matte tin over all
3. Product must comply RoHS specification.






PART NO.
FC0033RXXA
└ Pin No
04=4Pin
10=10Pin
.....



Detail B
Scale 4:1



RECOMMENDED PCB MOUNTING PATTERN

CKTS	DIM A	DIM B	DIM C	DIM D	DIM E	DIM F
9	4.30	1.80	2.40	3.03	3.73	3.00
11	4.90	2.40	3.00	3.63	4.33	3.60
13	5.50	3.00	3.60	4.23	4.93	4.20
15	6.10	3.60	4.20	4.83	5.53	4.80
17	6.70	4.20	4.80	5.43	6.13	5.40
19	7.30	4.80	5.40	6.03	6.73	6.00
21	7.90	5.40	6.00	6.63	7.33	6.60
23	8.50	6.00	6.60	7.23	7.93	7.20
25	9.10	6.60	7.20	7.83	8.53	7.80
27	9.70	7.20	7.80	8.43	9.13	8.40
29	10.30	7.80	8.40	9.03	9.73	9.00
31	10.90	8.40	9.00	9.63	10.33	9.60
33	11.50	9.00	9.60	10.23	10.93	10.20
35	12.10	9.60	10.20	10.83	11.53	10.80
37	12.70	10.20	10.80	11.43	12.13	11.40
39	13.30	10.80	11.40	12.03	12.73	12.00
41	13.90	11.40	12.00	12.63	13.33	12.60
43	14.50	12.00	12.60	13.23	13.93	13.20
45	15.10	12.60	13.20	13.83	14.53	13.80
47	15.70	13.20	13.80	14.43	15.13	14.40
49	16.30	13.80	14.40	15.03	15.73	15.00
51	16.90	14.40	15.00	15.63	16.33	15.60
53	17.50	15.00	15.60	16.23	16.93	16.20
55	18.10	15.60	16.20	16.83	17.53	16.80
57	18.70	16.20	16.80	17.43	18.13	17.40
59	19.30	16.80	17.40	18.03	18.73	18.00
61	19.90	17.40	18.00	18.63	19.33	18.60
63	20.50	18.00	18.60	19.23	19.93	19.20
65	21.10	18.60	19.20	19.83	20.53	19.80
67	21.70	19.20	19.80	20.43	21.13	20.40
69	22.30	19.80	20.40	21.03	21.73	21.00
71	22.90	20.40	21.00	21.63	22.33	21.60

NO.	PART NAME	DESCRIPTION , REMARKS	NO.	PART NAME	DESCRIPTION , REMARKS


GENERAL	TOLERANCE	UNITS: mm	SCALE 1 : 1
X. ± 0.30	X.° ± 5°	APRROVED	LEO
.X ± 0.20	.X° ± 3°	CHECKED	GONG
.XX ± 0.15	.XX° ± 2°	DESIGNED	Qiang

CPT 元精技术


TITLE: 0.3Pitch H=0.9 FPC/FFC Back-Flip RA Tpel SMT CONN
DRAWING NO. : C-FC0033R-01 A
PART NO. : SEE PART No
1/2

Rohs 2.0 Compliant	Pb Lead-free	HF


REV.	ECN NUMBER	DESCRIPTION	DAET	DRAWN	CHECKED	APPROVED
A	/	NEW	2023.01.04	QIANG	GONG	LEO



49~61PIN REEL




9~47PIN REEL



CKTS	B0	B1	W	W1	F	S
9	4.50	2.40	16.00	16.40	7.50	单边孔
11	5.10	3.00				
13	5.70	3.60				
15	6.30	4.20				
17	6.90	4.80				
19	7.50	5.40				
21	8.10	6.00	24.00	24.40	11.50	
23	8.70	6.60				
25	9.30	7.20				
27	9.90	7.80				
29	10.50	8.40				
31	11.10	9.00				
33	11.70	9.60				
35	12.30	10.20				
37	12.90	10.80				
39	13.50	11.40				
41	14.10	12.00				
43	14.70	12.60				
45	15.30	13.20				
47	15.90	13.80				
49	16.50	14.40	32.00	32.40	14.20	28.40
51	17.10	15.00				
53	17.70	15.60				
55	18.30	16.20				
57	18.90	16.80				
59	19.50	17.40				
61	20.10	18.00				
63	20.70	18.60				
65	21.30	19.20				
67	21.90	19.80				
69	22.50	20.40	44.00	44.40	20.20	40.40
71	23.10	21.00				

DIRECTION OF UNREELING



TRAILER TAPING(FREE) LEADER

GENERAL	TOLERANCE	UNITS: mm	SCALE 1 : 1
X. ± 0.30	X.° ± 5°	APRROVED	LEO
.X ± 0.20	.X° ± 3°	CHECKED	Gong
.XX ± 0.15	.XX° ± 2°	DESIGNED	Qiang

元精技术

TITLE: 0.3Pitch H=0.9 FPC/FFC Back-Flip RA Tpel SMT CONN

DRAWING NO. : C-FC0033R-01 A

PART NO. : SEE PART No 2/2