


RoHS Compliant


REV.	ZONE	DESCRIPTION	DESIGN	DATE
D		Modify the error view and size	ZXM	2024/05/16










组装示意图




RECOMMEND P.C.B LAYOUT(COMPONENT SIDE)
TOLERANCE FOR PCB LAYOUT IS ±0.05








NOTES:
SPECIFICATION:
1.CURRENT RATING: 3.0A MAX.
2.VOLTAGE: 100 VAC
3.TEMPERATURE RANGE: −30°C~+85°C
4.CONTACT RESISTANCE: 40 MILLION HM MAX.
5.INSULATION RESISTANCE: 100 MEG OHMS MIN.
6.LNSERTION FORCE: 5N~20N
7.UNMATING FORCE: 8N−20N
8.DURABILITY: 10000 CYCLES
9.WATER PROOFNESS:THIS PRODUCT IS BASED ON IPX8.





加防水圈示意图

TABLE:

NO	PART	Q'TY	Material
1	SHELL	1	STAINLESS STEEL,NI PLATED
2	CONTACT	6	COPPER STEEL,TIN/Au/NI PLATED
3	MID PLATE	1	STAINLESS STEEL,NO PLATING
4	1MD HOUSING	1	HIGH TEMPERATURE RESISTANT PLASTIC BLACK UL94 V-0
5	2MD HOUSING	1	HIGH TEMPERATURE RESISTANT PLASTIC BLACK UL94 V-0
6	SHIELDING PLATE	1	STAINLESS STEEL,NI PLATED

X.	±0.50	X.°	± 2°
.X	±0.30	.X°	± 1°
.XX	±0.10	.XX°	± 0.5°
.XXX	± 0.05		

UNITS mm
MAT'L
FINISH
Q'TY

广东创粤科技有限公司

TITLE: TYPE C 6PIN板上四脚插板SMT
防水母座 后柱 防水等级IPX8级

APPD:
CHKD:
DR:

DWG NO.: TYPE-C-6P-L7.9SMT-00110

SCALE	SHEET	REV.
1/1	1/2	D


THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF SHENZHEN CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF SHENZHEN CHUANGYUE TECHNOLOGY CO., LTD

USB TYPE-C PIN ASSIGNMENTS


PIN NUMBER	A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12
SIGNAL NAME					CC1				VBUS			GND
PIN NUMBER	B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1
SIGNAL NAME	GND			VBUS				CC2				


RoHS Compliant

REV.	ZONE	DESCRIPTION	DESIGN	DATE
D		Modify the error view and size	ZXM	2023/03/25




① 产品入载带示意图







② 卷盘贴标签示意图



③ 7盘产品叠层示意图



④ 产品入外箱示意图



⑤ 外箱封箱示意图

包装说明：

1. 将检验好的成品;对插口朝前放入载带;每卷装700PCS产品;具体如图一所示
2. 将包装好的产品;每盘必需贴上内标签;具体如图二所示
3. 将贴好内标签的产品每7盘叠;具体如图三所示
5. 装好后并封好纸箱及贴好相关标签;具体如图五所示;
   (产品包装的标签，如客户有要求，请按客户要求包装出货)
6. 载带前面留16PCS空格，后面留16PCS空格
7. COVER与CARRY剥离力:50-125g,速度:300mm/分钟左右,
   剥离角度:165°-180°

	REEL	CARTON
CONNECTOR (PCS)	700	4900

X. ±0.50	X.° ± 2°	UNITS mm	广东创粤科技有限公司
.X ±0.30	.X° ± 1°	MAT'L	TITLE: TYPE C 4PIN/6PIN/16PIN板上防水母座 包装规范
.XX ±0.10	.XX° ± 0.5°	FINISH	APPD: / DWG NO.: TYPE-C-6P-L7.9SMT-00110
.XXX ± 0.05		Q'TY	CHKD: / SCALE 1/1 / SHEET 2/2 / REV. D

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF SHENZHEN CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF SHENZHEN CHUANGYUE TECHNOLOGY CO., LTD

DR: