BORN SEMICONDUCTOR


RB521S-30

Schottky Barrier Diode

Features

- Low forward voltage drop
- High current capability
- High reliability
- High surge current capability
- Epitaxial construction


Package



General Description

- Case: molded plastic
- Polarity: Color band denotes cathode
- Package: SOD-523 Plastic Package

Marking



Ordering information

Order code	Package	Marking	Base qty	Delivery mode
RB521S-30	SOD-523	C	5K	Tape and reel

Maximum Ratings (@T_A=25°C unless otherwise noted)

Symbol	Parameter	Value	Units
V_R	Reverse voltage	30	V
$I_{F(AV)}$	Average forward current	200	mA
I_{FSM}	Peak forward surge current (at 8.3ms single half sine-wave)	1	A
P_D	Power Dissipation	200	mW
T_J	Operating junction temperature	125	°C
T_{STG}	Storage temperature range	-55 to +125	°C

BORN SEMICONDUCTOR , INC. ALL RIGHT RESERVED

Specifications are subject to change without notice.
Please refer to http://*www.born-tw.com* for current information.

Revision: 2022-Jan-1-A

RB521S-30

Schottky Barrier Diode

Electrical Characteristics(@T_A=25°C unless otherwise noted)

Symbol	Parameter	Test Condition	Limits		Unit
			Min.	Max.	
B_V	Breakdown Voltage	I_R=500uA	30	–	V
I_R	Reverse Leakage Current	V_R=10V	–	30	uA
V_F	Forward Voltage	I_F = 200mA	–	0.5	V

BORN SEMICONDUCTOR , INC. ALL RIGHT RESERVED

Specifications are subject to change without notice.
Please refer to http://*www.born-tw.com* for current information.

RB521S-30

Schottky Barrier Diode

Typical Performance Characteristics(T_J = 25 °C, unless otherwise noted)

Figure 1: Forward Characteristics




Figure 2: Reverse Characteristics





Figure 3: Total Capacitance




BORN SEMICONDUCTOR , INC. ALL RIGHT RESERVED

Specifications are subject to change without notice.
Please refer to http://*www.born-tw.com* for current information.

RB521S-30

Schottky Barrier Diode


Outline Drawing - SOD-523



Note:
dimension:in millimeters


SYMBOL	MILLIMETER		INCHES	
	MIN.	MAX.	MIN.	MAX.
A	0.50	0.70	0.020	0.028
b	0.25	0.35	0.010	0.014
C	0.07	0.20	0.0028	0.0079
D	1.10	1.30	0.043	0.051
E	0.70	0.90	0.028	0.035
H_E	1.50	1.70	0.059	0.067
L	0.15	0.25	0.006	0.010

Packaging Tape - SOD-523



SYMBOL	MILLIMETER
A0	0.50±0.10
A1	1.00±0.10
B0	1.30±0.10
B1	1.80±0.10
d0	1.55±0.10
d1	0.50±0.05
E	1.75±0.10
F	3.50±0.10
K0	0.65±0.10
P	2.00±0.10
P0	4.00±0.10
P1	2.00±0.10
W	8.00±0.30
T	0.2 ±0.05

Packaging Reel



SYMBOL	MILLIMETER
A	177.8±0.2
B	2.7±0.2
C	13.5±0.2
D	9.6±0.3
E	54.5±0.2
F	12.3±0.3
T1	1.0±0.2
Quantity	5000PCS

BORN SEMICONDUCTOR , INC. ALL RIGHT RESERVED

Specifications are subject to change without notice.
Please refer to http://*www.born-tw.com* for current information.

Revision: 2022-Jan-1-A