


RoHS Compliant


Process Capable

REV.	ZONE	DESCRIPTION	DESIGN	DATE
A	—	外露1.7改为1.5	曾捷	2023.3.31
B	—	根据实物重新出图	Peter Tan	2026.09.15











RECOMMEND P.C.B LAYOUT(COMPONENT SIDE)

TOLERANCE FOR PCB LAYOUT IS ±0.05





NOTES:

SPECIFICATION:

1. CURRENT RATING: 3.0A MAX
2. VOLTAGE: 100 VAC
3. TEMPERATURE RANGE: -30°C~+85°C
4. CONTACT RESISTANCE: 40 MILLION HM MAX
5. INSULATION RESISTANCE: 100 MEG OHMS MIN
6. LNSERTION FORCE: 5N~20N
7. UNMATING FORCE: 8N-20N
8. DURABILITY: 10000 CYCLES
9. WATER PROOFNESS:THIS PRODUCT IS BASED ON IPX8.

TABLE:

NO	PART	Q'TY	Material
1	SHELL	1	STAINLESS STEEL,NI PLATED
2	CONTACT	6	COPPER STEEL,TIN/Au/NI PLATED
3	MID PLATE	1	STAINLESS STEEL,NO PLATING
4	1MD HOUSING	1	HIGH TEMPERATURE RESISTANT PLASTIC BLACK UL94 V-0
5	2MD HOUSING	1	HIGH TEMPERATURE RESISTANT PLASTIC BLACK UL94 V-0
6	SHIELDING PLATE	1	STAINLESS STEEL,NI PLATED

USB TYPE-C PIN ASSIGNMENTS

PIN NUMBER	A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12
SIGNAL NAME					CC1				VBUS			GND
PIN NUMBER	B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1
SIGNAL NAME	GND			VBUS				CC2				

X. ± 0.20	X.° ± 2°	UNITS	mm
.X ± 0.15	.X° ± 1°	MAT'L	
.XX ± 0.10	.XX° ± 0.5°	FINISH	
.XXX ± 0.05		Q'TY	

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF GUANGDONG CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPROOUCED. COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF GUANGDONG CHUANGYUE TECHNOLOGY CO.,Ltd.

广东创粤科技有限公司

Guangdong Chuangyue Technology Co.,Ltd

TITLE: TYPE-C 6PIN四脚沉板SMT防水母座 防水等级IPX8级外露1.50mm

APPD: CZN

CHKD: CZJ

DR: Peter Tan

PART NO.: TYPE-C-6P-R0.8L7.9SMT-00124


SCALE 1/1

SHEET 1/1


REV.	ZONE	DESCRIPTION	DESIGN	DATE
A	—	外露1.7改为1.5	曾捷	2023.3.31
B	—	根据实物重新出图	Peter Tan	2026.09.15

Process Capable


RoHS Compliant




① 产品入载带示意图




② 卷盘贴标签示意图



③ 7盘产品叠层示意图



④ 产品入外箱示意图



⑤ 外箱封箱示意图

	REEL	CARTON
CONNECTOR (PCS)	700	4900

包装说明：

1. 将检验好的成品;对插口朝前放入载带;每卷装700PCS产品;具体如图一所示
2. 将包装好的产品;每盘必需贴上内标签;具体如图二所示
3. 将贴好内标签的产品每7盘叠;具体如图三所示
5. 装好后并封好纸箱及贴好相关标签;具体如图五所示;
   (产品包装的标签，如客户有要求，请按客户要求包装出货)
6. 载带前面留16PCS空格，后面留16PCS空格
7. COVER与CARRY剥离力:50-125g,速度:300mm/分钟左右,
   剥离角度:165°-180°

X. ± 0.20	X.° ± 2°	UNITS	mm
.X ± 0.15	.X° ± 1°	MAT'L	
.XX ± 0.10	.XX° ± 0.5°	FINISH	
.XXX ± 0.05		Q'TY	

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF GUANGDONG CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPROOUCED. COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF GUANGDONG CHUANGYUE TECHNOLOGY CO.,Ltd.

广东创粤科技有限公司
Guangdong Chuangyue Technology Co.,Ltd

TITLE: TYPE-C 6PIN四脚沉板SMT防水母座 防水等级IPX8级外露1.50mm

APPD:	CZN
CHKD:	CZJ
DR:	Peter Tan

PART NO.: TYPE-C-6P-R0.8L7.9SMT-00124

SCALE	SHEET
1/1	1/1