V_{DSS}	40	V
I_D	82	A
$R_{DS(ON)}$	3.9	mΩ

Features

Uses advanced Trench technology
Extremely low on-resistance RDS(on)
Excellent gate charge x RDS(on) product(FOM)

Application

Motor control and drive
Battery management
DC/DC


GK xxx
T004N04

LOGO GK xxx CODE


T004N04

RDS(ON) VDSS

PDFN5X6-8L top&bottom view



Equivalent Circuit



MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Absolute Maximum Ratings (T_C=25℃ unless otherwise noted)

Parameter	Symbol	Value	Unit
Drain-source voltage	V_{DS}	40	V
Gate-Source Voltage	V_{GS}	±20	V
Continuous drain current T_c=25℃（Silicon limit） T_c=100℃（Silicon limit）	I_D	82 52	A
Pulsed Drain Current	I_{DM}	320	A
Maximum Power Dissipation	P_d	54.3	W
Single pulse avalanche energy	E_{AS}	193	mJ
Operating Junction and Storage Temperature Range	T_J,T_{STG}	-55 To 150	℃

Thermal Characteristic

Thermal Resistance,Junction-to-Case	$R_{\theta JC}$	2.3	℃/W

Electrical Characteristics (T_J=25℃unless otherwise noted)

Static Characteristic	Symbol	Condition	min	typ	max	Unit
Drain-source breakdown voltage	$V_{(BR)DSS}$	V_{GS}=0V, I_D=250uA	40	45	-	V
Gate threshold voltage	$V_{GS(th)}$	V_{DS}=VGS, I_D=250uA	1	1.5	2	
Zero gate voltage drain current	I_{DSS}	V_{DS}=40V,V_{GS}=0V	-	-	±1	μA
Gate-source leakage current	I_{GSS}	V_{GS}=±20V,V_{DS}=0V	-	-	±100	nA
Drain-source on-state resistance	$R_{DS(on)}$	I_D=10A,V_{GS}=10V	-	3.9	5.0	mΩ
		I_D=10A,V_{GS}=4.5V	-	5.2	6.2	
Dynamic Characteristic						
Input Capacitance	C_{iss}	V_{DS}=20V,V_{GS}=0V, f=1MHz	-	2669	-	pF
Output Capacitance	C_{oss}		-	220	-	
Reverse Transfer Capacitance	C_{rss}		-	197	-	
Gate Total Charge	Q_G	V_{DS}=20V,I_D=20A,	-	90	-	nC
Gate-Source charge	Q_{gs}		-	14	-	
Gate-Drain charge	Q_{gd}		-	22	-	
Turn-on delay time	$t_{d(on)}$	V_{GS}=10V, V_{DD}=20V, R_G=3Ω	-	15	-	ns
Rise time	t_r		-	18	-	
Turn-off delay time	$t_{d(off)}$		-	58	-	
Fall time	t_f		-	23	-	
Gate resistance	Rg	VGS=0V, VDS=0V, f=1MHz	-	3	-	Ω
Body Diode Characteristic						
Diode Forward Voltage	V_{SD}	VGS=0V,IS=40A	-	0.85	1	v
Reverse Recovery Time	t_{rr}	I_F =20A di/dt = 100A/μs	-	42	-	ns
Reverse Recovery Charge	Q_{rr}		-	45	-	nC

RATING AND CHARACTERISTIC CURVES




Figure 1 Output Characteristics




Figure 4 Rdson-JunctionTemperature




Figure 2 Transfer Characteristics




Figure 5 Gate Charge




Figure 3 Rdson- Drain Current




Figure 6 Source- Drain Diode Forward

RATING AND CHARACTERISTIC CURVES




Figure 7 Capacitance vs Vds




Figure 9 Power De-rating




Figure 8 Safe Operation Area




Figure 10 $V_{GS(th)}$ vs Junction Temperature






Figure 11 Normalized Maximum Transient Thermal Impedance

Test Circuit & Waveform


Gate Charge Test Circuit & Waveform




Resistive Switching Test Circuit & Waveforms



Unclamped Inductive Switching (UIS) Test Circuit & Waveforms




Diode Recovery Test Circuit & Waveforms



Soldering parameters


Reflow Condition		Pb-Free assembly (see as bellow)
Pre Heat	-Temperature Min ($T_{s(min)}$)	+150℃
	-Temperature Max($T_{s(max)}$)	+200℃
	-Time (Min to Max) (ts)	60-180 secs.
Average ramp up rate (Liquid us Temp (T_L) to peak)		3℃/sec. Max
$T_{s(max)}$ to T_L - Ramp-up Rate		3℃/sec. Max
Reflow	-Temperature(T_L)(Liquid us)	+217℃
	-Temperature(t_L)	60-150 secs.
Peak Temp (T_p)		+260(+0/-5)℃
Time within 5℃ of actual Peak Temp (t_p)		30 secs. Max
Ramp-down Rate		6℃/sec. Max
Time 25℃ to Peak Temp (T_P)		8 min. Max
Do not exceed		+260℃

FIG5: Reflow condition




Package Dimensions & Suggested Pad Layout

PDFN5*6




Dim.	Min.	Max.
A	4.8	5.2
B	0.25	0.35
C	1	1.2
C1	Typ0.254	
C2	Typ0.254	
E	Typ1.27	
L	6	6.3
L1	5.7	6
L2	Max0.2	
R	Typ13°	
All Dimensions in millimeter		




Dimensions	Value (in mm)
C	1.27
G	6.45
X	0.62
X1	4.50
X2	0.62
Y	3.70
Y1	1.05
Y2	0.80

Tape & rell specification

Tape



13” Reel



Symbol	Dimension (mm)
P0	4.00±0.20
P1	8.00±0.20
P2	2.00±0.20
D0	1.55±0.20
D1	1.55±0.20
E	1.75±0.20
F	5.50±0.20
W	12.00±0.20
A0	6.60±0.20
B0	5.70±0.20
K0	1.30±0.20
T	0.20±0.20
D2	330.0±5.0
D3	100.0±4.0
W1	12.0±5.0
W2	14.0±5.0
I	13.0±2.0

Quantity: 5000PCS