



由 Autodesk 教育版产品制作


REV.	ZONE	DESCRIPTION	DESIGN	DATE
B		NEW		

















Recommended P.C.B Layout

Tolerance ±0.05

A12	A11	A10	A9	A8	A7	A6	A5	A4	A3	A2	A1
GND	RX2+	RX2-	V_{BUS}	SBU1	D-	D+	CC1	V_{BUS}	TX1-	TX1+	GND
GND	TX2+	TX2-	V_{BUS}	CC2	D+	D-	SBU2	V_{BUS}	RX1-	RX1+	GND
B1	B2	B3	B4	B5	B6	B7	B8	B9	B10	B11	B12

1.Material:
Contacts: Copper alloy T=0.15
Insulator: HIGH TEMPERATURE PLASTIC UL 94V-0,
Shell: STEEL T=0.15
MID Plate: Stainless Steel
EMI Plate: Stainless Steel
2.Electrical:
Current-max[amps]: 5A Max For Vbus/GND PIN;
0.9A Max For Other PIN.
Withstanding Voltage: 100V AC R.M.S
Contact Resistance [ohms]: 40mΩ Max.For
Initial 10mΩ.Change Afier
Test.Measure AT 20mV,100mA
Insulation Resistance [ohms]: 100 mΩ min.
3.MECHANICAL CHARACTERISTICS:
Mating force: 5~20N
Unmated Force: 6~20N After test.
Durability: 10000 cycles min.
4.Plating:
Contacts: SEE TABLE Au plated on contact area,
Fog SN plating 80-100U"Min on solder area
Nickel Under plating 20u"Min over all
Gnd pin: Plating 30u"min Nickel under overall
on solder SN 80u"Min
Shell : plating 50~100U"Nickel over
5.Environmental
Temperature Range: -55° C~+85° C

NO	DESCRIPTION	QTY	MATERIAL	PLATING & COLOR
G	EMI	2	SUS301	---
F	CONTACT	12	C7025	Au:1U"
E	TOP COVER	1	LCP+30%GF,UL 94V-0	BLACK
D	BOTTOM COVER	1	LCP+30%GF,UL 94V-0	BLACK
C	GND PIN	1	SUS301	30U" min NI on SN Plating
B	CONTACT	12	C7025	Au:1U"
A	SHELL	1	SUS304	50～100U"NICKEL Plating

ITEM	Part Name	Part No.	Marker
1	USB TYPE-CM 端子SMT+SMT 不锈钢DIP脚外壳 黑色料雾锡高导铜Gold Flash成品（卷装）	2711-4421-27D	不锈钢壳镍;黑胶;高导铜C7025端子G/F U"

TABLE:


X. ±0.50	X.° ± 2°	UNITS mm	广东创粤科技有限公司
.X ±0.30	.X° ± 1°		
.XX ±0.20	.XX° ± 0.5°	MAT'L	TITLE: TYPE-C 24PIN 沉板公头 双排贴片 端子卡勾加长款
.XXX ± 0.10			
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF SHENZHEN CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF SHENZHEN CHUANGYUE TECHNOLOGY CO., LTD		FINISH	APPD: / DWG NO.: TYPE-CM-24P-H13.75-00114
		Q'TY	CHKD: / SCALE 1/1 / SHEET 1/2 / REV. B
			DR:

电话：0755-85298729 传真：0755-23711550 网址：www.gdzhaoyi.com 邮箱：zhijia.chen@gdzhaoyi.cn


由 Autodesk 教育版产品制作

REV.	ZONE	DESCRIPTION	DESIGN	DATE
B		NEW		


RoHS Compliant




① 产品入载带示意图




② 卷盘贴标签示意图



③ 7盘产品叠层示意图



④ 产品入外箱示意图



⑤ 外箱封箱示意图

	REEL	CARTON
CONNECTOR (PCS)	1000	7000

包装说明：

1. 将检验好的成品;对插口朝前放入载带;每卷装1000PCS产品;具体如图一所示
2. 将包装好的产品;每盘必需贴上内标签;具体如图二所示
3. 将贴好内标签的产品每7盘叠;具体如图三所示
5. 装好后并封好纸箱及贴好相关标签;具体如图五所示;
   (产品包装的标签，如客户有要求，请按客户要求包装出货)
6. 载带前面留22PCS空格，后面留22PCS空格
7. COVER与CARRY剥离力:50-125g,速度:300mm/分钟左右,
   剥离角度:165°-180°

X. ±0.50	X.° ± 2°	UNITS mm
.X ±0.30	.X° ± 1°	MAT'L
.XX ±0.20	.XX° ± 0.5°	
.XXX ± 0.10		FINISH
		Q'TY

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF SHENZHEN CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF SHENZHEN CHUANGYUE TECHNOLOGY CO., LTD

广东创粤科技有限公司

TITLE: TYPE-C 24PIN 沉板公头 双排贴片 铆压款包装规范

APPD:

CHKD:

DR:

DWG NO.: TYPE-CM-24P-H13.75-00114

SCALE	SHEET	REV.
N/A	2/2	B

由 Autodesk 教育版产品制作