


RoHS


REV.	EC#	DESCRIPTION	DATE	DRAWING	CHECKED	APPROVED
A0		导入ERP料号	03/05'21	YINXUAN		HAIYONG








RECOMMENDED PCB LAYOUT





SIM pin assignment	
PIN#	Name
C1	VCC供电电压
C2	RST重置
C3	CLK时钟
C5	GND接地
C6	VPP程序电压
C7	I/O输入输出

NOTES:
1. MATERIAL:
   1.1 Insulator: High Temperature Thermoplastic, UL94V-0; Color Black.
   1.2 Terminal:Copper Alloy.
   1.3 Shell:Stainless Steel.
2. PLATING:
   2.1 Contact: Plated 50u'' Ni Overall Contact Au 1u",
   2.2 Shell: Plated 50u'' Ni Overall,PAD Au 1u"
3. SPECIALITY:
   2.1 Current Rating :0.5mA AC/DC max.
   2.2 Voltage Rating :125V AC/DC
   2.3 Ambient Temperature Range :-20° C~+60° C
   2.4 Storage Temperature Range :-40° C~+70° C
   2.5 Ambient Humidity Range :95% R.H. Max.
   2.6 Contact Resistance:100mΩ max.
   2.7 Insulation Resistance:1000MΩ min./500VDC
   2.8 Mating Cycles:10,000 Insertions
   2.9 Reflow peak temp.: 260° C ±5° C, 3~5 S
   2.10 Mating Cycles:3,000 Insertions Min
4. PLEASE CONTACT LQ SALES REPRESENTATIVE TO VERIFY PRODUCTDETAILS & AVAILABILITY

Unless otherwise specified tolerances are	
X.X	±0.30
X.XX	±0.20
X.XXX	±0.10
X°	±3.0°
X.X°	±1.5°

广东国连电子有限公司
GUANGDONG GUOLIAN ELECTRONICS CO., LTD


		DATE	DRAW NAME:
DRAW NO.			SIM 卡座 6Pin 1.35H 有定位柱(客户图)
DWN			
CHK			P/N : NNB5FW1062C2
APVD			

Third Angle Project

FINISH		UNIT	SCALE	WEIGHT	REV	SHEET
DWG NO.		mm	1:1		A0	1 OF 2

RoHS


User Direction of Unreeling



User Direction of Unreeling

NOTES

1. NUMBER OF CONNECTORS:1800PCS/REEL
2. LEAD TAPE LENGTH




3.QUANTITY:18000PCS/CARTON

4. WEIGHT :

3.1 NET WEIGHT : Kg

3.2 GROSS WEIGHT : Kg



Unless otherwise specified tolerances are	
X.X	±0.30
X.XX	±0.20
X.XXX	±0.10
X°	±3.0°
X.X°	±1.5°

广东国连电子有限公司
GUANGDONG GUOLIAN ELECTRONICS CO.,LTD

DRAW NO.		DATE	DRAW NAME:
DWN			SIM 卡座 6Pin 1.35H 有定位柱(客户图)
CHK			P/N : C-NNB5FW1062C2
APVD			

Third Angle Project	FINISH		UNIT	SCALE	WEIGHT	REV	SHEET
	DWG NO.		mm	1:1		A1	2 OF 2