2N7002BKS

N-Channel SMD MOSFET ESD Protection

Product Summary

$V_{(BR)DSS}$	$R_{DS(on)MAX}$	I_D
60V	5.0Ω@10V	0.34A
	5.3Ω@4.5V	


Feature

- High density cell design for ultra low on-resistance
- Voltage controlled small signal switch
- Rugged and reliable
- High saturation current capability
- ESD protected

Application


- Load Switch for Portable Devices
- DC/DC Converter

Package



SOT-363

Circuit diagram



Marking:72K

Absolute maximum ratings (Ta=25C° unless otherwise noted)

Parameter	Symbol	Value	Unit
Drain-Source Voltage	V_{DS}	60	V
Gate-Source Voltage	V_{GS}	±20	V
Continuous Drain Current	I_D	0.34	A
Power Dissipation	P_D	0.15	W
Thermal Resistance from Junction to Ambient	$R_{\theta JA}$	833	℃/W
Junction Temperature	T_J	150	℃
Storage Temperature	T_{STG}	-55 ~ +150	℃

Electrical characteristics (T_A=25 °C, unless otherwise noted)

Parameter	Symbol	Test Condition	Min.	Typ.	Max.	Unit
Static Characteristics						
Drain-source breakdown voltage	$V_{(BR)DSS}$	V_{GS} = 0V, I_D =10μA	60			V
Zero gate voltage drain current	I_{DSS}	V_{DS} =48V,V_{GS} = 0V			1	μA
Gate-body leakage current	I_{GSS}	V_{GS} =±20V, V_{DS} = 0V			±10	μA
Gate threshold voltage	$V_{GS(th)}$	V_{DS} =V_{GS}, I_D =250μA	1.0		2.5	V
Drain-source on-resistance[1]	$R_{DS(on)}$	V_{GS} =10V, I_D =0.5A		0.9	5	Ω
		V_{GS} =4.5V, I_D =0.2A		1.1	5.3	
Dynamic characteristics[2]						
Input Capacitance	C_{iss}	V_{DS} =10V,V_{GS} =0V,f =1MHz			40	pF
Output Capacitance	C_{oss}				30	
Reverse Transfer Capacitance	C_{rss}				10	
Turn-on delay time	$t_{d(on)}$	V_{DD}=50V,V_{GS}=10V, R_L=250Ω,R_{GEN}=50Ω			10	nS
Turn-off delay time	$t_{d(off)}$				15	
Source-Drain Diode characteristics						
Diode Forward voltage	V_{DS}	V_{GS} =0V, I_S=0.3A			1.5	V


Notes:

1) Pulse Test: Pulse Width < 300μs, Duty Cycle ≤2%.


2) Guaranteed by design, not subject to production testing.

Typical Characteristics


Output Characteristics




Transfer Characteristics




$R_{DS(ON)}$ — I_D




$R_{DS(ON)}$ — V_{GS}




I_S — V_{SD}



Threshold Voltage



SOT-363 Package Information



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	0.900	1.100	0.035	0.043
A1	0.000	0.100	0.000	0.004
A2	0.900	1.000	0.035	0.039
b	0.150	0.350	0.006	0.014
c	0.100	0.150	0.004	0.006
D	2.000	2.200	0.079	0.087
E	1.150	1.350	0.045	0.053
E1	2.150	2.400	0.085	0.094
e	0.650 TYP.		0.026 TYP.	
e1	1.200	1.400	0.047	0.055
L	0.525 REF.		0.021 REF.	
L1	0.260	0.460	0.010	0.018
θ	0°	8°	0°	8°