


Rev No.	Description of Revision	Date	Name	Approved	ECN No.
A					




LOCK CARD TATUS




OPEN CARD TATUS






RECOMMENDED PCB LAYOUT(Top View)

GENERAL TOLERANCE ±0.05






MICRO SIM

PIN NO.	NAME	PIN NO.	NAME
C1	VCC	C4	VPP
C2	GND	C5	CLK
C3	RST	C6	I0

NOTES:

1. ELECTRICAL CHARACTERISTICS
   - 1-1. CONTACT RESISTANCE: 60 Milliohms Max
   - 1-2. INSULATION RESISTANCE: 1,000 Megohms Min.
   - 1-3. VOLTAGE RATING: 50V.
   - 1-4. CURRENT RATING: 1.0A.
2. MECHANICAL CHARACTERISTICS
   - 2-1. OPERATION TEMPERATURE RANGE: -20°C~+85°C
   - 2-2. DURABILITY: 5000 CYCLES
3. MATERIAL:
   - 3-1. HOUSING: THERMOPLASTIC,UL 94-V0
   - 3-2. TERMINAL: PHOSPHOR BRONZE,T=0.15mm
   - 3-3. SHELL: STAINLESS STEEL,T=0.20mm
4. FINISHED:
   - 4-1. TERMINAL: Ni PLATED UNDER, 1U" Au MIN PLATED ON CONTACT AREA,AU PLATED ON SOLDER TAIL
   - 4-2. SHELL: Ni PLATED UNDER,G/F PLATED ON SOLDER TAIL



UNLESS OTHERWSE SPECIFED TOLERANCES		广东国连电子有限公司 GUANGDONG GUOLIAN ELECTRONICS CO.,LTD			
DECIMALS:	ANGLES	TITLE: MICRO SIM CARD 1.5H 掀盖客户图			
X. ±0.20	X° ±2°	Drdwn. PETERLI	PART NO. MIB5FS1062E5		
X.X ±0.15	X.X° ±1°	Checked. PETERLI	SCALE. 1:1	UNIT. mm	PROJ.
X.XX ±0.10	X.XX° ±0.5°	Approved. LEE	SIZE. A4	SHEET. 1 OF 1	REV. A
X.XXX ±0.05		CUSTOMER COPY			