


RoHS Compliant

REV.	ZONE	DESCRIPTION	DESIGN	DATE
A		NEW	曾捷	2023/06/15







A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME





SECTION
B−B
SCALE 1:1




SECTION
A−A
SCALE 1:1







RECOMMENDED P.C.B. LAYOUT
TOLERANCE UNSPECIFIED ±0.05mm




Note:
1.Material:
1.1 Housing: LCP
1.2 Contact:C7025,T=0.15mm
1.3 Shell: SUS304 T=0.3mm
2.ELECTRICAL:
2−1:CURUENT RATAING:
VBUS AND GND CONTACTS RATED AT 1.25A
PARALLELED FOR A TOTAL OF 5A;
2−2:INITIAL CONTACT RESISTANCE :40 MEGOHMS
2−3:DIEELECTRIC WITHSTANDING VOLTAGE:
100V AC MIN;
3:MECHANICAL CHARACTERISTICS:
3−1:MATING FORCE:5~20N
3−2:UNMATING FORCE:8~20N(INITIAL),
6~20N(AFTER 10000 CYCLES)
3−3:FREQUENCE: 200±50 CYCLES /HOUR,
10000 CYCLES
3−4:OPERATING TEMPERATURE ;−40°~80°.

X. ±0.50	X.° ± 2°	UNITS	广东创粤科技有限公司
.X ±0.30	.X° ± 1°	mm	
.XX ±0.10	.XX° ± 0.5°	MAT'L	TITLE: TYPE-C 16PIN直立式母座H=6.8无弹片
.XXX ± 0.05			
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF SHENZHEN CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF SHENZHEN CHUANGYUE TECHNOLOGY CO., LTD		FINISH	APPD: / DWG NO.: TYPE-C-16P-H6.8SMT-00171
		Q'TY	CHKD: / SCALE 1/1 / SHEET 1/2 / REV. A
			DR:


由 Autodesk 教育版产品制作

RoHS Compliant


REV.	ZONE	DESCRIPTION	DESIGN	DATE
A		NEW	曾捷	2023/06/15




① 产品入载带示意图




② 卷盘贴标签示意图



③ 7盘产品叠层示意图



④ 产品入外箱示意图



⑤ 外箱封箱示意图

	REEL	CARTON
CONNECTOR (PCS)	600	4200

包装说明:

1. 将检验好的成品;对插口朝前放入载带;每卷装600PCS产品;具体如图一所示
2. 将包装好的产品;每盘必需贴上内标签;具体如图二所示
3. 将贴好内标签的产品每7盘叠;具体如图三所示
5. 装好后并封好纸箱及贴好相关标签;具体如图五所示;
   (产品包装的标签, 如客户有要求, 请按客户要求包装出货)
6. 载带前面留16PCS空格, 后面留16PCS空格
7. COVER与CARRY剥离力:50-125g,速度:300mm/分钟左右,
   剥离角度:165°-180°

X. ±0.50	X.° ± 2°	UNITS mm	广东创粤科技有限公司
.X ±0.30	.X° ± 1°	MAT'L	TITLE: TYPE-C 16PIN/24PIN直立式母座包装规范
.XX ±0.10	.XX° ± 0.5°		
.XXX ± 0.05		FINISH	APPD: / DWG NO.: TYPE-C-16P-H6.8SMT-00171
		Q'TY	CHKD: / SCALE 1/1 / SHEET 2/2 / REV. A
			DR:

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF SHENZHEN CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF SHENZHEN CHUANGYUE TECHNOLOGY CO., LTD