

■ Features

- Glass passivated chip
- Low reverse leakage current
- High surge current capability
- Reliable low cost construction utilizing molded plastic technique

Reverse Voltage

50-1000 V

Forward Current

60.0 A max

■ Applications


- General purpose use in AC/DC bridge full wave rectification

■ Mechanical Data

- Case: HGBJ
- Polarity symbols being marked on body
- Molding compound meets UL 94V-0 flammability rating
- RoHS-compliant, Solder plated, solderable per MIL-STD-750, Method 2026



Appearance Image



■ Marking

- HD60SBxx(10~120)

■ Maximum Ratings @ Ta = 25°C unless otherwise noted

PARAMETER	SYMBOL	UNIT	HD60SB 10	HD60SB 20	HD60SB 40	HD60SB 60	HD60SB 80	HD60SB 100	HD60SB 120
Repetitive peak reverse voltage	V_{RRM}	V	100	200	400	600	800	1000	1200
Maximum RMS voltage	V_{RMS}	V	70	140	280	420	560	700	840
Maximum DC blocking Voltage	V_{DC}	V	100	200	400	600	800	1000	1200
Maximum average output current@60Hz sine wave, resistance load	$I_{F(AV)}$	A	50.0						
Peak forward surge current 8.3 ms single half sine wave superimposed on rated load	I_{FSM}	A	550						
Peak forward surge current 1.0 ms single half sine wave superimposed on rated load		A	1100						
Current squared time @1ms≤t<8.3ms Tj=25°C, Rating of per diode	I^2t	A²S	1255.38						
Storage temperature	T_{stg}	°C	-55~+150						
Junction temperature	T_j	°C	-55~+150						

■ Electrical Characteristics @ Ta = 25°C unless otherwise noted

PARAMETER	TEST CONDITIONS	SYMBOL	UNIT	HD60SB 10	HD60SB 20	HD60SB 40	HD60SB 60	HD60SB 80	HD60SB 100	HD60SB 120
Maximum instantaneous forward voltage	$I_F=30.0A$	V_F	V	1.0						
Maximum DC reverse current at rated DC blocking voltage	$V_R=V_{DC}, T_j=25^\circ C$	I_R	μA	10						
	$V_R=V_{DC}, T_j=100^\circ C$	I_R		500						

■ Characteristic Curve (Typical)




FIG1. Derating Curve For Output Rectified Current




FIG2. Surge Forward Current Capability




FIG3. Typical Forward Characteristics





FIG4. Typical Reverse Characteristics



■ **Marking and packet information**



HD**SB*** : Marking Model **TOS** : Brand Logo

Packaging information	
每盒	250PCS
每箱	2000PCS
脚长定制	支持

■ **HGBJ Package outline dimensions**



Dimensions in milimeters

■ **Notice**

XILONG reserves the right to make modifications,enhancements,improvements,corrections or other changes without further notice to any product herein.
xilong does not assume any liability arising out of the application or use of any product described herein.