

自主封測 品質把控 售後保障


WEB | WWW.TDSEMIC.COM




電源管理




顯示驅動




二三極管



LDO穩壓器




觸摸芯片



MOS管




運算放大器



存儲芯片



MCU



串口通信


BAV70-TD

產品規格說明書


BAV70 SWITCHING DIODES

FEATURES

Fast Switching Speed
For General Purpose Switching Applications
High Conductance



SOT-23



1. BASE
2. EMITTER
3. COLLECTOR

MARKING: A4

Maximum Ratings @T_A=25°C





Paramet	Symbol	Lim	Unit
Reverse voltage	V _R	8	V
Forward Current	I _F	2	mA
Peak Forward Surge Current	I _{FM(surge)}	5	mA
Power Dissipation	P _D	2	mW
Thermal Resistance Junction to Ambient Air	R _{θJA}	5	°C/W
Junction temperature	T _J	1	°C
Storage temperature range	T _{STG}	-55-150	°C

Electrical Characteristics @T_A=25°C

Parameter	Symbol	Min.	Typ.	Max.	Unit	Conditions
Reverse Breakdown Voltage	V _R	80			V	I _R =100μA
Forward voltage	V _{F1}			0.715	V	I _F =1mA
	V _{F2}			0.855	V	I _F =10mA
	V _{F3}			1	V	I _F =50mA
	V _{F4}			1.25	V	I _F =150mA
Reverse current	I _R			2.5	μA	V _R =80V
Capacitance between terminals	C _T			1.5	pF	V _R =0, f=1MHz
Reverse recovery time	t _{rr}			6	ns	I _F = I _R = 10mA, I _{rr} = 0.1 x I _R , R _L = 100Ω

Typical Characteristics



BAV70



PACKAGE OUTLINE

Plastic surface mounted package; 3 leads

SOT-23



UNIT	A	B	bp	C	D	E	HE	A1	Lp
mm	1.40 0.95	2.04 1.78	0.50 0.35	0.19 0.08	3.10 2.70	1.65 1.20	3.00 2.20	0.100 0.013	0.50 0.20