
MSKSEMI 美森科
SEMICONDUCTOR



MSZ0G05A

Product specification

MSZ0G05A

60V/5A N-Channel MOSFET



Features

- Excellent package for good heat dissipation
- Ultra low gate charge
- Low reverse transfer capacitance
- Fast switching capability
- Avalanche energy specified

Application

- Power switching application

Reference News

SOT-89-3L	Schematic diagram	Marking
		0G05A ****

Product Summary

V_{DS}	$R_{DS(ON)}$ MAX	I_D MAX
60V	100mΩ@10V	5A
	150mΩ@4.5V	

Absolute Maximum Ratings (TA=25℃unless otherwise noted)

Symbol	Parameter		Rating	Unit
Common Ratings (TC=25°C Unless Otherwise Noted)				
V_{DS}	Drain-Source Breakdown Voltage		60	V
V_{GS}	Gate-Source Voltage		±20	V
T_J	Maximum Junction Temperature		150	°C
T_{STG}	Storage Temperature Range		-55 to 150	°C
I_S	Diode Continuous Forward Current	Tc=25°C	5	A
Mounted on Large Heat Sink				
I_{DM}	Pulse Drain Current Tested	Tc=25°C	20	A
I_D	Continuous Drain Current	Tc=25°C	5	A
P_D	Maximum Power Dissipation	Tc=25°C	0.5	W
$R_{\theta JA}$	Thermal Resistance Junction-Ambient		200	°C/W

Ordering Information (Example)

Type	Package	Minimum Package(pcs)	Inner Box Quantity(pcs)	Outer Carton Quantity(pcs)	Delivery Mode
MSZ0G05A	SOT-89-3L	1,000	4,000	24,000	7"reel

Copyright© Msksemi Incorporated

Electrical Characteristics (TJ=25℃ unless otherwise noted)

Symbol	Parameter	Condition	Min	Typ	Max	Unit
Static Electrical Characteristics @ TJ = 25°C (unless otherwise stated)						
$BV_{(BR)DSS}$	Drain-Source Breakdown Voltage	V_{GS}=0V, I_D=250μA	60	--	--	V
I_{DSS}	Zero Gate Voltage Drain Current	V_{DS}=60V, V_{GS}=0V	--	--	1	μA
I_{GSS}	Gate-Body Leakage Current	V_{GS}=±20V, V_{DS}=0V	--	--	±100	nA
$V_{GS(th)}$	Gate Threshold Voltage	V_{DS}=V_{GS}, I_D=250μA	1.0	1.3	2.5	V
$R_{DS(on)}$	Drain-Source On-State Resistance	V_{GS}=10V, I_D=3A	--	70	100	mΩ
		V_{GS}=4.5V, I_D=2A	--	85	150	mΩ
Dynamic Electrical Characteristics @ TJ = 25°C (unless otherwise stated)						
C_{ISS}	Input Capacitance	V_{DS}=30V, V_{GS}=0V, f=1MHz	--	400	--	pF
C_{OSS}	Output Capacitance		--	28	--	pF
C_{RSS}	Reverse Transfer Capacitance		--	23	--	pF
Switching Characteristics						
Q_g	Total Gate Charge	V_{DS}=30V, I_D=5A, V_{GS}=10V	--	9	--	nC
Q_{gs}	Gate Source Charge		--	1	--	nC
Q_{gd}	Gate Drain Charge		--	2.5	--	nC
$t_{d(on)}$	Turn-on Delay Time	V_{DD}=30V, I_D=5A, V_{GS}=10V, R_G=2.3Ω	--	4	--	nS
t_r	Turn-on Rise Time		--	10	--	nS
$t_{d(off)}$	Turn-Off Delay Time		--	12.5	--	nS
t_f	Turn-Off Fall Time		--	1.8	--	nS
Source- Drain Diode Characteristics						
V_{SD}	Forward on voltage	Tj=25°C, Is=5A	--	0.8	1.2	V

Copyright© Msksemi Incorporated

Typical Operating Characteristics




Fig1. Typical Output Characteristics




Fig2. Typical Gate Charge Vs.Gate-Source Voltage




Fig3. Normalized On-Resistance Vs. Temperature




Fig4. On-Resistance Vs. Drain-Source Current




Fig5. Maximum Safe Operating Area





Fig6 Typical Capacitance Vs.Drain-Source Voltage


Copyright© Msksemi Incorporated

PACKAGE MECHANICAL DATA



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	1.400	1.600	0.055	0.063
b	0.320	0.520	0.013	0.020
b1	0.400	0.580	0.016	0.023
c	0.350	0.440	0.014	0.017
D	4.400	4.600	0.173	0.181
D1	1.550 REF.		0.061 REF.	
E	2.300	2.600	0.091	0.102
E1	3.940	4.250	0.155	0.167
e	1.500 TYP.		0.060 TYP.	
e1	3.000 TYP.		0.118 TYP.	
L	0.900	1.200	0.035	0.047

Suggested Pad Layout



Note:
1.Controlling dimension:in millimeters.
2.General tolerance:±0.05mm.
3.The pad layout is for reference purposes only.

Copyright© Msksemi Incorporated

Attention

■ Any and all MSKSEMI Semiconductor products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your MSKSEMI Semiconductor representative nearest you before using any MSKSEMI Semiconductor products described or contained herein in such applications.

■ MSKSEMI Semiconductor assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specificationsof any andall MSKSEMI Semiconductor products described orcontained herein.

■ Specifications of any and all MSKSEMI Semiconductor products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer'sproducts orequipment.

■ MSKSEMI Semiconductor. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with someprobability. It is possiblethat these probabilistic failures could give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits anderror prevention circuitsfor safedesign, redundant design, and structural design.

■ In the event that any or all MSKSEMI Semiconductor products(including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from theauthorities concerned in accordance with the above law.

■ No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of MSKSEMI Semiconductor.

■ Information (including circuit diagrams and circuit parameters) herein is for example only ; it is not guaranteed for volume production. MSKSEMI Semiconductor believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringementsof intellectual property rights or other rightsof third parties.

■ Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. Whendesigning equipment, referto the "Delivery Specification" for the MSKSEMI Semiconductor productthat you intend to use.

Copyright© Msksemi Incorporated