
TK2SC2412

TRANSISTOR (NPN)




FEATURES

· Low C_{ob} ,C_{ob} = 2.0 pF (Typ).

SOT-23 Plastic-Encapsulate Transistors



CLASSIFICATION of h_{FE}

Rank	Q	R	S
Range	120-270	180-390	270-560
Marking	BQ	BR	BS
MARKING			

MAXIMUM RATINGS (T_a=25℃ unless otherwise noted)


Symbol	Parameter	Value	Unit
V_{CBO}	Collector-Base Voltage	60	V
V_{CEO}	Collector-Emitter Voltage	50	V
V_{EBO}	Emitter-Base Voltage	7	V
I_C	Collector Current	150	mA
P_C	Collector Power Dissipation	200	mW
$R_{\Theta JA}$	Thermal Resistance From Junction To Ambient	625	℃/W
T_J,T_{stg}	Operation Junction and Storage Temperature Range	-55～+150	℃

ELECTRICAL CHARACTERISTICS (T_a=25℃ unless otherwise specified)


Parameter	Symbol	Test conditions	Min	Typ	Max	Unit
Collector-base breakdown voltage	$V_{(BR)CBO}$	I_C=50μA,I_E=0	60			V
Collector-emitter breakdown voltage	$V_{(BR)CEO}$	I_C=1mA,I_B=0	50			V
Emitter-base breakdown voltage	$V_{(BR)EBO}$	I_E=50μA,I_C=0	7			V
Collector cut-off current	I_{CBO}	V_{CB}=60V,I_E=0			0.1	μA
Emitter cut-off current	I_{EBO}	V_{EB}=7V,I_C=0			0.1	μA
DC current gain	h_{FE}	V_{CE}=6V,I_C=1mA	120		560	
Collector-emitter saturation voltage	$V_{CE(sat)}$	I_C=50mA,I_B=5mA			0.4	V
Transition frequency	f_T	V_{CE}=12V,I_C=-2mA,f=100MHz		160		MHz
Collector output capacitance	C_{ob}	V_{CB}=12V,I_E=0,f=1MHz		2.0	3.5	pF

Typical Characteristics


V_{CE} —— I_C




h_{FE} —— I_C




V_{CEsat} —— I_C




V_{BEsat} —— I_C




I_C —— V_{BE}




f_T —— I_C





C_{ob}/C_{ib} —— V_{CB}/V_{EB}




P_C —— T_a










Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	0.900	1.150	0.035	0.045
A1	0.000	0.100	0.000	0.004
A2	0.900	1.050	0.035	0.041
b	0.300	0.500	0.012	0.020
c	0.080	0.150	0.003	0.006
D	2.800	3.000	0.110	0.118
E	1.200	1.400	0.047	0.055
E1	2.250	2.550	0.089	0.100
e	0.950 TYP		0.037 TYP	
e1	1.800	2.000	0.071	0.079
L	0.550 REF		0.022 REF	
L1	0.300	0.500	0.012	0.020
θ	0°	8°	0°	8°

SOT-23 Suggested Pad Layout



Note:
1.Controlling dimension:in millimeters.
2.General tolerance:± 0.05mm.
3.The pad layout is for reference purposes only.