

零件编号 : [2264712111](#)

Product Description : Nano-Fit Crimp Terminal,
Female, 1.50µm Matte Tin (Sn) Plating, 26-24 AWG

系列号 : [226471](#)

Status : Active

Product Category : Crimp Terminals



Documents and Resources

图纸

[2264712111_sd.pdf](#)

[2264711000-PK-000.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

规格

[AS-105300-100-001.pdf](#)

[PS-105300-100-001.pdf](#)

[1053000000-TS-000.pdf](#)

[1053001000-TS-000.pdf](#)

产物环境合规

合规

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

合规声明

- EU RoHS
- REACH SVHC
- Low-Halogen

行业文件

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

关注物质

产品详情

一般

状态	Active
类别	Crimp Terminals
系列	226471
说明	Nano-Fit Crimp Terminal, Female, 1.50µm Matte Tin (Sn) Plating, 26-24 AWG
应用	Wire-to-Board
产品名称	Nano-Fit
UPC	198282793625

电气

每触点最大电流	6.0A
电压 - 最大	250V AC (RMS)/DC

物理

耐用性(插拔次数) - 最多次数	25
部件属性	Female
材料 - 金属	High Conductivity Copper
材料 - 接合部位电镀	Matte Tin
材料 - 终端电镀	Matte Tin
净重	0.103/g
包装形式	Reel
最薄镀层 - 接合部位	1.500µm
最薄镀层 - 端接	1.500µm
终端界面类型	Crimp or Compression
导线绝缘直径	1.30mm
线径规格 (AWG)	24, 26
线缆尺寸mm²	N/A

可配插/可连接使用的产品

可连接使用部件

说明	零件编号
Nano-Fit TPA Capable Single Row Receptacle Housings for UL 1569/1007 Wire	226354

Nano-Fit TPA Capable Dual Row Receptacle Housings for UL 1569/1007 Wire	226362
---	------------------------

施工工具

Global

说明	零件编号
Hand Crimp Tool for Nano-Fit Receptacle Crimp Terminals, 26-20 AWG, UL 1569 / UL 1007	2238634300
FineAdjust Applicator for Insulation OD 1.20 - 1.45mm - UL1007	639034800
Extraction Tool for Nano-Fit Power Connectors/Terminals and DuraClik Robust Connectors/Terminals, 26-20 AWG and 0.30-0.50mm ² Wire	638244600