
MSKSEMI 美森科
SEMICONDUCTOR



MSK2460G

Product specification

GENERAL DESCRIPTION

MSK2460G is a current mode monolithic buck switching regulator. Operating with an input range of 4.5V~40V, the MSK2460G delivers 800mA of continuous output current with two integrated N-Channel MOSFETs. The internal synchronous power switches provide high efficiency without the use of an external Schottky diode. At light loads, the regulator operates in low frequency to maintain highefficiency and low output ripple. Current mode control provides tight load transient response and cycle-by-cycle current limit.

The MSK2460G guarantees robustness with short-circuit protection, thermal protection, current run-away protection, and input under voltage lockout.

The MSK2460G is available in 6-pin SOT23-6 package,which provides a compact solution with minimal external components.



FEATURES

- 4.5V to 40V Input Voltage Range 800mA output current
- High Efficiency: Up to 95%
- No Schottky Diode Required
- 0.8V Reference
- Slope Compensated Current Mode Control for Excellent Line and Load Transient Response Integrated internal compensation
- Stable with Low ESR Ceramic Output Capacitors
- Input under voltage lockout
- Short circuit protection
- Thermal Shutdown
- Inrush Current Limit and Soft Start
- -40°C to +85°C Temperature Range

APPLICATIONS

- Distributed Power Systems
- Automotive Systems
- High Voltage Power Convertion
- Industrial Power Systems
- Battery Powered Systems

Reference News


SOT-23-6	PIN CONFIGURATION	MARKING
		

ORDER INFORMATION


P/N	PKG	QTY
MSK2460G	SOT-23-6	3000

Copyright© Msksemi Incorporated

Typical Application Circuit



Efficiency@V_{IN}=12V



Pin Assignment

Pin Number SOT-23-6	Pin Name	Function
1	BST	Bootstrap pin. Connect a 100nF capacitor from this pin to SW.
2	GND	Ground.
3	FB	Feedback Input. Connect an external resistor divider from the output to FB and GND to set VOUT.
4	EN	Enable pin for the IC. Drive this pin high to enable the part, low to disable.
5	VIN	Supply Voltage. Bypass with a 22μF ceramic capacitor to GND.
6	SW	Inductor Connection. Connect an inductor Between SW and the regulator output.


Copyright© Msksemi Incorporated

AbsoluteMaximumRatings

Parameter	Symbol	Maximum Rating		Unit
Input Voltage	V_{IN}	V_{SS}-0.3～V_{SS}+45		V
SW Voltage		V_{SS}-0.3～V_{IN}+0.3		
BST Voltage		V_{SW}-0.3～V_{SW} +6		
FB Voltage		V_{SS}-0.3～V_{SS}+6		
Power Dissipation	P_D	SOT-23-6L	600	mW
Thermal Resistance θ_{JC}	θ_{JC}	130		°C/W
Thermal Resistance θ_{JA}	θ_{JA}	170		°C/W
Operating Ambient Temperature	Topr	-40～85		°C
Storage Temperature	Tstg	-40～+150		
ESD HBM (Human Body Mode)		2		KV

Caution: The absolute maximum ratings are rated values exceeding which the product could suffer physical damage. These values must therefore not be exceeded under any conditions.

Function Block Diagram



Electrical Characteristics

Note：VIN = 12V, VOUT = 5.0V, unless otherwise specified. Typical values are at TA = 25℃)


Parameter	Symbol	Condition	Min	Typ	Max	Unit
Input Voltage	V_{IN}		4.5		40	V
VIN Under Voltage Protect	V_{UV}			4.3		V
VIN Under Voltage Protect Hys.	V_{UV_hys}			0.2		V
Supply Current	I_{Q1}	V_{EN}=2V，V_{FB}=0.85V		40	60	μA
Supply Shutdown Current	I_{SD}		-1		1	μA
FB Voltage	V_{FB}	T_A=25°C，4.5V≤V_{IN}≤40V	0.776	0.8	0.824	V
Switching Frequency	F_{OSC}			800		kHz
Minimum On Time	T_{ON_MIN}			200		ns
Maximum Duty Cycle	DMAX			90		%
High Side Switch On Resistance	R_{DSON_H}			450		mΩ
Low Side Switch On Resistance	R_{DSON_L}			270		mΩ
High Side Current Limit	I_{LIM}			2		A
EN Rising Threshold	V_{ENH}			1.3		V
EN Falling Threshold	V_{ENL}			1.2		V
EN Input Current	I_{EN}	V_{EN}=5V		2		uA
Thermal Shutdown	T_{SHD}			160		°C
Thermal Shutdown Hys.	T_{SHD_Hys}			20		°C

Typical Performance Characteristics

Vin=12V，Vout=5.0V，L=10uF，Cout=10uF，TA=+25℃，unless otherwise noted.


Efficient @Vout=5.0V

C_{VIN}=22uF，C_{OUT}=10uF，C_{BST}=0.1uF L_{IND}=10uH



Efficient @Vout=3.3V


C_{VIN}=22uF，C_{OUT}=10uF，C_{BST}=0.1uF L_{IND}=10uH



Copyright© Msksemi Incorporated


Steady State Test

Vin=12V，Vout=5.0V，Lout=800mA




Light Load Operation

Vin=12V，Vout=5.0V， Iout=0A




Medium Load Operation

Vin=12V，Vout=5.0V，Lout=400mA




Startup through Enable

Vin=12V，Vout=5.0V，Lout=800mA（Resistive load）




Shutdown through Enable

Vin=12V，Vout=5.0V，Lout=800mA（Resistive load）




Load Transient

Load：300mA ->800mA ->300mA




Short Circuit Protection

Vin=12V，Vout=5.0V，Lout=800mA - Short



Short Circuit Protection

Vin=12V，Vout=5.0V，Lout= Short - 800mA



Copyright© Msksemi Incorporated

Functional Description

The MSK2460G is a synchronous, current-mode, step-down regulator. It regulates input voltages from 4.5V to 40V, and is capable of supplying up to 800mA of load current.

Current-Mode Control

The MSK2460G utilizes current-mode control to regulate the output voltage. The output voltage is measured at the FB pin through a resistive voltage divider and the error is amplified by the internal transconductance error amplifier. Output of the internal error amplifier is compared with the switch current measured internally to control the output current.

PFM Mode

The MSK2460G operates in PFM mode at light load. In PFM mode, switch frequency decreases when load current drops to boost power efficiency at light load by reducing switch-loss, while switch frequency increases when load current rises, minimizing output voltage ripples..

Shutdown Mode

The MSK2460G shuts down when voltage at EN pin is below 0.3V. The entire regulator is off and the supply current consumed by the MSK2460G drops below 0.1uA.

Power Switch

N-Channel MOSFET switches are integrated on the MSK2460G to down convert the input voltage to the regulated output voltage. Since the top MOSFET needs a gate voltage great than the input voltage, a boost capacitor connected between BST and SW pins is required to drive the gate of the top switch. The boost capacitor is charged by the internal 4.0V rail when SW is low.

Vin Under Voltage Protection

A resistive divider can be connected between Vin and ground, with the central tap connected to EN, so that when Vin drops to the pre-set value, EN drops below 1.2V to trigger input under voltage lockout protection.

Over-Current-Protection and Hiccup

At start-up, due to the high voltage at input and low voltage at output, current inertia of the output inductance can be easily built up, resulting in a large start-up output current. In the MSK2460G used current limit of low side power mosfet to control the output current at start-up.

Output Short Protection

When output is shorted to ground, output current rapidly reaches its peak current limit and the top power switch is turned off. And the bottom power switch is turned on and stay on until the output current falls below the current limit. When output current is below the current limit, the top power switch will be turned on again and if the output short is still present, the top power switch is turned off when the peak current limit is reached and the bottom power switch is turned on. This cycle goes on until the output short is removed and the regulator comes into normal operation again.

Thermal Protection

When the temperature of the MSK2460G rises above 160°C, it is forced into thermal shut-down. Only when core temperature drops below 140°C can the regulator becomes active again

Copyright© Msksemi Incorporated

Application Information

Setting the Output Voltage

The external resistor divider is used to set the output voltage. Choose R1 and R2 follow the next table or calculated by following equation, where the internal reference voltage V_{REF}=0.8V.

$$\frac{R1}{R2} = \frac{V_{OUT} - V_{REF}}{V_{REF}}$$

V_{OUT}(V)	R2(kΩ)	R1(kΩ)
2.5	24	51
3.3	24	75
5.0	24	126

Inductor Selection

A 4.7μH to 22μH inductor with a DC current rating of at least 25% percent higher than the maximum load current is recommended for most applications. For highest efficiency, the inductor DC resistance should be less than 15mΩ. For most designs, the inductance value can be derived from the following equation.

$$L > \frac{V_{OUT} \times (V_{IN} - V_{OUT})}{V_{IN} \times \Delta I_L \times f_{OSC}}$$

Where ΔI_L is the inductor ripple current.

Choose ΔI_L to be approximately 30% of the maximum load current.

Under light load conditions below 100mA, larger inductance is recommended for improved efficiency.

Note：If the output voltage is less than 2.5V, it is recommended to use a larger inductance and add a small capacitance（10nF） parallel to R1.

Input Capacitor Selection

The input capacitor reduces the surge current drawn from the input and switching noise from the device. The input capacitor impedance at the switching frequency should be less than input source impedance to prevent high frequency switching current passing to the input. A low ESR input capacitor sized for maximum RMS current must be used. Ceramic capacitors with X5R or X7R dielectrics are highly recommended because of their low ESR and small temperature coefficients. A 22μF ceramic capacitor for most applications is sufficient. Include a capacitor with a value of 0.1 μF for high-frequency filtering and place it as close as possible to the device pins.

Output Capacitor Selection

The output capacitor (C_{OUT}) is required to maintain the DC output voltage, and the capacitance value determines the output ripple voltage. The output voltage ripple can be calculated by:

$$\Delta V_{OUT} = \frac{V_{OUT} \times (V_{IN} - V_{OUT})}{V_{IN} \times f_{OSC} \times L} \times (R_{ESR} + \frac{1}{8 \times f_{OSC} \times C_{OUT}})$$

Where L is the inductor value and R_{ESR} is the equivalent series resistance (ESR) value of the output capacitor.

The output capacitor can be low ESR electrolytic, tantalum or ceramic, which lower ESR capacitors get lower output ripple voltage.

The characteristics of the output capacitor also affect the stability of the regulation system, and a 10uF ceramic capacitor is recommended in typical application.The MSK2460G can be optimized for a wide range of capacitance and ESR values.

Copyright© Msksemi Incorporated

Application Information


For minimum noise problem and best operating performance, the PCB is preferred to following the guidelines as reference.

1. Place the input decoupling capacitor as close to MSK2460G (VIN pin and GND) as possible to eliminate noise at the input pin.The loop area formed by input capacitor and GND must be minimized.
2. Put the feedback trace as far away from the inductor and noisy power traces as possible.
3. The ground plane on the PCB should be as large as possible for better heat dissipation.

Reference Design


Reference 1:

V_{IN} : 5.0V~40V
V_{OUT} : 3.3V
I_{OUT} : 0~800mA




Reference 2:


V_{IN} : 6.5V~40V
V_{OUT} : 5.0V
I_{OUT} : 0~800mA



Copyright© Msksemi Incorporated


SOT-23-6 Package Outline Dimensions





Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	1.050	1.250	0.041	0.049
A1	0.000	0.100	0.000	0.004
A2	1.050	1.150	0.041	0.045
b	0.300	0.500	0.012	0.020
c	0.100	0.200	0.004	0.008
D	2.820	3.020	0.111	0.119
E1	1.500	1.700	0.059	0.067
E	2.650	2.950	0.104	0.116
e	0.950(BSC)		0.037(BSC)	
e1	1.800	2.000	0.071	0.079
L	0.300	0.600	0.012	0.024
θ	0°	8°	0°	8°

SOT-23-6 Suggested Pad Layout



Note:
1.Controlling dimension:in millimeters.
2.General tolerance:± 0.05mm.
3.The pad layout is for reference purposes only.

Copyright© Msksemi Incorporated

Attention

■ Any and all MSKSEMI Semiconductor products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your MSKSEMI Semiconductor representative nearest you before using any MSKSEMI Semiconductor products described or contained herein in such applications.

■ MSKSEMI Semiconductor assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specificationsof any andall MSKSEMI Semiconductor products described orcontained herein.

■ Specifications of any and all MSKSEMI Semiconductor products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer'sproducts orequipment.

■ MSKSEMI Semiconductor. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with someprobability. It is possiblethat these probabilistic failures could give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits anderror prevention circuitsfor safedesign, redundant design, and structural design.

■ In the event that any or all MSKSEMI Semiconductor products(including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from theauthorities concerned in accordance with the above law.

■ No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of MSKSEMI Semiconductor.

■ Information (including circuit diagrams and circuit parameters) herein is for example only ; it is not guaranteed for volume production. MSKSEMI Semiconductor believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringementsof intellectual property rights or other rightsof third parties.

■ Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. Whendesigning equipment, referto the "Delivery Specification" for the MSKSEMI Semiconductor productthat you intend to use.

Copyright© Msksemi Incorporated