




● * ROHS compliant


















RECOMMENDED PCB LAYOUT
TOLERANCE ±0.05
SMT SOLDER AREA



PIN NO.	PIN NAME
C1	VCC
C2	RST
C3	CLK
C5	GND
C6	VPP
C7	I/O
S/W	Switch Pin

NOTES:

1. MATERIAL:
   - 1.1 Housing:High Temperature Thermoplastic UL94V-0; Color Black.
   - 1.2 Terminal:Copper Alloy,T=0.10mm.
   - 1.3 Shell:Stainless Steel,T=0.20mm.
2. FINISH:
   - 2.1 Terminal:Plated Gold on the Contact Area and Solder Tails
   - 2.2 Peg:Plated Gold on the Solder Tails.
3. SPECIALITY:
   - 3.1 Rated current:0.5A
   - 3.2 Rated voltage:50V
   - 3.3 Contact Resistance:80mΩ MAX
   - 3.4 Insulation Resistance:100MΩMIN 100V DC
   - 3.5 Dielectric withstanding voltage: 100V AC.
   - 3.6 Solder ability:245±5°C,5±0.5s.
   - 3.7 Operating condition:Temperature: -30°C~+80°C Humidity: 80% R H MAX

Circuit Diagram for Card Detect Switc



浙江创都电子科技有限公司

REVISION NO.	ECR NO.	DESCRIPTION	MARK	DATE

DIMENSIONS INIT: mm
UNLESS OTHERWISE SPECIFIABLE

DIMENSION	TOLERANCE
X.X: ±	0.15
X.XX: ±	0.10
X.XXX: ±	0.05
ANGULAR: ±	1°

PRODUCT NAME: NANO-SIM 掀盖 7P	DRAWING:	DATE: 2015/04/10
模号：Z	CHECK:	DATE: 2015/04/11
PART NO: CAX-NANO-SIM-KLB7P-TB1.4H-JCFGZ	APPROVED:	DATE: 2015/04/11

SCALE:	DWG ID:	REV.:	PAGE:
1:1	C D	A	1 OF 1

1 2 3 4 5 6