



REV.	ZONE	DESCRIPTION	DESIGN	DATE
C				11/28-11










SLIDE SHELL OPEN　　SLIDE SHELL LOCK









RECOMMENDED PCB LAYOUT
TOLERANCE ±0.05

DIMENSION INFORMATION

P/N	MID.A
CAX-TF-FG-H1.8AU-Z	1.8H

NOTES:
1.MATERIAL:
1).HOUSING MATERIAL:THERMOPLASTIC UL94V-0;COLOR:BLACK
2).CONTACT MATERIAL:COPPER ALLOY,T=0.15mm
3).SHELLMATERIAL:STATILESS STEEL,T=0.20mm
2.FINISH:
1).CONTACT FINISH:50u"min.NICKEL UNDER PLATED,PLATED 3u"Au ON CONTACT AREA;TIN-PLATED HIGH-TEMPER ATURR 80u"-120u" ON SOLDER AREA.
2).SHELL FINISH:Cleaning.
3.ELECTRICAL SPECIFICATIONS:
1).OPERATING VOLTAGE: 250V(AC/DC).
2).CURRENT RATING: 0.5A.
3).OPERATING TEMPERATURE: -20°C~+65°C.
4).INSULATION RESISTANCE: 1000M OHMS min. at 250VDC.
5).DIELECTRIC WITHSTANDING VOLTAGE:500VAC/1minute.
6).CONTACT RESISTANCE:100m OHMS max.

RoHS Compliant

Unless otherwise specified tolerances are	
X.	±0.25
X.X	±0.20
X.XX	±0.15
X.XXX	±0.10
X°	±2.0°
X.X°	±1.0°

浙江创都电子科技有限公司

DRAW NO.	FD111128-003		PART NO：CAX-TF-FG-H1.8AU-Z
DWN			
CHK			模号：Z
APVD			

Third Angle Project

FINISH	MATERIAL	UNIT	SCALE	REV	SHEET
SEE NOTES		mm	1:1	C	1 OF 1