HSF RoHS

NOTES:

1.0. RATING:

1.1. VOLTAGE: AC 500 VOLTAGE R.M.S.

1.2. CURRENT: 1.0 AMPERES

1.3. TEMPERATURE: −55°C TO +105°C

2.0. METERIALS:

1. INSULATOR

INSULATOR	COVER
BLACK	W/COVER

2. **Back Shell: Zinc Alloy Nickel Plated Over Copper**
Flat Screws: Steel Nickel Plated Over Copper
Cable Clipper: Steel Nickel Plated Over Copper
Jackscrews: Steel Nickel Plated Over Copper

3.0. FINISHS:


1. PLATING OF CONTACT:


3: GOLD PLATED 10 u" ON MATING END; TIN/Cu PLATED 100~200 u" ON SOLDER TAIL; ALL OVER NICKEL 50 u" UNDERPLATED


5: GOLD PLATED 30 u" ON MATING END; TIN/Cu PLATED 100~200 u" ON SOLDER TAIL; ALL OVER NICKEL 50 u" UNDERPLATED


2. PLATED OF SHELL:


2: Nickel 5 um MIN Over Copper 2 um Min











ITEM	NAME	MATERIAL	Q'TY
1	HOUSING	PBT UL 94V-0, BLACK	1
2	STRAIN RELIEF	PBT, UL 94V-0, BLACK	1
3	SHELL	SPC-3,Ni/Cu 5um min/2um min	1
4	SHORT CONTACT	C5191R,Ni(50u"),SN(100u"),Au(5U/15u") t=0.25mm	50
5	LONG CONTACT	C5191R,Ni(50u"),SN(100u"),Au(5U/15u") t=0.25mm	50

REV	DATE	MODIFICATION DESCRIPTION	CHANGE
A0	2016.08.03	NEW DRAWING	

OPERATION		DRAW		16.08.03
X.X	±0.30			
X.XX	±0.20	CHECK	QHJL	
X.XXX	±0.10			
Angle	±3°	APPROVE		
DIM	TOL			

SCALE	FIT
UNIT	mm
SIZE	A4
SHEET	1/1
PROJ.	

浙江创都电子科技有限公司

PART NO.	CAX-CN100P-LGWK6330-M100
TITLE:	HALF PITCH RIBBON CONNECTOR SCSI 100P CN-Type Male 180° 出线 锌合金外壳螺杆式