


HSF RoHS


SPECIFICATIONS
PERFORMANCE
Current Rating: 0.5A
Voltage Rating: 50V
Insulation Resistance:500MΩ Min
Contact Resistance:30mΩ Max
Voltage Withstand: 200V AC For 1Minute
Return Loss: < 10dB up to 5GHz
Insertion Loss: < 1.5dB up to 5GHz
ratng Temperature:−40℃ to +125℃


Material
Cap:Stainless steel
Contact:Phosphor Bronze
Contact Area Finish:Gold or Gold flash
Insulator Material:Polyester(UL94V−0)
Housing:LCP
Soldering temperature:260℃±5° 5S












Ordering Information

3710 F XXX 038 XX F R XX

- No.of Pins: 040=40P, 060=60P, 080=80P, 100=100P, 120=120P, 140=140P
- Plastics Height: H=3.7
- Contact Plating: G3=2u" Gold; G4=3u" Gold; G5=5u" Gold; G6=10u" Gold; G7=15u" Gold; G8=30u" Gold; S0=Gold Flash/Matte-Tin; S1=3u" Gold/Matte-Tin; S2=5u" Gold/Matte-Tin; S3=10u" Gold/Matte-Tin; S4=15u" Gold/Matte-Tin; S5=30u" Gold/Matte-Tin
- Insulator Material Option: F=LCP
- Packing: R=Reel+Cap
- Stream Code: 01~99



No.of Contacts	Dimensions					
	A	B	C	D	E	F
24	8.80	15.36	13.70	11.24	12.38	13.80
40	15.20	21.76	20.10	17.64	18.78	20.20
50	19.20	25.76	24.10	21.64	22.78	24.20
60	23.20	29.76	28.10	25.64	26.78	28.20
80	31.20	37.76	36.10	33.64	34.78	36.20
100	39.20	45.76	44.10	41.64	42.78	44.20
120	47.20	53.76	52.10	49.64	50.78	52.20
140	55.20	61.76	60.10	57.64	58.78	60.20

REV	DATE	MODIFICATION DESCRIPTION	CHANGE
	料号编码	3710FXX038XXFRXX	
A	2020.03.04	NEW DRAWING	

OPERATION	
X.X	±0.30
X.XX	±0.20
X.XXX	±0.10
Angle	±3°
DIM	TOL

模号 AUJJ
CHECK
APPROVE

SCALE FIT
UNIT mm
SIZE A4
SHEET 1/1
PROJ.

浙江创都电子科技有限公司

PART NO. CAX-0.8BTB-M-120P-H3.7-TJ5.58-AUJJ
TITLE: 0.8BTB−NPIN H=3.7mm Female