
http://hcdz2017.com/

标记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修改 REVISE	日期 DATE	核准 APPROVE



Note:
Materlals:
Plunger: Bross C6801, plating 3U" Min AU over 50~120U" Ni MIN;
Barrel: Bross C6801, plating 3U" Min AU over 50~120U" Ni MIN;
Srring: SUS304
Throughout the burr removal, the surface roughness is in Ra0.4
Salt spray test:
Electrical: 48H
Voltage: 12V
Current: 3A Max
Mechanical:
Force:80g ± 20% at Normal Working height
Durability: 10000 cycles,
contact reslstance:50m Ω Max at working height.
Ⓚ Key inspection dimension.

序号	品名	材质	电镀/颜色	备注
2	插针	铜	镀金	
1	基座	PA9T	黑色	公座

深圳市虹成电子有限公司	品名 TITLE	磁吸连接器	
	料号 PART NO	HC-CX-PH254-1x6PZ-4050B-E	
一般公差 TOLERANCE	比列 SCALE	1:1	
LENGTH X.XX ±0.05mm X.X ±0.10mm X. ±0.20mm DIAMETER X.XX ±0.03mm X.X ±0.05mm X. ±0.10mm ANGLE X.XX ±0.50° X.X ±1.00° X. ±2.00°	单位 UNIT	MM	制图 DRAW AhYe
	张数 PART NO	1 OF 1	审核 CHECKED 夏操云
	版本 REV	A	批准 APPROVE 赵亮亮

http://hcdz2017.com/