MUR860CT-OSEN


Super-Fast Rectifier - 8Amp 600Volt

◆ Features:

- ✧ Super fast recovery time. high voltage
  快恢复时间，高电压
- ✧ Low forward voltage drop
  正向压降低
- ✧ High efficiency and low power loss
  高效低功耗
- ✧ High volume of current and good capability of surge current
  大电流浪涌能力强

RoHS COMPLIANT


TO-220AB-2L




◆ Applications

- ✧ High frequency rectifier of switching mode power supplies
  高频整流器开关电源
- ✧ Freewheeling diodes
  续流二极管
- ✧ Polarity protection application
  极性保护应用
- ✧ DC-DC converters
  直流-直流变换器

PIN CONNECTIONS





SYMBOL	MM		
	MIN	NOM	MAX
*A	10.00	10.05	10.20
*A1	10.10	10.30	10.50
A2	9.80	9.90	10.00
*B	8.80	9.00	9.20
*C	12.80	13.10	13.40
*D2		5.08BSC	
E	1.27	1.32	1.40
*F1	0.75	0.80	0.85
*G	1.26	1.27	1.28
*H	2.40	2.55	2.70
h1	2.70	2.74	2.80
h2	1.27	1.32	1.37
h3	0.40	0.42	0.45
*h4	3.40	3.45	3.50
h5	3.60	3.63	3.65
*I	0.35	0.38	0.45
*J	4.45	4.50	4.60
*K	4.90	5.00	5.10
*k	6.00	6.03	6.05
L1	3.30	3.40	3.50
L2	3.90	4.00	4.10
*L3	4.50	4.60	4.70
*ϕP	3.75	3.80	3.90
带*为检验尺寸，C之尺寸参考原则必须满足有“实脚”			

◆ Absolute Maximum Ratings (Tc=25°C)

Symbol	Parameters	Ratings	Unit
V_{RRM}	Repetitive Peak Reverse Voltage 最大反向重复峰值电压	**600**	V
V_{RWM}	Working peak reverse voltage 反向峰值工作电压	**600**	V
V_R	Maximum DC blocking voltage 最大直流反向电压	**600**	V
$I_{F(AV)}$	Maximum average forward rectified current Total device 最大正向平均电流	**8**	A
I_{FSM}	Peak Forward Surge Current 正向峰值浪涌电流	**120**	A
T_j	Operating junction temperature range 结温	**175**	℃
T_{stg}	Storage temperature range 贮存温度	**-55~175**	℃

◆ Electrical characteristics

Symbol	Parameters	Min	Typical	Max	Units	Conditions
I_R	Maximum Reverse Leakage Current （Note 1） 最大反向瞬态电流	--	--	**10**	μA	V_R=600V，T_C = 25 °C
V_F	Maximum Instantaneous Forward Voltage（Note 2） 最大瞬态正向压降	--	**1.30**	**1.50**	V	I_F= 8 A，T_C = 25 °C
$R_{th(j-c)}$	Typical Thermal Resistance,Junction to Case 结到外壳的典型热阻	--	--	**1.76**	°C/W	
dV/dt	Voltage Rate of Change 电压变化率	--	--	**10000**	V/μs	
Trr	Maximum Reverse recovery time 最大反转恢复时间	--	**25**	**35**	ns	IF=1.0A,V_R=30V dIF/dt=50A/us

Note 1: 2.0uS Pulse Width, f=1.0KHz

Note 2: Pulse Test : 300us Pulse Width, 2% Duty Cycle

◆ DISCLAIMER

Unless otherwise specified in the datasheet, OSEN products are designed and qualified as standard commercial products and are not intended for use in applications that require extraordinary levels of quality and reliability, such as automotive, aviation/aerospace, and life-support devices or systems.

Semiconductor products are subject to an inherent possibility of failure or malfunction under certain conditions, which may result in personal injury, death, or property damage. Customers shall be solely responsible for ensuring adequate safety provisions in their system designs. And independently assume all responsibility arising from the application or use of the products or circuits described in this document

OSEN does not assume any liability arising out of the application or use of any product or circuit described herein; neither does it convey any license under its patent rights, nor the rights of others. OSEN reserves the right to improve product design, function, and reliability without notice.