



REVISION RECORD			
ECO	DESCRIPTION	DRFT	CHKD









PC Board Layout

Component Side Shown

NOTES:

MATERIAL :

1.HOUSING MATERIAL	:GLASS FILLED POLYESTER UL94V-0.
2.CONTACT MATERIAL	:PHOSPHOR BRONZE φ0.46mm.
3.PLATING	:GOLD PLATING OVER NICKEL.
4.SHIELD	ɔmm THICKNESS COPPER ALLOY WITH NICKEL PLATED.
5.LED	:OPTION

ELECTRICAL:

1.VOLTAGE RATING	:125 VAC RMS.
2.CURRENT RATING	:1.5 AMP.
3.CONTACT RESISTANCE	:30 MILLIOHMS MAX.
4.INSULATION RESISTANCE	:500 MEGOHMS MIN @ 500V DC .
5.DIELECTRIC WITHSTANDING RESISTANCE	:1000V AC RMS 50Hz. 1MIN.

MECHANICAL:

1. DURRABILITY	:750 CYCLES MIN.
2.PCB RETENTION PRE-SOLDER	:1 LB MIN.

ENVIRONMENTAL:

1. STORAGE	: -40℃~+85℃
2. OPERATION	: 0°C TO 70°C.

PART NUMBER:

MM (INCH)	DFTO SHB 2007.05.05	浙江创都电子科技有限公司	
TOLERANCES EXCEPT AS NOTED	CHKD LANBO 2007.05.05		
MM .0 ± 0.15 ± .00 ± 0.075 ± .000 ± 0.05 ±	MFO	PART NO：CAX-RJ56-8P8C-DLDT-SN	
	APPVL		
	MATERIAL :	模号：SN	SIZE A3 / REV 0
ANGLES ± 0.5	Q.T'Y :		
THIRD ANGLE PROJECTION	FINISH	DO NOT SCALE DRAWING	SHEET X OF Y
DETACHED LISTS	SCALE :		

8 7 6 5 4 1