

RoHS


REV	ECN NO.	DESRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	更换图框			2024.04.17



SPECIFICATIONS
Current Rating: 20 Amps @ 500V AC
Temperature Rating: -40 °C to 125 °C
Insulator: PBT , UL 94V-0
Contacts: Brass,
Finish:Tin plated over Nickel
Fuse Size：Standard automotive blade Fuses



3D REFER TO



适用线路板(PCB LAYOUT)

X.±0.50	X.°±
.X±0.25	.X°±
.XX±0.15	.XX°±
.XXX±0.10	.XXX°±
UNITS:	mm

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED,COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN

PART NO: XF-507P		XFCN兴飞连接器	
TITLE: 标准（中型）汽车刀片保险丝座		0769-82001899	
		www.xfconn.com	
		DWG NO: /	
APPD	Chen ZhiQiang		
CHKD	Liu Wei	VIEW	
DRAW	Chen HongJiang	SCALE	SHEET / REV
DATE	2024.07.19	NONE	1/1 / A1