



PIN	SIGNAL NAME
B12	GND
B9	VBUS
A9	VBUS
A12	GND





NOTES:

1.MATERIAL:
- MOLDING: LCP UL94 V-0
- CONTACT:COPPER ALLOY.
- GOLD PLATED Min ON CONTACT AREA,100u''
- Min TIN (LEAD FREE) ON SOLDER AREA,
- SHELL: SUS201-H,T=0.25±0.03mm
- 50u" NICKEL PLATING OVER ALL.

2.MECHANICAL:
- INSERTION: 5~20N.
- EXTRACTION: 8~20N AFTER TEST.
- DURABILITY: 5000 CYCLES

3.ELECTRICAL:
- CURRENT: 3A FOR VBUS;
- 1.25A FOR GND PIN.
- 0.25A FOR OTHER.
- VOLTAGE: 20 V MAX
- WITHSTANDING VOLTAGE: 100V AC R.M.S.
- CONTACT RESISTANCE: 40mΩ MAX.
- INSULATION RESISTANCE: 100MΩ MIN.

4.ENVIRONMENTAL
- TEMPERATURE RANGE -25°C ~ +85°C

5. 尺寸标注事项:
图示有标☆"者为首样全检,重点管控尺寸.

6. 产品符合RoHS标准.

深圳市韩下电子有限公司

深圳市韩下电子有限公司	
绘图：黄彬	产品名称：
审核：张伟	HX-TYPE-C 2P IP65-100
核准：罗小春	

深圳市韩下电子有限公司
Shenzhen Hanxia Electronic Co.,Ltd
Tel:0755-23086569 Email: shouhan2@so-han.com

承　认　书

SPECIFICATION FOR APPROVAL

产 品 编 码
Material code: _____

产品名称 Project： TYPE-C

规格型号 Part No： HX-TYPE-C 2P IP65-100

贵公司承认印 Approval signatures

料 号/Part No.	签　章/Signatures

日期 Date:

拟制/Drawn	黄彬	深圳市韩下电子有限公司 工程专用章
审核/Check	张伟	
批准/Approved	罗小春	

深圳市韩下电子有限公司