UMW PTVSHC3D7VU

1.Description

The PTVSHC3D7VU protects sensitive semiconductor components from damage or upset due to electrostatic discharge (ESD) and other voltage induced transient events. The PTVSHC3D7VU is available in a SOD-323 package with working voltages of 7 volt.

2.Mechanical Characteristics

- Lead finish:100% matte Sn(Tin)
- Mounting position: Any
- Qualified max reflow temperature:260℃
- Pure tin plating: 7 ~ 17 um
- Pin flatness:≤ 3mi


3.Features

- 1100W Peak pulse power per line (tp=8/20μs)
- Response time is typically < 1ns
- Protect one I/O or power line
- Low clamping Voltage
- Transient protection for data lines to IEC 61000-4-2(ESD)
- ±30KV(air), ±30KV(contact); IEC 61000-4-4 (EFT) 40A (5/50ns)

4.Applications


- Cell phone handsets and accessories
- Personal digital assistants (PDA's)
- Notebooks, desktops, and servers
- Portable instrumentation
- Cordless phones
- Digital cameras
- Peripherals
- MP3 players

5.Pinning information



SOD-323

6.Electrical Parameters (T_A=25°C unless otherwise noted)



Symbol	Parameter
V_{RWM}	Peak Reverse Working Voltage
I_R	Reverse Leakage Current @ V_{RWM}
V_{BR}	Breakdown Voltage @ I_T
I_T	Test Current
I_{PP}	Maximum Reverse Peak Pulse Current
V_C	Clamping Voltage @ I_{PP}
P_{PP}	Peak Pulse Power
C_J	Junction Capacitance
I_F	Forward Current
V_F	Forward Voltage @ I_F

7.Electrical Characteristic (T_A=25°C unless otherwise noted)

Parameter	Symbol	Conditions	Min	Typ	Max	Units
Working Voltage	V_{RWM}				7	V
Breakdown Voltage	V_{BR}	I_T=1mA		8	9.5	V
Reverse Leakage Current	I_R	V_{RWM}=7V			1	μA
Clamping Voltage	V_C	I_{PP}=60A, t_p=8/20μs		18	25	V
Junction Capacitance	C_J	V_R=0V, f=1MHz	470	500	550	pF

8.Absolute maximum rating @ 25°C

Parameter	Symbol	Value	Units
Peak Pulse Power (tp=8/20μs)	P_{PP}	1100	W
Lead Soldering Temperature	T_L	260 (10 sec)	°C
Junction Temperature	T_J	-55 to 125	°C
Storage Temperature	T_{STG}	-55 to 150	°C

9.Typical characteristic




Figure 1: Pulse Waveform




Figure 2: Power Derating Curve




Figure 3: Clamping voltage vs. Peak pulse current




Figure 4: Capacitance vs. Reveres voltage




Figure 5: Non Repetitive Peak Pulse Power vs. Pulse time

10.Solder Reflow Recommendation





Figure 6: Peak Temp=257°C, Ramp Rate=0.802deg. °C/sec


11.SOD-323 Package Outline Dimensions



DIMENSIONS (mm are the original dimensions)

Symbol	A	b_p	C	D	E	H_E	A_1	p
Min	0.80	0.25	0.10	1.50	1.15	2.30	0.01	0.20
Max	1.20	0.40	0.15	1.80	1.35	2.80	0.10	0.50

12.Ordering information



ww: Batch Code

Order Code	Package	Base QTY	Delivery Mode
UMW PTVSHC3D7VU	SOD-323	3000	Tape and reel

13.Disclaimer

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.