UMW IRF9317TR

-30V P-Channel MOSFET

1.Features

- $V_{DS\ (V)}$=-30V
- I_D=-16A
- $R_{DS(ON)}$<6.6mΩ(V_{GS}=-10V)
- $R_{DS(ON)}$<10.2mΩ(V_{GS}=-4.5V)
- Industry-Standard SO8 Package
- RoHS Compliant Containing no Lead, no Bromide and no Halogen

2.Application

- Charge and Discharge Switch for Notebook PC Battery Application


3.Benefits


- Multi-Vendor Compatibility
- Environmentally Friendlier

4.Pinning information

Pin	Symbol	Description
1,2,3	S	SOURCE
4	G	GATE
5,6,7,8	D	DRAIN

SOP-8





5.Absolute Maximum Ratings

Parameter		Symbol	Rating	Units
Drain- Source Voltage		V_{DS}	-30	V
Gate-to-Source Voltage		V_{GS}	±20	V
Continuous Drain Current, V_{GS}=10V	T_A=25°C	I_D	-16	A
Continuous Drain Current, V_{GS}=10V	T_A=70°C		-13	A
Pulsed Drain Current ①		I_{DM}	-130	A
Power Dissipation ④	T_A=25°C	P_D	2.5	W
Power Dissipation ④	T_A=70°C		1.6	W
Linear Derating Factor			0.02	W/°C
Junction and Storage Temperature Range		T_J, T_{STG}	-55 to 150	°C

6.Electrical Characteristics T_J=25°C

Parameter	Symbol	Conditions	Min	Typ	Max	Units
Static						
Drain-Source Breakdown Voltage	BV_{DSS}	I_D=-250μA, V_{GS}=0V	-30			V
Breakdown Voltage Temp. Coefficient	$\Delta BV_{DSS}/\Delta T_J$	I_D=-1mA,Reference to 25°C		0.022		V/°C
Static Drain-to-Source On-Resistance	$R_{DS(ON)}$	V_{GS}=-10V, I_D=-16A ③		5.4	6.6	mΩ
		V_{GS}=-4.5V, I_D=-13A ③		8.3	10.2	
Gate Threshold Voltage	$V_{GS(th)}$	V_{DS}=V_{GS}, I_D=-50μA	-1.3	-1.8	-2.4	V
Gate Threshold Voltage Coefficient	$\Delta V_{GS(th)}$			-5.7		mV/°C
Drain-to-Source Leakage Current	I_{DSS}	V_{DS}=-24V, V_{GS}=0V			-1	μA
		V_{DS}=-24V,V_{GS}=0V,T_J=125°C			-150	μA
Gate-to-Source Forward Leakage	I_{GSS}	V_{GS}=-20V			-100	nA
Gate-to-Source Reverse Leakage		V_{GS}=20V			100	nA
Forward Transconductance	g_{FS}	V_{DS}=-10V, I_D=-13A	36			S
Total Gate Charge	Q_g	V_{DS}=-15V,V_{GS}=-4.5V,I_D=-13A		31		nC
Total Gate Charge	Q_g	V_{DS}=-10V		61	92	nC
Gate-to-Source Charge	Q_{gs}	V_{GS}=-15V		9		nC
Gate-to-Drain Charge	Q_{gd}	I_D=-13A		14		nC
Gate Resistance	R_g			14		Ω
Turn-On Delay Time	$t_{D(on)}$	V_{DD}=-15V, V_{GS}=-4.5V ③		19		ns
Rise Time	t_r	I_D=-1A		64		ns
Turn-Off Delay Time	$t_{D(off)}$	R_G=6.8Ω		160		ns
Fall Time	t_f	See Figs. 20a &20b		120		ns
Input Capacitance	C_{iss}	V_{GS}=0V		2820		pF
Output Capacitance	C_{oss}	V_{DS}=-15V		640		pF
Reverse Transfer Capacitance	C_{rss}	f=1.0MHz		370		pF
Avalanche Characteristics						
Single Pulse Avalanche Energy ②	E_{AS}				330	mJ
Avalanche Current ①	I_{AR}				-13	A

Diode Characteristics						
Continuous Source Current (Body Diode)	I_S	MOSFET symbol showing the integral reverse p-n junction diode.			-2.5	A
Pulsed Source Current (Body Diode) ①	I_{SM}				-130	A
Diode Forward Voltage	V_{SD}	T_J=25°C,I_S=-2.5A,V_{GS}=0V③			-1.2	V
Reverse Recovery Time	t_{rr}	T_J=25°C, I_F=-2.5A,V_{DD}=-24V dI/dt=100A/μs ③		33	50	ns
Reverse Recovery Charge	Q_{rr}			30	45	nC
Thermal Resistance						
Junction-to-Drain Lead ⑤	$R_{\theta JL}$				20	°C/W
Junction-to-Ambient ④	$R_{\theta JA}$				50	°C/W

Notes:

① Repetitive rating; pulse width limited by max. junction temperature.


② Starting T_J=25°C, L=4.3mH, R_G=25Ω, I_{AS}=-13A.

③ Pulse width ≤ 400μs; duty cycle ≤ 2%.

④ When mounted on 1 inch square copper board.


⑤ R_θ is measured at T_J of approximately 90°C.

7.1Typical Characterisitics




$-V_{DS}$ - Drain-to-Source Voltage (V)

Fig 1. Typical Output Characteristics




$-V_{DS}$ - Drain-to-Source Voltage (V)

Fig 2. Typical Output Characteristics




$-V_{GS}$, Gate-to-Source Voltage (V)

Fig 3. Typical Transfer Characteristics




T_J, Junction Temperature (°C)

Fig 4. Nomalized On-ResistanceVs. Temperature



$-V_{DS}$,Drain-to-Source Voltage (V)


Fig 5. Typical Capacitance Vs. Drain-to-Source Voltage



Q_G, Total Gate Charge (nC)


Fig 6. Typical Gate Charge Vs. Gate-to-Source Voltage

7.2Typical Characterisitics




$-V_{SD}$, Source-to-Drain Voltage (V)

Fig 7. Typical Source-Drain Diode Forward Voltage




$-V_{DS}$, Drain-to-Source Voltage (V)

Fig 8. Maximum Safe Operating Area




T_A , Ambient Temperature (°C)

Fig 9. Maximum Drain Current vs. Ambient Temperature




T_J , Temperature (°C)

Fig 10. Threshold Voltage vs. Temperature



$-V_{GS}$, Gate -to -Source Voltage (V)

Fig 11. On-Resistance vs. Gate Voltage



$-I_D$, Drain Current (A)

Fig 12. Typical On-Resistance vs. Drain Current

7.3Typical Characterisitics




Fig 13. Maximum Avalanche Energy vs. Drain Current




Fig 14. Typical Power vs. Time




Fig 15. Maximum Effective Transient Themal Impedance, Junction-to-Ambient




Fig 16a. Gate Charge Test Circuit




Fig 16b. Gate Charge Waveform




Fig 17a. Unclamped Inductive Test Circuit




Fig 17b. Unclamped Inductive Waveforms




Fig 18a. Switching Time Test Circuit





Fig 18b. Switching Time Waveforms

8.SOP-8 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	A1	A2	A3	b	c	D	E	E1	e	h	L
Min	-	0.05	1.30	0.60	0.39	0.20	4.70	5.80	3.80	1.24	0.30	0.50
Max	1.75	0.20	1.50	0.70	0.47	0.24	5.10	6.20	4.00	1.30	0.50	0.80

Symbol	L1	θ
Min	1.00	0°
Max	1.10	8°

9.Ordering information



yy: Year Code
ww: Week Code

Order Code	Package	Base QTY	Delivery Mode
UMW IRF9317TR	SOP-8	3000	Tape and reel

10.Disclaimer

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.