
3-Terminal Positive Voltage Regulator



1.OUT 2.GND 3.IN

SOT-89 Plastic Package

Absolute Maximum Ratings (T_a = 25 °C)


Parameter	Symbol	Rating	Unit
Input Voltage	V_I	35	V
Power Dissipation	P_{tot}	800 [1)]	mW
Operating Temperature	T_{opr}	- 20 to + 120	°C
Storage Temperature Range	T_{stg}	- 55 to +150	°C

[1)] 15 mm X 25 mm X 0.7 mm alumina ceramic board, $T_a \leq 25$ °C

Electrical Characteristics (T_a = 25 °C)

(Unless otherwise specified, 0 °C ≤ T_J ≤ 125 °C, V_I = 19 V, I_O = 40 mA, C_I = 0.33 µF, C_O = 0.1 µF)


Parameter	Symbol	Test Condition	Min.	Typ.	Max.	Unit
Output Voltage	V_O	T_j = 25 °C	11.5	12	12.5	V
		14.5 V ≤ V_I ≤ 27 V, 1 mA ≤ I_O ≤ 40 mA	11.4	-	12.6	V
		V_I = 19 V, 1 mA ≤ I_O ≤ 70 mA	11.4	-	12.6	V
Line Regulation	Regline	14.5 V ≤ V_I ≤ 27 V, T_j = 25 °C	-	-	250	mV
		16 V ≤ V_I ≤ 27 V, T_j = 25 °C	-	-	200	
Load Regulation	Regload	1 mA ≤ I_O ≤ 100 mA, T_j = 25 °C	-	-	100	mV
		1 mA ≤ I_O ≤ 40 mA, T_j = 25 °C	-	-	50	
Quiescent Current	I_Q	T_j = 25 °C	-	-	6	mA
Quiescent Current Change	ΔI_Q	16 V ≤ V_I ≤ 27 V	-	-	1.5	mA
		1 mA ≤ I_O ≤ 40 mA	-	-	0.1	
Output Noise Voltage	V_N	10 Hz ≤ f ≤ 100 KHz, T_j = 25 °C	-	80	-	µV
Ripple Rejection	RR	f = 120 Hz, 15 V ≤ V_I ≤ 25 V, T_j = 25 °C	37	-	-	dB
Dropout Voltage	V_{Drop}	T_j = 25 °C	-	1.7	-	V




Copyright © All right reserved： Heyuan China Base Electronics Technology Co., Ltd.

Typical Characteristics (continued) (V_{OUT} = 12V, T_J = 25°C, unless otherwise specified)


Output Characteristics




Dropout Characteristics




Quiescent Current




Current Cut-off Grid Voltage



Output Voltage vs Junction Temperature



Power Derating Curve



Copyright © All right reserved： Heyuan China Base Electronics Technology Co., Ltd.