
FEATURES

- Low on-resistance
- Fast switching speed
- Low voltage drive makes this device ideal for portable equipment
- Easily designed drive circuits
- Easy to parallel

SOT-23




1. GATE
2. SOURCE
3. DRAIN

MOSFET MAXIMUM RATINGS (T_a = 25°C unless otherwise noted)

Symbol	Parameter	Value	Units
V_{DS}	Drain-Source Voltage	30	V
V_{GSS}	Gate-Source Voltage	+20	V
		-12	V
I_D	Continuous Drain Current	0.1	A
P_D	Power Dissipation	0.35	W
T_J	Junction Temperature	150	℃
T_{stg}	Storage Temperature	-55~+150	℃
$R_{\theta JA}$	Thermal Resistance, Junction-to-Ambient	357	℃ /W

Equivalent circuit



MOSFET ELECTRICAL CHARACTERISTICS(T_a=25℃ unless otherwise noted)


Parameter	Symbol	Test Condition	Min	Typ	Max	Units
Off Characteristics						
Drain-Source Breakdown Voltage	V_{DS}	V_{GS} = 0V, I_D = 10μA	30			V
Zero Gate Voltage Drain Current	I_{DSS}	V_{DS} =30V,V_{GS} = 0V			0.2	μA
Gate –Source leakage current	I_{GSS}	V_{GS} =+20V, V_{DS} = 0V			1	μA
		V_{GS} =-12V, V_{DS} = 0V			-1	μA
Gate Threshold Voltage	$V_{GS(th)}$	V_{DS} = 3V, I_D =100μA	0.8		1.5	V
Drain-Source On-Resistance	$R_{DS(on)}$	V_{GS} = 4V, I_D =10mA			8	Ω
		V_{GS} =2.5V,I_D =1mA			13	Ω
Forward Transconductance	g_{FS}	V_{DS} =3V, I_D = 10mA	20			mS
Dynamic Characteristics*						
Input Capacitance	C_{iss}	V_{DS} =5V,V_{GS} =0V,f =1MHz		13		pF
Output Capacitance	C_{oss}			9		pF
Reverse Transfer Capacitance	C_{rss}			4		pF
Switching Characteristics*						
Turn-On Delay Time	$t_{d(on)}$	V_{GS} =5V, V_{DD} =5V, I_D =10mA, Rg=10Ω, R_L=500Ω,		15		ns
Rise Time	t_r			35		ns
Turn-Off Delay Time	$t_{d(off)}$			80		ns
Fall Time	t_f			80		ns

* These parameters have no way to verify.


WPMtek

Typical Characteristics


Output Characteristics




Transfer Characteristics




$R_{DS(ON)}$ — I_D



$R_{DS(ON)}$ — V_{GS}




I_S — V_{SD}




WPMtek

PACKAGE OUTLINE

Plastic surface mounted package; 3 leads **SOT-23**





UNIT	A	B	bp	C	D	E	HE	A1	Lp
mm	1.40 0.95	2.04 1.78	0.50 0.35	0.19 0.08	3.10 2.70	1.65 1.20	3.00 2.20	0.100 0.013	0.50 0.20

WPMtek reserves the right to make changes to the product specification and data in this document without notice. WPMtek makes no warranty, representation or guarantee regarding the suitability of its products for any particu lar purpose, nor does WPMtek assume any liability arising from the application or use of any products or circuits, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages.Any enquiry ,please write to sales@wpmtek.com for futher information.